








Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm



With Cap
Scale 4:1

NOTE:

1. MATERIAL:
HOUSING: HIGH TEMP PLASTIC, UL94-V0, BLACK
TERMINAL: COPPER ALLOY, T=0.15MM
CAP: STAINLESS STEEL, T=0.1MM
2. FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1.27um(50u")MIN Ni OVER ALL
3. SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1420
4. THE HSG. WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW.
5. PRODUCT NUMBERING:
20021323 - X 0 0 XX X X LF

— LEAD FREE

PLATING:
1:GOLD FLASH ALL OVER
4:0.25um(10U")GOLD AT CONTACT
8:0.76um(30U")GOLD AT CONTACT
9:1u" GOLD OVER 30u" PdNi AT CONTACT

— PACKING

D: TUBE + CAP

T: TUBE

C: REEL + CAP (8,10,20,22,30,40,42,70P)

— PIN COUNT

4, 6, 8, ..., 80

(EVERY EVEN PIN)

— 0· WITHOUT POST

0: WITHOUT POST
1: WITH POST

mat'l. code				surface 		tolerance		projection 		product family MINITEK			
litr ecn nodr date				tolerances unless otherwise specified		title		1.27X1.27MM BTB RECEPTACLE SMT BOTTOM ENTYR					
A	T09-1117	S.LIN	09/15/09	angle line size		0.X±0.38	MM						
B	T10--0020	S.LIN	01/20/10			0.XX±0.25							
C	T10--0120	S.LIN	07/30/10		0±.2'	0.XXX±0.10							
D	ELXT004402	S.LIN	07/11/11	dr	STERLING LIN	09/15/09		dwg no		sheet 1 of 1		size	
E	ELX-N-010370	ZK	01/16/12	engr	STERLING LIN	09/15/09		20021323		A4			
F	ELX-N-011532	ZK	05/07/12	chr	GRAY HSIEH	09/15/09							
G	ELX-N-011756	ZK	05/28/12	appd	JOSEPH	09/15/09		type Product Customer Drawing					
sheet index		revision											
		sheet 1											