

Ultra Low -OH



CHARACTERISTICS

Step index	High laser damage threshold
Numerical aperture: 0.22 ± 0.02	Sterilizable and bio-compatible – USP class VI*
Full acceptance cone: 25.4 degrees	Low-OH silica core, doped silica clad
Vis-NIR transmission, 380nm to 2,200nm	Polyimide buffer standard; silicone, acrylate, high-temperature acrylate also available.

Polymicro Silica/Silica Optical Fiber FI

Polyimide concentricity < 3µm
Sizes for bundling
Tighter tolerances available
Operating temperature: -65° to +300°C
Intermittent, up to 400°C
Proof tested to 100kpsi

Typical Attenuation



* The end manufacturer is responsible for bio-compatibility and sterilization testing and validation studies.

Specifications

Product Descriptor	Core (µm)	Clad (µm)	Buffer (µm)
FIP100110125*	100 ± 3	110 ± 3	124 ± 3
FIP150165195*	150 ± 3	165 ± 3	195 ± 5
FIP200220240	200 ± 4	220 ± 4	239 ± 5
FIP300330370	300 ± 6	330 ± 7	370 ± 7
FIP400440480	400 ± 8	440 ± 9	480 ± 7
FIP500550590	500 ± 10	550 ± 10	590 ± 10
FIP600660710	600 ± 10	660 ± 10	710 ± 10
FIA8008801100**	800 ± 20	880 ± 15	1100 ± 30
FIP100120140	100 ± 3	120 ± 3	140 ± 4
FIP200240280	200 ± 4	240 ± 4	275 ± 5
FIP320385415	320 ± 8	385 ± 8	415 ± 10
FIP050070085	50 ± 2	70 ± 2	85 ± 3
FIP100140170	100 ± 3	140 ± 3	170 ± 5
FIA100010501250**	1000 ± 20	1050 ± 15	1250 ± 40

Note: The items listed in this table are standard configurations and sizes. Other configurations may be available on request.

* Not recommended for wavelengths greater than 1000nm.

** Acrylate buffer; Operating Temperature: -65° to 80°C