




INSULATION

SERRATIONS

SLEEVE

BODY

5

13.49
[.531]

11.89
[.468]
MIN

26.77
[1.054]
MAX

33.58
[1.322]
MAX

0.79
[.031]
MIN

4

ø8.33±0.13
[ø.328±.005]
FOR M8[5/16] STUD

6

7

1

2

3

4

5

6

7

—	100	LOOSE PC, BOX	8-35111-1
MS25036-113 CLASS 2	2500	ON TAPE, REEL	2-35111-1
MS25036-113 CLASS 1&2	500	LOOSE PIECE	35111
MILITARY PART NO& CLASS	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

RECOMMENDED OPERATING TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
300V MAX

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± —

1 PLC ± —

2 PLC ± 0.20[.008]

3 PLC ± —

4 PLC ± —

ANGLES ± 5°

FINISH

6

7

DWN KIRAN HOLAL 02APR12

CHK ROHDE DANIEL 02APR12

APVD ROHDE DANIEL 02APR12

PRODUCT SPEC

APPLICATION SPEC

WEIGHT —

CUSTOMER DRAWING

STE

TE Connectivity

WIRE TERMINAL

P.I.D.G RING TONGUE

WIRE SIZE: 12-10

SIZE A3

CAGE CODE 00779

DRAWING NO C-35111

RESTRICTED TO —

SCALE 5:1

SHEET 1 OF 1

REV K3

1470-19 (3/11)