


MLCC Gold Termination – AU Series



General Specifications



AVX Corporation will support those customers for commercial and military Multilayer Ceramic Capacitors with a termination consisting of Gold. This termination is indicated by the use of a “7” or “G” in the 12th position of the AVX Catalog Part Number. This fulfills AVX’s commitment to providing a full range of products to our customers. Please contact the factory if you require additional information on our MLCC Gold Termination.

PART NUMBER

AU03	Y	G	104	K	A	7	2	A
Size	Voltage	Dielectric	Capacitance Code (In pF)	Capacitance Tolerance	Failure Rate	Terminations	Packaging	Special Code
AU02 - 0402 AU03 - 0603 AU05 - 0805 AU06 - 1206 AU10 - 1210 AU12 - 1812 AU13 - 1825 AU14 - 2225 AU16 - 0306 AU17 - 0508 AU18 - 0612	6.3V = 6 10V = Z 16V = Y 25V = 3 35V = D 50V = 5 100V = 1 200V = 2 500V = 7	C0G (NP0) = A X7R = C X5R = D	2 Sig. Digits + Number of Zeros	B = ±10 pF (<10pF) C = ±.25 pF (<10pF) D = ±.50 pF (<10pF) F = ±1% (≥ 10 pF) G = ±2% (≥ 10 pF) J = ±5% K = ±10% M = ±20%	A = Not Applicable	G* = 1.9 μ" to 7.87 μ" 7 = 100 μ" minimum	2 = 7" Reel 4 = 13" Reel U = 4mm TR (01005) Contact Factory For Multiples*	A = Std. Product

* Contact factory for availability.

MLCC Gold Termination – AU Series

Capacitance Range (NP0 Dielectric)



PREFERRED SIZES ARE SHADED

SIZE	AU02				AU03				AU05					AU06					
Soldering	Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*					Reflow/Epoxy/ Wire Bond*					
Packaging	All Paper				All Paper				Paper/Embossed					Paper/Embossed					
(L) Length	mm	1.00 ± 0.10			mm	1.60 ± 0.15			2.01 ± 0.20					3.20 ± 0.20					
	(in.)	(0.040 ± 0.004)				(0.063 ± 0.006)			(0.079 ± 0.008)					(0.126 ± 0.008)					
(W) Width	mm	0.50 ± 0.10			mm	0.81 ± 0.15			1.25 ± 0.20					1.60 ± 0.20					
	(in.)	(0.020 ± 0.004)				(0.032 ± 0.006)			(0.049 ± 0.008)					(0.063 ± 0.008)					
(t) Terminal	mm	0.25 ± 0.15			mm	0.35 ± 0.15			0.50 ± 0.25					0.50 ± 0.25					
	(in.)	(0.010 ± 0.006)				(0.014 ± 0.006)			(0.020 ± 0.010)					(0.020 ± 0.010)					
WVDC	16	25	50	100	16	25	50	100	16	25	50	100	200	16	25	50	100	200	500
Cap (pF)	0.5	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.0	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.2	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.5	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	1.8	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	2.2	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	2.7	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	3.3	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	3.9	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	4.7	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	5.6	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	6.8	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	8.2	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	10	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	12	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	15	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	18	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	22	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	27	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	33	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	39	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	47	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	56	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	68	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	82	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	100	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	120	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	150	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	180	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J
	220	C	C	C	G	G	G	G	J	J	J	J	J	J	J	J	J	J	M
	270	C	C	C	G	G	G	G	J	J	J	J	M	J	J	J	J	J	M
	330	C	C	C	G	G	G	G	J	J	J	J	M	J	J	J	J	J	M
	390	C	C	C	G	G	G	G	J	J	J	J	M	J	J	J	J	J	M
	470	C	C	C	G	G	G	G	J	J	J	J	M	J	J	J	J	J	M
	560				G	G	G		J	J	J	J	M	J	J	J	J	J	M
	680				G	G	G		J	J	J	J	M	J	J	J	J	J	P
	820				G	G	G		J	J	J	J	M	J	J	J	J	M	
	1000				G	G	G		J	J	J	J	M	J	J	J	J	Q	
	1200								J	J	J			J	J	J	J	Q	
	1500								J	J	J			J	J	J	M	Q	
	1800								J	J	J			J	J	M	M		
	2200								J	J	N			J	J	M	P		
	2700								J	J	N			J	J	M	P		
	3300								J	J				J	J	M	P		
	3900								J	J				J	J	M	P		
	4700								J	J				J	J	M	P		
	5600													J	J	M			
	6800													M	M				
	8200													M	M				
	0.010																		
	0.012																		
	0.015																		
	0.018																		
	0.022																		
	0.027																		
	0.033																		
	0.039																		
	0.047																		
	0.068																		
	0.082																		
	0.1																		
WVDC	16	25	50	100	16	25	50	100	16	25	50	100	200	16	25	50	100	200	500
SIZE	AU02				AU03				AU05					AU06					

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
PAPER						EMBOSSED							



The Important Information/Disclaimer is incorporated in these specifications by reference and should be reviewed in full before placing any order.

MLCC Gold Termination – AU Series

Capacitance Range (NP0 Dielectric)




PREFERRED SIZES ARE SHADED

SIZE		AU10					AU12					AU13			AU14		
Soldering		Reflow/Epoxy/ Wire Bond*					Reflow/Epoxy/ Wire Bond*					Reflow/Epoxy/ Wire Bond*			Reflow/Epoxy/ Wire Bond*		
Packaging		Paper/Embossed					All Embossed					All Embossed			All Embossed		
(L) Length	mm (in)	3.20 ± 0.20 (0.126 ± 0.008)					4.50 ± 0.30 (0.177 ± 0.012)					4.50 ± 0.30 (0.177 ± 0.012)			5.72 ± 0.25 (0.225 ± 0.010)		
W) Width	mm (in)	2.50 ± 0.20 (0.098 ± 0.008)					3.20 ± 0.20 (0.126 ± 0.008)					6.40 ± 0.40 (0.252 ± 0.016)			6.35 ± 0.25 (0.250 ± 0.010)		
(t) Terminal	mm (in)	0.50 ± 0.25 (0.020 ± 0.010)					0.61 ± 0.36 (0.024 ± 0.014)					0.61 ± 0.36 (0.024 ± 0.014)			0.64 ± 0.39 (0.025 ± 0.015)		
WVDC		25	50	100	200	500	25	50	100	200	500	50	100	200	50	100	200
Cap (pF)	0.5																
	1.0																
	1.2																
	1.5																
	1.8																
	2.2																
	2.7																
	3.3																
	3.9																
	4.7																
	5.6																
	6.8																
	8.2																
	10					J											
	12					J											
	15					J											
	18					J											
	22					J											
	27					J											
	33					J											
	39					J											
	47					J											
	56					J											
	68					J											
	82					J											
	100					J											
	120					J											
	150					J											
	180					J											
	220					J											
	270					J											
	330					J											
	390					M											
	470					M											
	560	J	J	J	J	M											
	680	J	J	J	J	M											
	820	J	J	J	J	M											
	1000	J	J	J	J	M	K	K	K	K	M	M	M	M	M	M	P
	1200	J	J	J	M	M	K	K	K	K	M	M	M	M	M	M	P
	1500	J	J	J	M	M	K	K	K	K	M	M	M	M	M	M	P
	1800	J	J	J	M		K	K	K	K	M	M	M	M	M	M	P
	2200	J	J	J	Q		K	K	K	K	P	M	M	M	M	M	P
	2700	J	J	J	Q		K	K	K	P	Q	M	M	M	M	M	P
	3300	J	J	J			K	K	K	P	Q	M	M	M	M	M	P
	3900	J	J	M			K	K	K	P	Q	M	M	M	M	M	P
	4700	J	J	M			K	K	K	P	Q	M	M	M	M	M	P
	5600	J	J				K	K	M	P	X	M	M	M	M	M	P
	6800	J	J				K	K	M	X		M	M	M	M	M	P
	8200	J	J				K	M	M			M	M		M	M	P
	0.010	J	J				K	M	M			M	M		M	M	P
	0.012	J	J				K	M				M	M		M	M	P
	0.015						M	M				M	M		M	M	Y
	0.018						M	M				P	M		M	M	Y
	0.022						M	M				P			M	Y	Y
	0.027						M	M				P			P	Y	Y
	0.033						M	M				P			P		
	0.039						M	M				P			P		
	0.047						M	M				P			P		
	0.068						M	M							P		
	0.082						M	M							Q		
	0.1														Q		
WVDC		25	50	100	200	500	25	50	100	200	500	50	100	200	50	100	200
SIZE		AU10					AU12					AU13			AU14		

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
PAPER						EMBOSS							



MLCC Gold Termination – AU Series

Capacitance Range (X7R Dielectric)



PREFERRED SIZES ARE SHADED

SIZE		AU02				AU03								AU05								AU06								
Soldering		Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*								Reflow/Epoxy/ Wire Bond*								Reflow/Epoxy/ Wire Bond*								
Packaging		All Paper				All Paper								Paper/Embossed								Paper/Embossed								
(L) Length	mm	1.00 ± 0.10				1.60 ± 0.15								2.01 ± 0.20								3.20 ± 0.20								
	(in.)	(0.040 ± 0.004)				(0.063 ± 0.006)								(0.079 ± 0.008)								(0.126 ± 0.008)								
W) Width	mm	0.50 ± 0.10				0.81 ± 0.15								1.25 ± 0.20								1.60 ± 0.20								
	(in.)	(0.020 ± 0.004)				(0.032 ± 0.006)								(0.049 ± 0.008)								(0.063 ± 0.008)								
(t) Terminal	mm	0.25 ± 0.15				0.35 ± 0.15								0.50 ± 0.25								0.50 ± 0.25								
	(in.)	(0.010 ± 0.006)				(0.014 ± 0.006)								(0.020 ± 0.010)								(0.020 ± 0.010)								
WVDC		10	16	25	50	63	10	16	25	50	100	200	63	10	16	25	50	100	200	63	10	16	25	50	100	200	500			
Cap (pF)	100																													
	150																													
	220				C				G																					
	330				C					G	G	G		J	J	J	J	J	J								K			
	470				C					G	G	G		J	J	J	J	J	J								K			
	680				C					G	G	G		J	J	J	J	J	J								K			
	1000				C					G	G	G		J	J	J	J	J	J								K			
	1500				C					G	G			J	J	J	J	J	J		J	J	J	J	J	J	M			
	2200				C					G	G			J	J	J	J	J	J		J	J	J	J	J	J	M			
	3300			C	C					G	G			J	J	J	J	J	J		J	J	J	J	J	J	M			
	4700			C	C					G	G			J	J	J	J	J	J		J	J	J	J	J	J	M			
	6800		C	C						G	G			J	J	J	J	J	J		J	J	J	J	J	J	P			
Cap (µF)	0.010		C					G		G	G			J	J	J	J	J	J		J	J	J	J	J	J	P			
	0.015		C						G	G				J	J	J	J	J	J		J	J	J	J	J	J				
	0.022	C	C						G	G				J	J	J	J	J	N		J	J	J	J	J	M				
	0.033	C							G	G				J	J	J	J	N			J	J	J	J	J	M				
	0.047							G	G	G				J	J	J	J	N			J	J	J	J	J	J	M			
	0.068							G	G	G				J	J	J	J	N			J	J	J	J	J	P				
	0.10						G	G	G	G				J	J	J	J				J	J	J	J	M	P				
	0.15					G	G							J	J	J	N	N			J	J	J	J	Q					
	0.22					G	G							J	J	N	N	N			J	J	J	J	Q					
	0.33													N	N	N	N	N			J	J	M	P	Q					
	0.47													N	N	N	N	N			M	M	M	P	Q					
	0.68													N	N	N					M	M	Q	Q	Q					
	1.0													N	N	N					M	M		Q	Q					
	1.5																				P	Q	Q							
	2.2															P*					Q	Q	Q							
	3.3																													
	4.7													P*							Q	Q								
	10																				Q*									
	22																													
	47																				Q*									
	100																													
WVDC		10	16	25	50	63	10	16	25	50	100	200	63	10	16	25	50	100	200	63	10	16	25	50	100	200	500			
SIZE			AU02				AU03								AU05								AU06							

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
PAPER						EMBOSSED							




The Important Information/Disclaimer is incorporated in these specifications by reference and should be reviewed in full before placing any order.

MLCC Gold Termination – AU Series

Capacitance Range (X7R Dielectric)



PREFERRED SIZES ARE SHADED

SIZE	AU10							AU12				AU13		AU14					
Soldering	Reflow/Epoxy/ Wire Bond*							Reflow/Epoxy/ Wire Bond*				Reflow/Epoxy/ Wire Bond*		Reflow/Epoxy/ Wire Bond*					
Packaging	Paper/EmbossedU							All Embossed				All Embossed		All Embossed					
(L) Length	mm (in.)	3.20 ± 0.20 (0.126 ± 0.008)						4.50 ± 0.30 (0.177 ± 0.012)				4.50 ± 0.30 (0.177 ± 0.012)		5.72 ± 0.25 (0.225 ± 0.010)					
W) Width	mm (in.)	2.50 ± 0.20 (0.098 ± 0.008)						3.20 ± 0.20 (0.126 ± 0.008)				6.40 ± 0.40 (0.252 ± 0.016)		6.35 ± 0.25 (0.250 ± 0.010)					
(t) Terminal	mm (in.)	0.50 ± 0.25 (0.020 ± 0.010)						0.61 ± 0.36 (0.024 ± 0.014)				0.61 ± 0.36 (0.024 ± 0.014)		0.64 ± 0.39 (0.025 ± 0.015)					
WVDC		10	16	25	50	100	200	500	50	100	200	500	50	100	50	100			
Cap (pF)	100 150 220																		
	330 470 680																		
	1000 1500 2200	J	J	J	J	J	J	M											
	3300 4700 6800	J	J	J	J	J	J	M											
Cap (μF)	0.010 0.015 0.022	J	J	J	J	J	J	M	K	K	K	K	M	M	M	P			
	0.033 0.047 0.068	J	J	J	J	J	J	Q	K	K	K	X	M	M	M	P			
	0.10 0.15 0.22	J	J	J	J	J	M		K	K	K	Z	M	M	M	P			
	0.33 0.47 0.68	J	J	J	J	Q			K	M	X		M	M	M	P			
	1.0 1.5 2.2	N	N		X	Z			M	X			M	P	M	P			
	3.3 4.7 10	X	X	Z	Z	Z			Z	Z			M		M	X			
	22 47 100																		
WVDC		10	16	25	50	100	200	500	50	100	200	500	50	100	50	100			
SIZE	AU10							AU12				AU13		AU14					

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
	PAPER					EMBOSSSED							

MLCC Gold Termination – AU Series



Capacitance Range (X5R Dielectric)

PREFERRED SIZES ARE SHADED

SIZE	AU02					AU03					AU05					AU06					AU10					AU12										
Soldering	Reflow/Epoxy Wire Bond*					Reflow/Epoxy Wire Bond*					Reflow/Epoxy Wire Bond*					Reflow/Epoxy Wire Bond*					Reflow/Epoxy Wire Bond*					Reflow/Epoxy Wire Bond*										
Packaging	All Paper					All Paper					Paper/Embossed					Paper/Embossed					Paper/Embossed					All Embossed										
(L) Length	mm (in.)	1.00 ± 0.10 (0.040 ± 0.004)					1.60 ± 0.15 (0.063 ± 0.006)					2.01 ± 0.20 (0.079 ± 0.008)					3.20 ± 0.20 (0.126 ± 0.008)					3.20 ± 0.20 (0.126 ± 0.008)					4.50 ± 0.30 (0.177 ± 0.012)									
(W) Width	mm (in.)	0.50 ± 0.10 (0.020 ± 0.004)					0.81 ± 0.15 (0.032 ± 0.006)					1.25 ± 0.20 (0.049 ± 0.008)					1.60 ± 0.20 (0.063 ± 0.008)					2.50 ± 0.20 (0.098 ± 0.008)					3.20 ± 0.20 (0.126 ± 0.008)									
(t) Terminal	mm (in.)	0.25 ± 0.15 (0.010 ± 0.006)					0.35 ± 0.15 (0.014 ± 0.006)					0.50 ± 0.25 (0.020 ± 0.010)					0.50 ± 0.25 (0.020 ± 0.010)					0.50 ± 0.25 (0.020 ± 0.010)					0.61 ± 0.36 (0.024 ± 0.014)									
WVDC	4 63 10 16 25 50	4 63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	4 63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50		
Cap (pF)	100 150 220																																			
	330 470 680					C C C																														
	1000 1500 2200					C C C																														
	3300 4700 6800					C C C							G G G																							
Cap (μF)	0.010 0.015 0.022					C C C							G G G																							
	0.033 0.047 0.068					C C C							G G G																							
	0.10 0.15 0.22		C C*			C C							G G																							
	0.33 0.47 0.68		C*										G G																							
	1.0 1.5 2.2												G G																							
	3.3 4.7 10												J* J* J* J*																							
	22 47 100												J* J* J* K*																							
WVDC	4 63 10 16 25 50	4 63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	4 63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50	63 10 16 25 35 50		
SIZE	AU02					AU03					AU05					AU06					AU10					AU12										

* Contact Factory

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
PAPER						EMBOSSSED							

 = *Optional Specifications – Contact Factory

NOTE: Contact factory for non-specified capacitance values


MLCC Gold Termination – AU Series



AU16/AU17/AU18

SIZE		AU16 (0306)					AU17 (0508)					AU18 (0612)				
Packaging		Embossed					Embossed					Embossed				
Length	mm	0.81 ± 0.15					1.27 ± 0.25					1.60 ± 0.25				
	(in.)	(0.032 ± 0.006)					(0.050 ± 0.010)					(0.063 ± 0.010)				
Width	mm	1.60 ± 0.15					2.00 ± 0.25					3.20 ± 0.25				
	(in.)	(0.063 ± 0.006)					(0.080 ± 0.010)					(0.126 ± 0.010)				
Cap Code	WVDC	4	6.3	10	16	25	6.3	10	16	25	50	6.3	10	16	25	50
102	Cap 0.001	A	A	A	A	A	S	S	S	S	V	S	S	S	S	V
222	(µF) .0022	A	A	A	A	A	S	S	S	S	V	S	S	S	S	V
332	0.0033	A	A	A	A	A	S	S	S	S	V	S	S	S	S	V
472	0.0047	A	A	A	A	A	S	S	S	S	V	S	S	S	S	V
682	0.0068	A	A	A	A	A	S	S	S	S	V	S	S	S	S	V
103	0.01	A	A	A	A	A	S	S	S	S	V	S	S	S	S	V
153	0.015	A	A	A	A	A	S	S	S	S	V	S	S	S	S	W
223	0.022	A	A	A	A	A	S	S	S	S	V	S	S	S	S	W
333	0.033	A	A	A	A	A	S	S	S	V	V	S	S	S	S	W
473	0.047	A	A	A	A	A	S	S	S	V	A	S	S	S	S	W
683	0.068	A	A	A	A	A	S	S	S	A	A	S	S	S	V	W
104	0.1	A	A	A	A	A	S	S	V	A	A	S	S	S	V	W
154	0.15	A	A	A	A	A	S	S	V	A	A	S	S	S	W	W
224	0.22	A	A	A	A	A	S	S	A	A	A	S	S	V	W	
334	0.33						V	V	A	A	A	S	S	V		
474	0.47						V	V	A	A	A	S	S	V		
684	0.68						A	A	A	A	A	V	V	W		
105	1	A					A	A	A	A	A	V	V	A		
155	1.5						A	A	A	A	A	W	W			
225	2.2											A	A			
335	3.3											A	A			
475	4.7															
685	6.8															
106	10															

PHYSICAL DIMENSIONS AND PAD LAYOUT




PHYSICAL DIMENSIONS MM (IN.)

	L	W	t
AU16 (0306)	0.81 ± 0.15 (0.032 ± 0.006)	1.60 ± 0.15 (0.063 ± 0.006)	0.13 min. (0.005 min.)
AU17 (0508)	1.27 ± 0.25 (0.050 ± 0.010)	2.00 ± 0.25 (0.080 ± 0.010)	0.13 min. (0.005 min.)
AU18 (0612)	1.60 ± 0.25 (0.063 ± 0.010)	3.20 ± 0.25 (0.126 ± 0.010)	0.13 min. (0.005 min.)

T - See Range Chart for Thickness and Codes

PAD LAYOUT DIMENSIONS MM (IN.)

	A	B	C
AU16 (0306)	0.31 (0.012)	1.52 (0.060)	0.51 (0.020)
AU17 (0508)	0.51 (0.020)	2.03 (0.080)	0.51 (0.020)
AU18 (0612)	0.76 (0.030)	3.05 (0.120)	0.635 (0.025)



Solid = X7R

= X5R

= X7S

mm (in.)	
AU16 (0306)	
Code	Thickness
A	0.56 (0.022)

mm (in.)	
AU16 (0508)	
Code	Thickness
S	0.56 (0.022)
V	0.76 (0.030)
A	1.02 (0.040)

mm (in.)	
AU16 (0612)	
Code	Thickness
S	0.56 (0.022)
V	0.76 (0.030)
W	1.02 (0.040)
A	1.27 (0.050)