

Raychem

**SPECIFICATION
CONTROL DRAWING**

Product name

ECA-0014


Date

18/12/91


Revision

B

**MULTI-PORT PLUG BACKSHELL
1" 4 OUTLETS**



APPLICATIONS



ØD		ØE		ØF MAX
Min.	MAX.	Min.	MAX.	
2.4	6	1.8	4.6	3.7

MAXIMUM QTY OF BRAIDS: 4

- Ø D: Outside diam. of jackets.
Ø E: Outside diam. of braids.
Ø F: Outside diam. of wires.

NOTE: THE VALUES TABLE GIVES GEOMETRICAL GUIDE LINES. HOWEVER PLATING, SHAPE, DIAMETER OF CABLE CAN VARY AND AN INSTALLATION MUST BE DONE TO GARANTEE PROPER RESULT.

NOTES:

1. MATERIAL:

- A) BACKSHELL COPPER ALLOY 172 PER 00-A-533
B) BACKSHELL SCREW STAINLESS STEEL PER 00-S-763, 300 SERIES
C) CLAMP BAR STAINLESS STEEL PER 00-S-766, 300 SERIES
D) TRANSITION ALUMINIUM ALLOY PER 00-A-356
E) CLAMP SCREW STAINLESS STEEL PER 00-S-763, 300 SERIES

2. FINISH:

- A) BACKSHELL CADMIUM PLATED PER 00-P-416
B) BACKSHELL SCREW CADMIUM PLATED PER 00-P-416
C) CLAMP BAR CADMIUM PLATED PER 00-P-416
D) TRANSITION CADMIUM PLATED PER 00-P-416
E) CLAMP SCREW CADMIUM PLATED PER 00-P-416



RAYCHEM PART NUMBER ECA-0014 AND DATE CODE ARE STAMPED APPROXIMATELY AS SHOWN.

TOLERANCES: ±0.5

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Dimensions are in millimeters

DRAWN S BRIENS
Engineering

APPROVED P. CONVERS
Product Manager

REPLACES REV A ECO 3567

APPROVED S BRIENS
Development

APPROVED B. DAUVILLIERS
Quality Assurance

PROJECT NUMBER