

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190020007](#)
Status: **Active**
Description: Avikrimp™ Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Mylar Tape

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Quick Disconnects
Series [19002](#)
Product Name Avikrimp™
Type Quick Disconnect

Physical

Barrel Type Closed
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Insulation Nylon (PA)
Lock to Mating Part None
Material - Metal Brass
Orientation Straight
Packaging Type Adhesive Tape on Reel
Polarized to Mating Part No
Tab Thickness 0.51mm (.020")
Tab Width 4.75mm (.187")
Temperature Range - Operating -65°C to +105°C
Wire Insulation Diameter 3.17mm (.125") max.
Wire Size AWG 18
Wire Size AWG 20
Wire Size AWG 22
Wire Size mm² 0.35 - 0.80

Electrical


CSA LR18689
UL E79133
Voltage - Maximum 300V

Material Info

Old Part Number AA-5267T

Reference - Drawing Numbers

Sales Drawing SD-19002-003



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Halogen-Free
Status**

China RoHS



Not Reviewed

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[19002](#) Series

Use With

[19001-0003](#) , [19001-0005](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
ATP Perishable Tool Kit Used in ATP Presses that Process Product on Tape	0192880028
Mini-Mac™ Applicator	0638852000