




PART NUMBER CODING
SWR25X-NRTC-S__-ST-BA

NUMBER OF POSITIONS
(CONTACTS PER ROW, 02 TO 20)




02 - 05 POSITIONS


06 - 20 POSITIONS



RECOMMENDED PCB LAYOUT





- NOTES:
- 1. INSULATOR MATERIAL: NYLON 66, UL94V-2, COLOR: BEIGE.
 - 2. CONTACT MATERIAL: BRASS.
 - 3. CONTACT PLATING: .000020" MIN. NICKEL UNDERPLATE, PURE TIN, BRIGHT OVERALL.
 - 4. CURRENT RATING: 5 AMPS PER CONTACT.
 - 5. VOLTAGE RATING: 250V AC/DC.
 - 6. INSULATOR RESISTANCE: 1000 MEGOHMS MIN.
 - 7. CONTACT RESISTANCE: 20 MILLIOHMS MAX.
 - 8. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC.
 - 9. OPERATING TEMPERATURE: -25° C TO +85° C.
 - 10. MATES WITH SWH25X SERIES SINGLE ROW HOUSING.



RoHS COMPLIANT

REVISIONS				
REV.	ECO. NO	DESCRIPTION	DATE	BY
A	2237	INITIAL RELEASE	05/23/2011	LH

Part Number	Positions/ Contacts	A		B	
		MM	INCH	MM	INCH
SWR25X-NRTC-S02-ST-BA	02/02	2.54	0.100	5.12	0.202
SWR25X-NRTC-S03-ST-BA	03/03	5.08	0.200	7.66	0.302
SWR25X-NRTC-S04-ST-BA	04/04	7.62	0.300	10.20	0.402
SWR25X-NRTC-S05-ST-BA	05/05	10.16	0.400	12.74	0.502
SWR25X-NRTC-S06-ST-BA	06/06	12.70	0.500	15.30	0.602
SWR25X-NRTC-S07-ST-BA	07/07	15.24	0.600	17.94	0.706
SWR25X-NRTC-S08-ST-BA	08/08	17.78	0.700	20.48	0.806
SWR25X-NRTC-S09-ST-BA	09/09	20.32	0.800	23.02	0.906
SWR25X-NRTC-S10-ST-BA	10/10	22.86	0.900	25.58	1.007
SWR25X-NRTC-S11-ST-BA	11/11	25.40	1.000	28.12	1.107
SWR25X-NRTC-S12-ST-BA	12/12	27.94	1.100	30.68	1.208
SWR25X-NRTC-S13-ST-BA	13/13	30.48	1.200	33.10	1.303
SWR25X-NRTC-S14-ST-BA	14/14	33.02	1.300	35.80	1.409
SWR25X-NRTC-S15-ST-BA	15/15	35.56	1.400	38.34	1.509
SWR25X-NRTC-S16-ST-BA	16/16	38.10	1.500	40.94	1.612
SWR25X-NRTC-S17-ST-BA	17/17	40.64	1.600	43.30	1.705
SWR25X-NRTC-S18-ST-BA	18/18	43.18	1.700	45.90	1.807
SWR25X-NRTC-S19-ST-BA	19/19	45.72	1.800	48.56	1.912
SWR25X-NRTC-S20-ST-BA	20/20	48.26	1.900	50.80	2.000
UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MM[INCHES] TOLERANCES: ANGULAR: X=± 0.3 [.01] .XX=± 0.30 [.012] INTERPRET DIMENSIONS AND TOLERANCING PER: ASME Y14.5M-2009	DRAWN	DATE	NAME		
		05/23/2011	LH		
	THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.			TITLE	
				WAFER 2.54mm[.100"] CC, 1 ROW, ST	
				PART NUMBER	
			SWR25X-NRTC-S_ _-ST-BA		
			SIZE	CAGE CODE	DWG. NO.
			C	54453	11633
			SCALE: 15:1		SHEET 1 OF 1
					REV A