

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS

SERIES KC SWITCHES

ROTARY SWITCHES



FEATURES & BENEFITS

- ▶ 1 to 4 poles
- ▶ 1 to 12 positions
- ▶ No stop option

APPLICATIONS/MARKETS

- ▶ Industrial controls
- ▶ Test & instrumentation
- ▶ Appliance
- ▶ HVAC

SPECIFICATIONS

Ratings:	350 mA @ 125 VAC
	150 mA @ 250 VAC
Life Expectancy:	10,000 cycles typical
Contact Resistance:	25mΩ initial @ 2-4 VDC, 100mA
Dielectric Strength:	1,500 max V rms at sea level
Insulation Resistance:	100MΩ min.
Operating Force:	8.6 N/cm

MATERIALS

Housing, Base, Shaft:	Glass filled nylon
Contact:	Silver plated copper alloy Gold flash over silver plate
Hardware:	Nut-Zinc, nickel plated Lockwasher-Steel, zinc plated Stop ring-Brass, nickel plated



HOW TO ORDER

SERIES KC	MODEL NO. 	ACTUATOR 	ACTUATOR LENGTH 	BUSHING 	TIMING 	TERMINATION 	CONTACT MATERIAL 
	See Model Options Table	A=Flat B=Round D=Slotted	See Actuator Option Chart	01 02*	N=Non-Short S=Shorting	P=PC Pin L=Solder Lug	S F



Example Ordering Number


KC-13-B-7.0-02-N-L-S

* Not available with #10 model.

Specifications subject to change without notice.

KC

GENERAL INFORMATION





MODEL NUMBER OPTIONS

(SP Models)		
Model	Sw. Func.	Terms
10	12-pos.-No stops	A, 1-12
11	ST	A, 2*
12	DT	A, 1,2*
13	3 pos.	A, 1-3*
14	4 pos.	A, 1-4*
15	5 pos.	A, 1-5*
16	6 pos.	A, 1-6*
17	7 pos.	A, 1-7
18	8 pos.	A, 1-8
19	9 pos.	A, 1-9
50	10 pos.	A, 1-10
51	11 pos.	A, 1-11
52	12 pos.	A, 1-12
53	2 pos. -60° index	A, 1,3*
54	2 pos. -90° index	A, 1,4*
55	3 pos. -60° index	A, 1,3,5*
56	3 pos. -90° index	A, 1,4,7
57	4 pos. -60° index	A, 1,3,5,7
58	4 pos. -90° index	A, 1,4,7,10**
59	5 pos. -60° index	A, 1,3,5,7,9
60	6 pos. -60° index	A, 1,3,5,7,9,11

(DP Models)		
Model	Sw. Func.	Terms
20	6-pos.-No stops	A,C,1-12
21	ST	A, C,2,8
22	DT	A,C,1,2,7,8
23	3 pos.	A,C 1-3, 7-9
24	4 pos.	A,C,1-4,7-10
25	5 pos.	A,C,1-5, 7-11
26	6 pos.	A,C,1-12
70	2 pos. 60° index	A,C,1,3,7,9
71	2 pos. 90° index	A,C,1,4,7,10
72	2 pos. 60° index	A,C,1,3,5,7,9,11

* Note: Switches with P terminations (PC pins) have additional terminal no. 9 as switch support only. This terminal is not connected electrically inside switch.

** Note: Standard with stops


All models 30° indexing unless otherwise noted.

(3P Models)		
Model	Sw. Func.	Terms
30	4-pos.-No stops	A,B,C,1-12
31	ST	A,B,C,2,6,10
32	DT	A,B,C,1,2,5,6,9,10
33	3 pos.	A,B,C,1-3,5,7,9-11
34	4 pos.	A,B,C,1-12
80	2 pos. 60° index	A,B,C,1,3,5,7,9,11
81	2 pos. 90° index	A,B,C,1,4,5,8,9,12


(4P Models)		
Model	Sw. Func.	Terms
40	3-pos.-No stops	all terms
41	ST	A,B,C,D,2,5,8,11
42	DT	A,B,C,D,1,2,4,5,7,8,10,11
43	3 pos.	all terms
91	2 pos. 60° index	A,B,C,D,1,3,4,6,7,9,10,12

ACTUATOR OPTIONS


A FLAT



B ROUND



D SLOTTED





Actuator	Available Actuator Lengths (mm)					
A	30.0	38.0	9.5	7.0	10.0	13.0
B	30.0	10.0	7.0			
D	0.0					



*All actuators shown in Pos. 1, fully CCW..

BUSHING OPTIONS

01 STANDARD



02 METRIC





TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS

SERIES KC SWITCHES



ROTARY SWITCHES

SCHEMATICS AND PC MOUNTING



SP 1 POLE, 12 POSITIONS





3P 3 POLE, 4 POSITIONS



DP 2 POLE, 6 POSITION



4P 4 POLE, 3 POSITIONS



TIMING OPTIONS


N= (STD.) Non-shorting – break before make

S = Shorting – make before break


Note: (S) shorting contacts available only with 30° indexing

TERMINATION OPTIONS

P PC PIN



L SOLDER LUG



CONTACT MATERIAL OPTIONS

S = Standard Silver over copper alloy

F = Gold Flash over silver plate over copper alloy

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[KC-43-A-30.0-01-N-P-S](#) [KC-26-A-30.0-01-N-L-S](#) [KC-26-A-30.0-01-N-P-S](#) [KC-52-A-30.0-01-N-L-S](#) [KC-34-A-13.0-01-N-L-S](#) [KC-34-A-30.0-01-N-P-S](#) [KC13B10.001NPF](#) [KC-58-A-30.0-01-N-P-S](#) [KC-34-A-9.5-01-N-P-S](#) [KC-43-A-30.0-01-N-L-S](#) [KC34B10.001NPF](#) [KC34D0.001NPS](#) [KC51A30.001NPS](#) [KC14A9.501NLS](#) [KC1901A](#) [KC34A30.001NLS](#) [KC56A13.001NPF](#) [KC10A30.001NLS](#) [KC10A9.501NPF](#) [KC10B30.001NPS](#) [KC12A10.001NLS](#) [KC13A13.001NPS](#) [KC13A9.501NPS](#) [KC13D0.001NLS](#) [KC14A30.001NPS](#) [KC14A30.001SLF](#) [KC14A38.001NPS](#) [KC14D0.001NLS](#) [KC15A10.001NLS](#) [KC15A10.001NPS](#) [KC15A9.501NPF](#) [KC16A30.001NPS](#) [KC17A7.001NLS](#) [KC17A9.501NPS](#) [KC18A10.001NPF](#) [KC18A9.501NPS](#) [KC19A30.001NPS](#) [KC19B10.001NPS](#) [KC23A13.001NPS](#) [KC24A10.001NLS](#) [KC24A13.001NLS](#) [KC24B30.001SLS](#) [KC25A30.001NLS](#) [KC26A30.001SLS](#) [KC26A38.001NPF](#) [KC26A9.501NLS](#) [KC26A9.501SPS](#) [KC26B10.001NPS](#) [KC26B30.002NPF](#) [KC33A9.501NPS](#) [KC33B7.001NLS](#) [KC34A7.001NPF](#) [KC34A9.501NLS](#) [KC43A9.501SLS](#) [KC50B30.001NPS](#) [KC51A30.001NLS](#) [KC51A7.001NPF](#) [KC52A13.002NPS](#) [KC52A30.001SPS](#) [KC52A38.002NPS](#) [KC52A7.001NPS](#) [KC52A9.502SPF](#) [KC52B30.001NPF](#) [KC53A13.001NPS](#) [KC53A30.002NLS](#) [KC54A10.001NPS](#) [KC58A10.001NPS](#) [KC58A9.501NLS](#) [KC60A30.001NLS](#) [KC52A9.501NPF](#) [KC52A9.501NPS](#) [KC52A9.501SPF](#) [KC52A9.501SPS](#) [KC52B10.001NLS](#) [KC52B10.001NPS](#) [KC52B30.001NPS](#) [KC52B7.001SPS](#) [KC52B7.002NPS](#) [KC53A10.001NLS](#) [KC53A30.001NLS](#) [KC53A7.001NLS](#) [KC53A7.001NPS](#) [KC54A10.001NLS](#) [KC54A10.001NPF](#) [KC54A7.001NLS](#) [KC55A10.001NPS](#) [KC55A30.001NLS](#) [KC55A7.001NPS](#) [KC56A10.001NPF](#) [KC56A30.001NPF](#) [KC56A30.001NPS](#) [KC56A38.001NLS](#) [KC56B10.002NLS](#) [KC57A10.001NLS](#) [KC57B10.001NLS](#) [KC58A10.002NLS](#) [KC58A13.001NLS](#) [KC58A13.001NPS](#) [KC58A30.001NLF](#) [KC58A30.002NPS](#)