



Contact data 06/2	Conditions	Min	Typ	Max	Unit
Contact - No.			06/2		
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			200	V
Switching current	DC or Peak AC			0,5	A
Carry current	DC or Peak AC			1	A

Special Product Data	Conditions	Min	Typ	Max	Unit
Number of contacts			1		
Contact - form			A - NO		
Sensor-resistance				680	mOhm
Housing material LS				Nylon/Polyamid	
Material of float				Polyamid/Nylon	
Case colour				black	
Sealing compound				Polyurethan	
Reach / RoHS conformity				yes	

Environmental data	Conditions	Min	Typ	Max	Unit
Shock				50	g
Vibration	from 10 - 1200 Hz			20	g
Operating temperature		-30		80	°C
Operating temperature		-5		80	°C
Storage temperature		-30		80	°C
Safety class				IP68 until the thread	

Cable specification	Conditions	Min	Typ	Max	Unit
Cable type				round cable	
Cable material				PVC	
Cross section				0.14 sq-mm	

General data	Conditions	Min	Typ	Max	Unit
Mounting advice				over 5m cable, a resistor is recommended.	
Tightening torque				0,5	Nm