

# E1SJA10-20.000M TR

[Click part number to visit Part Number Details page](#)

## REGULATORY COMPLIANCE (Data Sheet downloaded on Feb 28, 2018)


[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.



## ITEM DESCRIPTION

Quartz Crystal Resonator HC49/UP Short 2 Pad Surface Mount (SMD) 3.2mm Height Metal Resistance Weld Seal 20.000MHz  $\pm 15\text{ppm}$  at 25°C,  $\pm 30\text{ppm}$  over -40°C to +85°C 10pF Parallel Resonant

## ELECTRICAL SPECIFICATIONS

|                               |                                                                    |
|-------------------------------|--------------------------------------------------------------------|
| Nominal Frequency             | 20.000MHz                                                          |
| Frequency Tolerance/Stability | $\pm 15\text{ppm}$ at 25°C, $\pm 30\text{ppm}$ over -40°C to +85°C |
| Aging at 25°C                 | $\pm 5\text{ppm/year}$ Maximum                                     |
| Load Capacitance              | 10pF Parallel Resonant                                             |
| Shunt Capacitance             | 7pF Maximum                                                        |
| Equivalent Series Resistance  | 50 Ohms Maximum                                                    |
| Mode of Operation             | AT-Cut Fundamental                                                 |
| Drive Level                   | 1mWatt Maximum                                                     |
| Storage Temperature Range     | -55°C to +125°C                                                    |
| Insulation Resistance         | 500 Megaohms Minimum (Measured at 100Vdc)                          |


## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                               |
|------------------------------|-----------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 1, HBM: 1500V |
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A         |
| Flammability                 | UL94-V0                                       |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C         |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C          |
| Moisture Resistance          | MIL-STD-883, Method 1004                      |
| Moisture Sensitivity         | J-STD-020, MSL1                               |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K          |
| Resistance to Solvents       | MIL-STD-202, Method 215                       |
| Solderability                | MIL-STD-883, Method 2003                      |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B         |
| Vibration                    | MIL-STD-883, Method 2007, Condition A         |

E1SJA10-20.000M TR

[Click part number to visit Part Number Details page](#)


MECHANICAL DIMENSIONS (all dimensions in millimeters)



| LINE | MARKING                           |
|------|-----------------------------------|
| 1    | E20.000M<br>E=Ecliptek Designator |

Suggested Solder Pad Layout

All Dimensions in Millimeters



All Tolerances are ±0.1



# E1SJA10-20.000M TR

## Tape & Reel Dimensions

Quantity Per Reel: 1,000 units

All Dimensions in Millimeters


Compliant to EIA-481



E1SJA10-20.000M TR

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods




High Temperature Infrared/Convection

|                                     |                                                   |
|-------------------------------------|---------------------------------------------------|
| Ts MAX to TL (Ramp-up Rate)         | 3°C/Second Maximum                                |
| Preheat                             |                                                   |
| - Temperature Minimum (Ts MIN)      | 150°C                                             |
| - Temperature Typical (Ts TYP)      | 175°C                                             |
| - Temperature Maximum (Ts MAX)      | 200°C                                             |
| - Time (ts MIN)                     | 60 - 180 Seconds                                  |
| Ramp-up Rate (TL to TP)             | 3°C/Second Maximum                                |
| Time Maintained Above:              |                                                   |
| - Temperature (TL)                  | 217°C                                             |
| - Time (tL)                         | 60 - 150 Seconds                                  |
| Peak Temperature (TP)               | 260°C Maximum for 10 Seconds Maximum              |
| Target Peak Temperature (TP Target) | 250°C +0/-5°C                                     |
| Time within 5°C of actual peak (tp) | 20 - 40 Seconds                                   |
| Ramp-down Rate                      | 6°C/Second Maximum                                |
| Time 25°C to Peak Temperature (t)   | 8 Minutes Maximum                                 |
| Moisture Sensitivity Level          | Level 1                                           |
| Additional Notes                    | Temperatures shown are applied to body of device. |

E1SJA10-20.000M TR

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



Low Temperature Infrared/Convection 245°C

|                                            |                     |                                                        |
|--------------------------------------------|---------------------|--------------------------------------------------------|
| <b>Ts MAX to TL (Ramp-up Rate)</b>         |                     | 5°C/Second Maximum                                     |
| <b>Preheat</b>                             |                     |                                                        |
| - Temperature Minimum (Ts MIN)             | N/A                 |                                                        |
| - Temperature Typical (Ts TYP)             | 150°C               |                                                        |
| - Temperature Maximum (Ts MAX)             | N/A                 |                                                        |
| - Time (ts MIN)                            | 30 - 60 Seconds     |                                                        |
| <b>Ramp-up Rate (TL to TP)</b>             |                     | 5°C/Second Maximum                                     |
| <b>Time Maintained Above:</b>              |                     |                                                        |
| - Temperature (TL)                         | 150°C               |                                                        |
| - Time (tL)                                | 200 Seconds Maximum |                                                        |
| <b>Peak Temperature (TP)</b>               |                     | 245°C Maximum                                          |
| <b>Target Peak Temperature (TP Target)</b> |                     | 245°C Maximum 2 Times / 230°C Maximum 1 Time           |
| <b>Time within 5°C of actual peak (tP)</b> |                     | 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time |
| <b>Ramp-down Rate</b>                      |                     | 5°C/Second Maximum                                     |
| <b>Time 25°C to Peak Temperature (t)</b>   |                     | N/A                                                    |
| <b>Moisture Sensitivity Level</b>          |                     | Level 1                                                |
| <b>Additional Notes</b>                    |                     | Temperatures shown are applied to body of device.      |

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)