


SPECIFICATION	
Mating Cycles	500
Filter type	C
Capacitance	47pF±20%
Working Voltage	100V
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION dB
5	-
10	-
50	-
100	-
500	30dB
1000	35dB



							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, male, Straight 25 Poles, turned solder buckets, tin plated shell with dimples and clinch nuts	Mo?Mslab/ Scale 1.5:1
						Detail.	8-JUL-02	CV			
						Insp.					
						Stand.					
09643217218	M3		33423	06/01/06	JMDR	HARTING EURL F-95972 Paris				TB 0964321721x	Blatt / Page 1 / 1
09643217217	UNC 4-40		31058	8-JUL-02	CV						
Part number	Nut thread		Mod.	Dat.	Name						