



LIGHTING FOREVER

EVERLIGHT ELECTRONICS CO., LTD.

Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T

Features

- . Top View White LEDs
- . Lead frame package with individual 2 pins
- . Wide viewing angle
- . Soldering methods: IR reflow soldering
- . ESD protection
- . Pb-free
- . The product itself will remain within RoHS compliant version.



Descriptions

- . Due to the package design, 45-21 has wide viewing angle, low power consumption and white LEDs are devices which are materialized by combining blue chips and special phosphor. This feature makes the LED ideal for light guide application.

Applications

- . LCD back light
- . Mobile phones
- . Indicators
- . Illuminations
- . Switch Lights

Device Selection Guide







Chip	Emitted Color	Resin Color
Material		
InGaN	White	Water Clear

Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T

Package Outline Dimensions



Recommended soldering pad design

Note: Tolerances unless dimension are $\pm 0.1\text{mm}$, unit = mm.



LIGHTING FOREVER

EVERLIGHT ELECTRONICS CO., LTD.

Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T**Absolute Maximum Ratings (Ta=25°C)**

Parameter	Symbol	Rating	Unit
Reverse Voltage	V _R	5	V
Forward Current	I _F	30	mA
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}	100	mA
Power Dissipation	P _d	110	mW
Electrostatic Discharge(HBM)* ¹	ESD	2000	V
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	-40 ~ +90	°C
Soldering Temperature	Tsol	Reflow Soldering: 260 °C for 10 sec. Hand Soldering: 350 °C for 3 sec.	

Note: The products are sensitive to static electricity and must be carefully taken when handling products.

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	I _V	1420	-----	2250	mcd	I _F =20mA
Viewing Angle	2θ _{1/2}	---	120	---	deg	I _F =20mA
Forward Voltage	V _F	2.70	-----	3.70	V	I _F =20mA
Reverse Current	I _R	---	---	50	μ A	V _R =5V

Notes:

1. Tolerance of Luminous Intensity: ± 11%
2. Tolerance of Forward Voltage: ± 0.05V

**Technical Data Sheet****Top View LEDs****45-21/L2C-W4556W2X1G/2T****Bin Range of Luminous Intensity**

Bin Code	Min.	Max.	Unit	Condition
W2	1420	1800	mcd	I _F =20mA
X1	1800	2250		

Bin Range of Forward Voltage

Group	Bin Code	Min.	Max.	Unit	Condition
G	34	2.70	2.80	V	I _F =20mA
	35	2.80	2.90		
	36	2.90	3.00		
	37	3.00	3.10		
	38	3.10	3.20		
	39	3.20	3.30		
	40	3.30	3.40		
	41	3.40	3.50		
	42	3.50	3.60		
	43	3.60	3.70		

Notes:

- 1.Tolerance of Luminous Intensity: $\pm 11\%$
- 2.Tolerance of Forward Voltage: $\pm 0.05V$



Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T

Bin Range of Chromaticity Coordinates

CCT	Bin Code	CIE_x	CIE_y	CCT	Bin Code	CIE_x	CIE_y
4500K ~5000K	U4	0.3640	0.3830	5000K ~5650K	V4	0.3290	0.3570
		0.3670	0.4000			0.3290	0.3690
		0.3480	0.3850			0.3480	0.3850
		0.3470	0.3720			0.3470	0.3720
	U5	0.3640	0.3830		V5	0.3290	0.3450
		0.3620	0.3720			0.3290	0.3570
		0.3460	0.3590			0.3470	0.3720
		0.3470	0.3720			0.3460	0.3590
	U6	0.3620	0.3720		V6	0.3290	0.3310
		0.3600	0.3570			0.3290	0.3450
		0.3440	0.3440			0.3460	0.3590
		0.3460	0.3590			0.3440	0.3440
				V7	0.3290	0.3310	
					0.3440	0.3440	
					0.3430	0.3310	
					0.3290	0.3200	

Note:


1. Tolerance of the Chromaticity Coordinates: ± 0.01

Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T

The C.I.E. 1931 Chromaticity Diagram









Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T

Typical Electro-Optical Characteristics Curves





EVERLIGHT ELECTRONICS CO., LTD.

LIGHTING FOREVER

Technical Data Sheet

Top View LEDs


45-21/L2C-W4556W2X1G/2T

Label Explanation


CAT: Luminous Intensity Rank

HUE: Chromaticity Coordinates

REF: Forward Voltage Rank



Reel Dimensions



Note: The tolerances unless mentioned are $\pm 0.1\text{mm}$, unit = mm.


Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T


Carrier Tape Dimensions: Loaded Quantity 2000 pcs. Per Reel

Progressive direction



Note: Tolerances unless dimension are $\pm 0.1\text{mm}$, unit = mm.

Moisture Resistant Packaging



**Technical Data Sheet****Top View LEDs****45-21/L2C-W4556W2X1G/2T****Reliability Test Items and Conditions**

The reliability of products shall be satisfied with items listed below.

Confidence level : 90%

LTPD : 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 10 sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	H : +100°C 15min └ 5 min L : -40°C 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H : +100°C 5min └ 10 sec L : -10°C 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	I _F = 20 mA / 25°C	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C/85%RH	1000 Hrs.	22 PCS.	0/1

Technical Data Sheet

Top View LEDs

45-21/L2C-W4556W2X1G/2T

Precautions for Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

2.1 Do not open moisture proof bag before the products are ready to use.

2.2 Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.

2.3 After opening the package: The LED's floor life is 1 year under 30°C or less and 60% RH or less.


If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

Baking treatment : 60±5°C for 24 hours.

3. Soldering Condition

3.1 Pb-free solder temperature profile



3.2 Reflow soldering should not be done more than two times.

3.3 When soldering, do not put stress on the LEDs during heating.


3.4 After soldering, do not warp the circuit board.

Technical Data Sheet**Top View LEDs****45-21/L2C-W4556W2X1G/2T****4. Soldering Iron**

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

**6. Handling Indications**

During processing, mechanical stress on the surface should be minimized as much as possible. Sharp objects of all types should not be used to pierce the sealing compound

EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd,
Tucheng, Taipei 236, Taiwan, R.O.C

Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

<http://www.everlight.com>