

REVISION X

DIMENSIONS ARE IN INCHES			UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$	ANGLES $\pm 2^\circ$			LOW PROFILE TERMINAL ASSEMBLY	TLW-1XX-XX-XXX-X-XX-XXX
TWO PLACE DECIMALS $\pm .01$	FOUR PLACE DECIMALS $\pm .0020$					SHEET 1 OF 3






FIG. 1
(THROUGH HOLE)

NOTES:

- 1.) MAX ALLOWABLE BOW AFTER ASSEMBLY: .005 IN/IN.
- 2.) TERMINAL PUSHOUT FORCE: 2 lbs. MIN.
- 3.) MAX PIN ROTATION IN BODY: 2°.
- 4.) C REPRESENTS A CRITICAL DIMENSION.
- 5.) MAX CUT FLASH: .010.
- 6.) GOLD CONTACT AREA LOCATION FOR G, H, S, L, F, SM, LM, FM, & STL PLATINGS.
- 7.) ORIENTATE PINS TO PREVENT BANDOLIER MARKS FROM SHOWING IN THE POST AREA. (SEE TABLE 2)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

TLW-1XX-XX-XXX-X-XX-XXX

No. OF POSITIONS
-01 THRU -40 (SINGLE)
-01 THRU -36 (DOUBLE)

LEAD STYLE
-01: (RA) SEE FIG. 2
-05: (TH) SEE TABLE 1
-06: (TH) SEE TABLE 1


PLATING SPECIFICATION
-G: GOLD (SPECIFY -G IN TERMINAL SUFFIX -XXX)
-T: TIN (SPECIFY -T IN TERMINAL SUFFIX -XXX)
-H: HEAVY GOLD (SPECIFY -H IN TERMINAL SUFFIX -XXX)
-S: SELECTIVE (SPECIFY -S IN TERMINAL SUFFIX -XXX)
-F: FLASH SELECTIVE (SPECIFY -F IN TERMINAL SUFFIX -XXX)
-L: LIGHT SELECTIVE (SPECIFY -L IN TERMINAL SUFFIX -XXX)
-TM: MATTE TIN (SPECIFY -T IN TERMINAL SUFFIX -XXX)
-SM: SELECTIVE HEAVY GOLD, MATTE TIN TAIL (SPECIFY -S IN TERMINAL SUFFIX -XXX)
-FM: FLASH SELECTIVE GOLD, MATTE TIN TAIL (SPECIFY -F IN TERMINAL SUFFIX -XXX)
-LM: LIGHT SELECTIVE GOLD, MATTE TIN TAIL (SPECIFY -L IN TERMINAL SUFFIX -XXX)
-STL: SELECTIVE GOLD, TIN/LEAD TAIL (SPECIFY -STL IN TERMINAL SUFFIX -XXX) (AVAILABLE IN STRAIGHT THROUGH HOLE VERSION ONLY)

POLARIZING SPECIFICATION
XXX INDICATES POS. TO BE OMITTED
(IDENTIFY POSITION WITH FEET DOWN)


OPTIONS
-BLANK: THROUGH HOLE (SEE FIG 1)
-RA: RIGHT ANGLE (LEAD STYLE -01 ONLY)
(SEE FIG 2)
-LL: TH WITH LOCKING LEADS (SEE FIG 4)
-LA: RA WITH LOCKING LEADS (SEE FIG 3)

ROW SPECIFICATION
-S: SINGLE ROW (USE TLW-XX-S)
-D: DOUBLE ROW (USE TLW-XX-D)

TABLE 1						
LEAD	TERMINAL 1	TERMINAL 2	"L"	"A"	"B"	"C"
-05	T-1S6-21-XXX-2	N/A	.335	.105	.170	.050
-06	T-1S6-18-XXX-2	N/A	.300	.105	.135	.050
-01-S	T-1S6-22-XXX-2	N/A	.495	.230	N/A	.165
-01-D	T-1S6-22-XXX-2	-----	.495	.230	N/A	.165
-01-D	-----	T-1S6-23-XXX-2	.695	.230	N/A	.165



-S: SINGLE



-D: DOUBLE

MATERIAL:
INSULATOR:
LIQUID CRYSTAL POLYMER
COLOR: BLACK

TERMINALS:
PHOSPHOR BRONZE

samtec

EXISPROD/ASSEMBLY/100
TLWASM

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:

M PUFFER 8-18-97

TLW-1XX-XX-XXX-X-XX-XXX
SHEET 1 OF 3