


Data Sheet

Type Number:	6430
Designation IEC:	CR 2430
System:	Li-Manganese dioxide / Organic Electrolyte
UL Recognition:	MH 13654 (N)
Nominal Voltage [V]:	3
Typical Capacity C [mAh]:	280
Load 5.6 kOhm, at 20 °C down to 2.0 V	
Weight, approx [g]:	4
Volume [ccm]:	1,3
Coding:	Manufacturing Month/Year
Temperature Ranges [°C]:	min. max.
Storage:	-55 70
Discharge:	-20 65
Dimensions [mm]:	min. max.
Diameter [A]:	24,2 24,5
Height [B]:	2,7 3
Shoulder Diameter[E]:	
Shoulder Height [C]:	
Segment:	Electronic
Main Applications:	Watch Photo Electronic



Typical Capacities (at 20° C):

Discharge Type:	Load	End Voltage:	2.0 V
Continuous	5600	Ω Time:	560 h
24h/d, 7d/w		Capacity [mAh]:	280
Current [μA]:		Energy [mWh]:	785