

Circuit Structure

30° ± 5°

46.22 ± 1
(1.82 ± .039)

10.2 ± 3
(.402 ± .012)

17 ± 5
(.669 ± .02)

5.7 ± 5
(.224 ± .02)

10 ± 5
(.394 ± .02)

29.4 ± 5
(1.157 ± .02)

20.1 ± 3
(.791 ± .012)

10 ± 5
(.394 ± .02)

8.5 ± 3
(.335 ± .012)

18.4 ± 1
(.016 ± .004)

ø19
(ø.075)

4.5 ± 1
(.177 ± .004)

4.2 ± .05
(.165 ± .002)

ø5 ± 3
(ø.187 ± .012)

M12x0.75

ø12 ± 2
(ø.472 ± .008)

Mount Hole

.4 ± 1
(.016 ± .004)

- Rating: 3A/125VAC; 1.5A/250VAC
- Contact Resistance: 50m Ω max.
- Insulation Resistance: 500V DC 100M Ω min.
- Dielectric Strength: 1000V AC 1 minute

- Circuit: 6P DPDT ON-ON

Mountain Switch

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-0008](#)