




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M8	REVISED PER ECN-22-158830	16JUN2022	RK	MF



8	7	101.19	[3.984]	99.06	[3.900]	39	80	9-103330-0
8	7	98.65	[3.884]	96.52	[3.800]	38	78	8-103330-9
8	7	96.11	[3.784]	93.98	[3.700]	37	76	8-103330-8
8	7	93.57	[3.684]	91.44	[3.600]	36	74	8-103330-7
8	7	91.03	[3.584]	88.9	[3.500]	35	72	8-103330-6
8	7	88.49	[3.484]	86.36	[3.400]	34	70	8-103330-5
8	7	85.95	[3.384]	83.82	[3.300]	33	68	8-103330-4
8	7	83.41	[3.284]	81.28	[3.200]	32	66	8-103330-3
8	7	80.87	[3.184]	78.74	[3.100]	31	64	8-103330-2
8	7	78.33	[3.084]	76.2	[3.000]	30	62	8-103330-1
8	7	75.79	[2.984]	73.66	[2.900]	29	60	8-103330-0
8	7	73.25	[2.884]	71.12	[2.800]	28	58	7-103330-9
8	7	70.71	[2.784]	68.58	[2.700]	27	56	7-103330-8
8	7	68.17	[2.684]	66.04	[2.600]	26	54	7-103330-7
8	7	65.63	[2.584]	63.5	[2.500]	25	52	7-103330-6
8	7	63.09	[2.484]	60.96	[2.400]	24	50	7-103330-5
8	7	60.55	[2.384]	58.42	[2.300]	23	48	7-103330-4
8	7	58.01	[2.284]	55.94	[2.200]	22	46	7-103330-3
8	7	55.47	[2.184]	53.34	[2.100]	21	44	7-103330-2
8	7	52.93	[2.084]	50.8	[2.000]	20	42	7-103330-1
8	7	50.39	[1.984]	48.26	[1.900]	19	40	7-103330-0
8	7	47.85	[1.884]	45.72	[1.800]	18	38	6-103330-9
8	7	45.31	[1.784]	43.18	[1.700]	17	36	6-103330-8
8	7	42.77	[1.684]	40.64	[1.600]	16	34	6-103330-7
8	7	40.23	[1.584]	38.1	[1.500]	15	32	6-103330-6
8	7	37.69	[1.484]	35.56	[1.400]	14	30	6-103330-5
8	7	35.15	[1.384]	33.02	[1.300]	13	28	6-103330-4
8	7	32.61	[1.284]	30.48	[1.200]	12	26	6-103330-3
8	7	30.07	[1.184]	27.94	[1.100]	11	24	6-103330-2
8	7	27.53	[1.084]	25.4	[1.000]	10	22	6-103330-1
8	7	24.99	[.984]	22.86	[.900]	9	20	6-103330-0
8	7	22.45	[.884]	20.32	[.800]	8	18	5-103330-9
8	7	19.91	[.784]	17.78	[.700]	7	16	5-103330-8
8	7	17.37	[.684]	15.24	[.600]	6	14	5-103330-7
8	7	14.83	[.584]	12.7	[.500]	5	12	5-103330-6
8	7	12.29	[.484]	10.16	[.400]	4	10	5-103330-5
8	7	9.75	[.384]	7.62	[.300]	3	8	5-103330-4
8	7	7.21	[.284]	5.08	[.200]	2	6	5-103330-3
8	7	4.67	[.184]	2.54	[.100]	1	4	5-103330-2
8	7	2.13	[.084]	—	—	—	2	5-103330-1

1	ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
2	BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
3	0.00254 [.000100] -0.00508 [.000200] MATTE TIN-LEAD OVER 0.00127 [.000050] NICKEL.
4	0.00254 [.000100] -0.00508 [.000200] BRIGHT TIN OVER 0.00127 [.000050] NICKEL.
5	PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
6	HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK. POSTS: COPPER ALLOY
7	0.00254 [.000100] -0.00508 [.000200] MATTE TIN OVER 0.00127 [.000050] NICKEL.
8	HIGH TEMPERATURE CONFIGURATION.
9	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	Δ_5	Δ_4	101.19 [3.984]	99.06 [3.900]	39	80	4-103330-1
	OBSOLETE	Δ_3	101.19 [3.984]	99.06 [3.900]	39	80	4-103330-0
Δ_9	OBSOLETE	Δ_3	98.65 [3.884]	96.52 [3.800]	38	78	3-103330-9
Δ_9	OBSOLETE	Δ_3	96.11 [3.784]	93.98 [3.700]	37	76	3-103330-8
Δ_9	OBSOLETE	Δ_3	93.57 [3.684]	91.44 [3.600]	36	74	3-103330-7
Δ_9	OBSOLETE	Δ_3	91.03 [3.584]	88.9 [3.500]	35	72	3-103330-6
Δ_9	OBSOLETE	Δ_3	88.49 [3.484]	86.36 [3.400]	34	70	3-103330-5
Δ_9	OBSOLETE	Δ_3	85.95 [3.384]	83.82 [3.300]	33	68	3-103330-4
Δ_9	OBSOLETE	Δ_3	83.41 [3.284]	81.28 [3.200]	32	66	3-103330-3
Δ_9	OBSOLETE	Δ_3	80.87 [3.184]	78.74 [3.100]	31	64	3-103330-2
Δ_9	OBSOLETE	Δ_3	78.33 [3.084]	76.2 [3.000]	30	62	3-103330-1
Δ_9	OBSOLETE	Δ_3	75.79 [2.984]	73.66 [2.900]	29	60	3-103330-0
Δ_9	OBSOLETE	Δ_3	73.25 [2.884]	71.12 [2.800]	28	58	2-103330-9
Δ_9	OBSOLETE	Δ_3	70.71 [2.784]	68.58 [2.700]	27	56	2-103330-8
Δ_9	OBSOLETE	Δ_3	68.17 [2.684]	66.04 [2.600]	26	54	2-103330-7
Δ_9	OBSOLETE	Δ_3	65.63 [2.584]	63.5 [2.500]	25	52	2-103330-6
Δ_9	SUPERSEDED	Δ_3	63.09 [2.484]	60.96 [2.400]	24	50	2-103330-5
Δ_9	OBSOLETE	Δ_3	60.55 [2.384]	58.42 [2.300]	23	48	2-103330-4
Δ_9	OBSOLETE	Δ_3	58.01 [2.284]	55.94 [2.200]	22	46	2-103330-3
Δ_9	SUPERSEDED	Δ_3	55.47 [2.184]	53.34 [2.100]	21	44	2-103330-2
Δ_9	OBSOLETE	Δ_3	52.93 [2.084]	50.8 [2.000]	20	42	2-103330-1
Δ_9	OBSOLETE	Δ_3	50.39 [1.984]	48.26 [1.900]	19	40	2-103330-0
Δ_9	OBSOLETE	Δ_3	47.85 [1.884]	45.72 [1.800]	18	38	1-103330-9
Δ_9	OBSOLETE	Δ_3	45.31 [1.784]	43.18 [1.700]	17	36	1-103330-8
Δ_9	OBSOLETE	Δ_3	42.77 [1.684]	40.64 [1.600]	16	34	1-103330-7
	OBSOLETE	Δ_3	40.23 [1.584]	38.1 [1.500]	15	32	1-103330-6
Δ_9	OBSOLETE	Δ_3	37.69 [1.484]	35.56 [1.400]	14	30	1-103330-5
	OBSOLETE	Δ_3	35.15 [1.384]	33.02 [1.300]	13	28	1-103330-4
Δ_9	SUPERSEDED	Δ_3	32.61 [1.284]	30.48 [1.200]	12	26	1-103330-3
Δ_9	OBSOLETE	Δ_3	30.07 [1.184]	27.94 [1.100]	11	24	1-103330-2
Δ_9	OBSOLETE	Δ_3	27.53 [1.084]	25.4 [1.000]	10	22	1-103330-1
Δ_9	OBSOLETE	Δ_3	24.99 [0.984]	22.86 [0.900]	9	20	1-103330-0
	SUPERSEDED	Δ_3	22.45 [0.884]	20.32 [0.800]	8	18	—103330-9
	SUPERSEDED	Δ_3	19.91 [0.784]	17.78 [0.700]	7	16	—103330-8
Δ_9	OBSOLETE	Δ_3	17.37 [0.684]	15.24 [0.600]	6	14	—103330-7
Δ_9	OBSOLETE	Δ_3	14.83 [0.584]	12.7 [0.500]	5	12	—103330-6
	SUPERSEDED	Δ_3	12.29 [0.484]	10.16 [0.400]	4	10	—103330-5
Δ_9	SUPERSEDED	Δ_3	9.75 [0.384]	7.62 [0.300]	3	8	—103330-4
	SUPERSEDED	Δ_3	7.21 [0.284]	5.08 [0.200]	2	6	—103330-3
	SUPERSEDED	Δ_3	4.67 [0.184]	2.54 [0.100]	1	4	—103330-2
	SUPERSEDED	Δ_3	2.13 [0.084]	—	—	2	—103330-1

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN	190C192					TE Connectivity	
DIMENSIONS: mm [INCHES]						TOLERANCES UNLESS OTHERWISE SPECIFIED: P .010 ± F .010 ± R .010 ± C .010 ± H .010 ± ANGLES ± .013 [.005] FINISH ±		APPROVED B. JOHN KNITTLE		DATE 23NOV92		NAME	
						PRODUCT SPEC		ASSY.HEDR.BRKAWAY.MOD II, DUBL ROW .100X.100 C/L, RHT ANG, WITH .025 SORE POSTS					
MATERIAL 						APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
						WEIGHT —		A1		00779	103330	—	
SEE TABLE						CUSTOMER DRAWING		SCALE		4:1	SHEET	1 OF 1	REV M