




- 1 0.38 μ m[.000015] MIN GOLD ON MATING AREA,
1.27 μ m[.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27 μ m[.000050] MIN NICKEL.
- 2 2.54 μ m[.000100] MIN BRIGHT TIN-LEAD, OVER
1.27 μ m[.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54 μ m[.000100] MIN TIN ON MATING AREA, BOTH OVER
1.27 μ m[.000050] MIN NICKEL.
- 4 0.38 μ m[.000015] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27 μ m[.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5-
3	6	487923-4
5 OBSOLETE	1	487923-3-
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± -		CONTACT, SOLDER TAB, .050 C/L			
	1 PLC ± -		-			
	2 PLC ± 0.13[.005]		-			
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO
PHOSPHOR BRONZE		SEE TABLE	-	A2	00779	C=487923
CUSTOMER DRAWING			SCALE	10:1	SHEET	1 OF 1
			REV	D1		