

Photointerrupter, Ultraminiature DIP type



Absolute maximum ratings (Ta=25°C)

Parameter		Symbol	Limits	Unit
Input (LED)	Forward current	IF	50	mA
	Reverse voltage	VR	5	V
	Power dissipation	PD	80	mW
Output (photo-transistor)	Collector-emitter voltage	VCEO	30	V
	Emitter-collector voltage	VECO	4.5	V
	Collector current	IC	30	mA
	Collector power dissipation	PC	80	mW
	Operating temperature	Topr	-25 to +85	°C
Storage temperature		Tstg	-30 to +85	°C

Applications

DSC(Digital steal camera)
DVC(Digital video camera)
Digital handy phone

Features

- 1) Ultraminiature DIP type.
- 2) Gap 1.2mm.

Electrical and optical characteristics (Ta=25°C)

Parameter		Symbol	Min.	Typ.	Max.	Unit	Conditions
Input characteristics	Forward voltage	VF	—	1.3	1.6	V	IF=50mA
	Reverse current	IR	—	—	10	μA	VR=5V
Output characteristics	Dark current	ICEO	—	—	0.5	μA	VCE=10V
	Peak sensitivity wavelength	λP	—	800	—	nm	—
Transfer characteristics	Collector current	IC	0.95	—	4.95	mA	VCE=5V, IF=20mA
	Collector-emitter saturation voltage	VCE(sat)	—	—	0.4	V	IF=20mA, IC=0.1mA
	Response time	Rise time Fall time	tr tf	10 10	— —	μs μs	VCC=5V, IF=20mA, RL=100Ω
Collector rank	A	IC	0.45	—	2.33	mA	VCE=5V, IF=20mA
	B		0.95	—	4.95		
Infrared light emitter diode	Cut-off frequency	fC	—	1	—	MHz	IF=50mA * Non-coherent Infrared light emitting diode used.
	Peak light emitting wavelength	λP	—	950	—	nm	—
Photo transistor	Response time	tr·tf	—	10	—	μs	VCC=5V, IC=1mA, RL=100Ω * This product is not designed to be protected against electromagnetic wave.
	Maximum sensitivity wavelength	λP	—	800	—	nm	—

Electrical and optical characteristics curves




Fig.1 Relative output current vs. distance (I)




Fig.2 Forward current falloff




Fig.3 Forward current vs. forward voltage




Fig.4 Relative output current vs. distance (II)




Fig.5 Power dissipation / collector power dissipation vs. ambient temperature




Fig.6 Relative output vs. ambient temperature




Fig.7 Collector current vs. forward current




Fig.8 Response time vs. collector current




Fig.9 Dark current vs. ambient temperature




Fig.10 Output characteristics





Fig.11 Response time measurement circuit

Dimensions (Unit : mm)



- Notes:
1. Unspecified tolerance shall be ± 0.2 .
 2. Dimension in parenthesis are show for reference.

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>