

10

9

8

7

6



5

4





3

2

1



RECOMMENDED P.C.B HOLE LAYOUT



NOTES:

1. MATERIAL:

HSG: LCP, GLASS-FILLED, UL94V-0,

COLOR: BLACK

PIN: 0.64MM SQ PIN, COPPER ALLOY

2. PLATING TYPE:

(1) : 0.0254 μ m GOLD FLASH OVER1.25 μ m MIN. NICKEL OVERALL.(2) : 0.025 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(3) : 0.25 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(4) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(5) : 0.75 μ m MIN. GOLD PLATE ON CONTACT AND1.88 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL(6) : 2.50 μ m MIN. TIN OVER 1.25 μ m MIN. NICKEL OVERALL.(7) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND2.50 μ m MIN. TIN ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(8) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND0.05 μ m MIN. GOLD FLASH ON SOLDER TAIL OVER1.25 μ m MIN. NICKEL OVERALL.(9) : 0.05 - 0.25 μ m MIN. GOLD FLASH OVER1.25 μ m MIN. NICKEL OVERALL.

3. PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION

4. THE ABOVE 14 CKT IS FOR ILLUSTRATION PURPOSE ONLY.

5. FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.

6. RECOMMENDED PCB THICKNESS 1.60MM.

7. PRODUCT SPECIFICATION: PS-87920-019

8. WAFER TO BE FLAT WITHIN 0.003mm/mm

9. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION

IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN

BODY IS NOT ACCEPTABLE.

10. PARTS ARE NOT STACKABLE ON 2.54 CENTER

11. CAP TO BE PLACED AS CENTRAL OF PART AS POSSIBLE WITH THE TOP SURFACE FLAT FOR PICK AND PLACE.

12. PACKAGING SPECIFICATION:

TRAY: PK-89990-489

BULK: PK-89990-491

REVISION OF DRAWING MAY BE
CHANGED DURING FINAL RELEASED
FOR PRODUCTION.

ib_frame_A3_P_AM_T
Rev. G 2012/01/11

SEE SHEET 14
EC NO: S2015-1512
DRAWN: RAMAKRISHNA 2015/06/25
CHKD: ATSEE 2015/06/25
APPR: KPRASAD 2015/07/15

DESCRIPTION
REV

QUALITY SYMBOLS

 $F_A=0$ $F_G=0$ $F_P=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± ---	± ---
0 PLACE	±	±

ANGULAR $\pm 3^\circ$
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
KCHO	2004/11/05
CHECKED BY	DATE
PTLIM	2004/12/08
APPROVED BY	DATE
MLONG	2010/09/06

MATERIAL NO.

SEE TABLE

SCALE
NTS

TITLE

DOCUMENT NO.

DESIGN UNITS
METRIC

2.54MM PITCH
DUAL ROW HEADER
SINGLE WAFER, T/H
molex

SD-87914-013

SHEET NO. 1 OF 45

THIRD ANGLE PROJECTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

10		9		8		7		6		5		4		3		2		1						
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																
								A	B	F	M	P												
F	87914-0211	-----	-----	-----	-----	2	-----	1	2.54	----	10.92	5.84	2.79											
	87914-0221	-----	-----	-----	-----	2	-----	1	2.54	----	12.25	7.00	2.96											
	87914-0231	-----	-----	-----	-----	2	-----	1	2.54	----	13.38	6.09	5.00											
	87914-0212	-----	-----	-----	-----	2	-----	2	2.54	----	10.92	5.84	2.79											
	87914-0222	-----	-----	-----	-----	2	-----	2	2.54	----	12.25	7.00	2.96											
	87914-0232	-----	-----	-----	-----	2	-----	2	2.54	----	13.38	6.09	5.00											
E	87914-0213	-----	-----	-----	-----	2	-----	3	2.54	----	10.92	5.84	2.79											
	87914-0223	-----	-----	-----	-----	2	-----	3	2.54	----	12.25	7.00	2.96											
	87914-0233	-----	-----	-----	-----	2	-----	3	2.54	----	13.38	6.09	5.00											
	87914-0214	-----	-----	-----	-----	2	-----	4	2.54	----	10.92	5.84	2.79											
D	87914-0224	-----	-----	-----	-----	2	-----	4	2.54	----	12.25	7.00	2.96											
	87914-0234	-----	-----	-----	-----	2	-----	4	2.54	----	13.38	6.09	5.00											
	87914-0215	-----	-----	-----	-----	2	-----	5	2.54	----	10.92	5.84	2.79											
	87914-0225	-----	-----	-----	-----	2	-----	5	2.54	----	12.25	7.00	2.96											
	87914-0235	-----	-----	-----	-----	2	-----	5	2.54	----	13.38	6.09	5.00											
	87914-0216	-----	-----	-----	-----	2	-----	6	2.54	----	10.92	5.84	2.79											
C	87914-0226	-----	-----	-----	-----	2	-----	6	2.54	----	12.25	7.00	2.96											
	87914-0236	-----	-----	-----	-----	2	-----	6	2.54	----	13.38	6.09	5.00											
B																								
A	SEE SHEET 14		EC NO: S2015-1512		DRAWN: MRAMAKRI SHINA 2015/06/25		CHKD: ATSEE 2015/06/25		APPR: KPRASAD 2015/07/15		REV		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
																	MM ONLY		NTS		METRIC			
																	DRAWN BY		DATE		TITLE			
																	KCHO		2004/11/05		2.54MM PITCH			
																	CHECKED BY		DATE		DUAL ROW HEADER			
																	PTL IM		2004/12/08		SINGLE WAFER, T/H			
																	APPROVED BY		DATE					
																	MLONG		2010/09/06					
																	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
																	SEE TABLE		SD-87914-013		2 OF 45			
																SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
fb_frame_A3_P_AM_T		9		8		7		6		5		4		3		2		1						

	10	9	8	7	6	5	4	3	2	1																																																																																																																																				
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																																																																					
									A	B	F	M	P																																																																																																																																	
F	87914-0411	-----	-----	-----	-----	4	-----	1	5.08	2.54	10.92	5.84	2.79	F																																																																																																																																
	87914-0421	-----	-----	-----	-----	4	-----	1	5.08	2.54	12.25	7.00	2.96																																																																																																																																	
	87914-0431	-----	-----	-----	-----	4	-----	1	5.08	2.54	13.38	6.09	5.00																																																																																																																																	
	87914-0412	-----	-----	-----	-----	4	-----	2	5.08	2.54	10.92	5.84	2.79																																																																																																																																	
	87914-0422	-----	-----	-----	-----	4	-----	2	5.08	2.54	12.25	7.00	2.96																																																																																																																																	
	87914-0432	-----	-----	-----	-----	4	-----	2	5.08	2.54	13.38	6.09	5.00																																																																																																																																	
E	87914-0413	-----	-----	-----	-----	4	-----	3	5.08	2.54	10.92	5.84	2.79	E																																																																																																																																
	87914-0423	-----	-----	-----	-----	4	-----	3	5.08	2.54	12.25	7.00	2.96																																																																																																																																	
	87914-0433	-----	-----	-----	-----	4	-----	3	5.08	2.54	13.38	6.09	5.00																																																																																																																																	
	87914-0414	-----	-----	-----	-----	4	-----	4	5.08	2.54	10.92	5.84	2.79																																																																																																																																	
	87914-0424	-----	-----	-----	-----	4	-----	4	5.08	2.54	12.25	7.00	2.96																																																																																																																																	
	87914-0434	-----	-----	-----	-----	4	-----	4	5.08	2.54	13.38	6.09	5.00																																																																																																																																	
D	87914-0415	-----	-----	-----	-----	4	-----	5	5.08	2.54	10.92	5.84	2.79	D																																																																																																																																
	87914-0425	-----	-----	-----	-----	4	-----	5	5.08	2.54	12.25	7.00	2.96																																																																																																																																	
	87914-0435	-----	-----	-----	-----	4	-----	5	5.08	2.54	13.38	6.09	5.00																																																																																																																																	
	87914-0416	-----	-----	-----	-----	4	-----	6	5.08	2.54	10.92	5.84	2.79																																																																																																																																	
	87914-0426	-----	-----	-----	-----	4	-----	6	5.08	2.54	12.25	7.00	2.96																																																																																																																																	
	87914-0436	-----	-----	-----	-----	4	-----	6	5.08	2.54	13.38	6.09	5.00																																																																																																																																	
C														C																																																																																																																																
B														B																																																																																																																																
<table> <tr> <td rowspan="5">SEE SHEET 14</td><td colspan="2">EC NO: S2015-1512</td><td rowspan="5">DESCRIPTION</td><td rowspan="5">REV</td><td rowspan="5">QUALITY SYMBOLS</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE</td><td>SCALE</td><td>DESIGN UNITS</td><td colspan="2" rowspan="10">THIRD ANGLE PROJECTION</td></tr> <tr> <td colspan="5">DRAWN:IRAWAKRISHNA 2015/06/25</td><td colspan="3"></td><td colspan="2">MM ONLY</td><td>NTS</td><td>METRIC</td></tr> <tr> <td colspan="5">CHKD:ATSEE 2015/06/25</td><td colspan="3"></td><td>DRAWN BY</td><td>DATE</td><td colspan="4" rowspan="3">TITLE</td></tr> <tr> <td colspan="5">APPR:KPRASAD 2015/07/15</td><td colspan="3"></td><td>CHECKED BY</td><td>DATE</td></tr> <tr> <td colspan="5"></td><td colspan="3"></td><td>PTLIM</td><td>2004/12/08</td></tr> <tr> <td rowspan="5">A</td><td colspan="2"></td><td rowspan="5"></td><td rowspan="5"></td><td rowspan="5"></td><td colspan="3"></td><td>APPROVED BY</td><td>DATE</td><td colspan="4" rowspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr> <tr> <td colspan="5"></td><td colspan="3"></td><td>MLONG</td><td>2010/09/06</td></tr> <tr> <td colspan="5"></td><td colspan="3"></td><td colspan="2">MATERIAL NO.</td><td colspan="4" rowspan="3">moLEX</td></tr> <tr> <td colspan="5"></td><td colspan="3"></td><td colspan="6">SEE TABLE</td></tr> <tr> <td colspan="5"></td><td colspan="3"></td><td>SIZE</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr> </table>															SEE SHEET 14	EC NO: S2015-1512		DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		DRAWN:IRAWAKRISHNA 2015/06/25								MM ONLY		NTS	METRIC	CHKD:ATSEE 2015/06/25								DRAWN BY	DATE	TITLE				APPR:KPRASAD 2015/07/15								CHECKED BY	DATE									PTLIM	2004/12/08	A									APPROVED BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H												MLONG	2010/09/06									MATERIAL NO.		moLEX												SEE TABLE														SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
SEE SHEET 14	EC NO: S2015-1512		DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION																																																																																																																																	
	DRAWN:IRAWAKRISHNA 2015/06/25								MM ONLY		NTS	METRIC																																																																																																																																		
	CHKD:ATSEE 2015/06/25								DRAWN BY	DATE	TITLE																																																																																																																																			
	APPR:KPRASAD 2015/07/15								CHECKED BY	DATE																																																																																																																																				
									PTLIM	2004/12/08																																																																																																																																				
A									APPROVED BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																																																																																			
									MLONG	2010/09/06																																																																																																																																				
									MATERIAL NO.		moLEX																																																																																																																																			
									SEE TABLE																																																																																																																																					
									SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																																																				
	fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1																																																																																																																																				

[illegible]

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
	87914-0009	-----	-----	-----	-----	6	----	1	7.62	5.08	18.84	13.25	3.30							
	87914-0642	-----	-----	-----	-----	6	----	2	7.62	5.08	18.84	13.25	3.30							
	87914-0643	-----	-----	-----	-----	6	----	3	7.62	5.08	18.84	13.25	3.30							
	87914-0644	-----	-----	-----	-----	6	----	4	7.62	5.08	18.84	13.25	3.30							
	87914-0645	-----	-----	-----	-----	6	----	5	7.62	5.08	18.84	13.25	3.30							
	87914-0646	-----	-----	-----	-----	6	----	6	7.62	5.08	18.84	13.25	3.30							
E																				
D																				
C																				
B																				
A																				
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1										

SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	
		 =0  =0  =0			MM ONLY		NTS	METRIC		
			4 PLACES	mm	INCH	DRAWN BY	DATE	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		
			3 PLACES			CHECKED BY	DATE			
			2 PLACES			PTL IM	2004/12/08			
			1 PLACE			APPROVED BY	DATE			
		0 PLACE			MLONG	2010/09/06				
		ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.			SHEET NO. 5 OF 45
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-87914-013			
		SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

										10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION						F														
	A	B	F	M	P	G	E																						
	87914-0811	-----	-----	-----	-----	8		-----	1	10.16	7.62	10.92	5.84	2.79	----	D													
	87914-0821	-----	-----	-----	-----	8	-----	1	10.16	7.62	12.25	7.00	2.96	----	C														
	87914-0831	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.38	6.09	5.00	----		B													
	87914-0812	-----	-----	-----	-----	8	-----	2	10.16	7.62	10.92	5.84	2.79	----	A														
	87914-0822	-----	-----	-----	-----	8	-----	2	10.16	7.62	12.25	7.00	2.96	----		O													
	87914-0832	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.38	6.09	5.00	----	A														
	87914-0813	-----	-----	-----	-----	8	-----	3	10.16	7.62	10.92	5.84	2.79	----		B													
	87914-0823	-----	-----	-----	-----	8	-----	3	10.16	7.62	12.25	7.00	2.96	----	A														
	87914-0833	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----		O													
	87914-0814	-----	-----	-----	-----	8	-----	4	10.16	7.62	10.92	5.84	2.79	----	A														
	87914-0824	-----	-----	-----	-----	8	-----	4	10.16	7.62	12.25	7.00	2.96	----		O													
	87914-0834	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----	A														
	87914-0815	-----	-----	-----	-----	8	-----	5	10.16	7.62	10.92	5.84	2.79	----		B													
	87914-0825	-----	-----	-----	-----	8	-----	5	10.16	7.62	12.25	7.00	2.96	----	A														
	87914-0835	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.38	6.09	5.00	----		O													
	87914-0816	-----	-----	-----	-----	8	-----	6	10.16	7.62	10.92	5.84	2.79	----	A														
	87914-0826	-----	-----	-----	-----	8	-----	6	10.16	7.62	12.25	7.00	2.96	----		O													
	87914-0836	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.38	6.09	5.00	----	A														
	87914-0807	-----	-----	-----	-----	8	2,3,4,5,6,8	6	10.16	7.62	21.75	16.51	2.95	----		B													
															O														
																A													
															O														
																A													
															O														
																A													
															O														
																A													
															O														
																A													
															O														
																A													
															O														
																A													
															O														
																A													
															O														
																A													
															O														

10		9		8		7		6		5		4		3		2		1		
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
	A	B	F	M	P															
	87914-0841	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.51	8.75	2.47							
	87914-0842	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.51	8.75	2.47							
	87914-0843	-----	-----	-----	-----	8	-----	3	10.16	7.62	13.51	8.75	2.47							
	87914-0844	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.51	8.75	2.47							
	87914-0845	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.51	8.75	2.47							
	87914-0005	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.51	8.75	2.47							
E	87914-0108	-----	-----	-----	-----	8	-----	6	10.16	7.62	16.50	11.11	3.10							
	87914-0847	-----	-----	-----	-----	8	-----	6	10.16	7.62	26.70	20.76	3.65							
D																				
C																				
										</										

	10		9		8		7		6		5		4		3		2		1		
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	PART NO. FOR BULK PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
										A	B	F	M	P	G						
F	87914-1011	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	10.92	5.84	2.79	----						
	87914-1021	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	12.25	7.00	2.96	----						
	87914-1031	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	13.38	6.09	5.00	----						
E	87914-1012	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	10.92	5.84	2.79	----						
	87914-1022	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	12.25	7.00	2.96	----						
	87914-1032	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	13.38	6.09	5.00	----						
E	87914-1013	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	10.92	5.84	2.79	----						
	87914-1023	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	12.25	7.00	2.96	----						
	87914-1033	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	13.38	6.09	5.00	----						
D	87914-1014	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	10.92	5.84	2.79	----						
	87914-1024	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	12.25	7.00	2.96	----						
	87914-1034	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	13.38	6.09	5.00	----						
D	87914-1015	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	10.92	5.84	2.79	----						
	87914-1025	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	12.25	7.00	2.96	----						
	87914-1035	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	13.38	6.09	5.00	----						
C	87914-1016	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	10.92	5.84	2.79	----						
	87914-1026	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	12.25	7.00	2.96	----						
	87914-1036	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	13.38	6.09	5.00	----						
C	87914-0001	-----	-----	-----	-----	-----	10	-----	7	12.70	10.16	12.07	5.97	3.81	----						
	-----	-----	-----	-----	-----	87914-1037	10	9	4	12.70	10.16	10.92	5.84	2.79	----						
B																					

A	SEE SHEET 14 EC NO: S2015-1512 DRAWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_B=0 F_C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex	DOCUMENT NO. SD-87914-013	SHEET NO. 8 OF 45	A			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	ANGULAR ± 3 °	MATERIAL NO.	SEE TABLE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
									4 PLACES	± ---					± ---	DRAWN BY KCHO	DATE 2004/11/05
									3 PLACES	± ---					± ---	CHECKED BY PTLIM	DATE 2004/12/08
									2 PLACES	± 0.20					± ---	APPROVED BY MLONG	DATE 2010/09/06
1 PLACE	± ---	± ---															
0 PLACE	±	±															
fb_frame_A3_P_AM_T Rev. G 2012/01/11																	
9	8	7	6	5	4	3	2	1									

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P	E	D	C	B	A									
	87914-1211	-----	-----	-----	-----						12	-----	1	15.24	12.70	10.92	5.84	2.79	
	-----	87914-1291	-----	-----	-----	12	-----	9	15.24	12.70	10.92	5.84	2.79						
	87914-1221	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.25	7.00	2.96						
	87914-1231	-----	-----	-----	-----	12	-----	1	15.24	12.70	13.38	6.09	5.00						
	87914-1212	-----	-----	-----	-----	12	-----	2	15.24	12.70	10.92	5.84	2.79						
	87914-1222	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.25	7.00	2.96						
	87914-1232	-----	-----	-----	-----	12	-----	2	15.24	12.70	13.38	6.09	5.00						
	87914-1213	-----	-----	-----	-----	12	-----	3	15.24	12.70	10.92	5.84	2.79						
	87914-1223	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.25	7.00	2.96						
	87914-1233	-----	-----	-----	-----	12	-----	3	15.24	12.70	13.38	6.09	5.00						
	87914-1214	-----	-----	-----	-----	12	-----	4	15.24	12.70	10.92	5.84	2.79						
	87914-1224	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.25	7.00	2.96						
	87914-1234	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.38	6.09	5.00						
	87914-1215	-----	-----	-----	-----	12	-----	5	15.24	12.70	10.92	5.84	2.79						
	87914-1225	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.25	7.00	2.96						
	87914-1235	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.38	6.09	5.00						
	87914-1216	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79						
	87914-1226	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96						
	87914-1236	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.38	6.09	5.00						

10		9		8		7		6		5		4		3		2		1							
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																	
								A	B	F	M	P													
F	87914-1251	-----	-----	-----	-----	12	-----	1	15.24	12.70	18.40	13.08	3.03												
	87914-1252	-----	-----	-----	-----	12	-----	2	15.24	12.70	18.40	13.08	3.03												
	87914-1253	-----	-----	-----	-----	12	-----	3	15.24	12.70	18.40	13.08	3.03												
	87914-1254	-----	-----	-----	-----	12	-----	4	15.24	12.70	18.40	13.08	3.03												
	87914-1255	-----	-----	-----	-----	12	-----	5	15.24	12.70	18.40	13.08	3.03												
	87914-1256	-----	-----	-----	-----	12	-----	6	15.24	12.70	18.40	13.08	3.03												
E	87914-1241	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.50	6.95	3.26												
	87914-1242	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.50	6.95	3.26												
	87914-1243	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.50	6.95	3.26												
	87914-1244	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.50	6.95	3.26												
	87914-1245	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.50	6.95	3.26												
	87914-1246	-----	-----	-----	-----	12	-----	6	15.24	12.70	29.26	23.32	3.65												
D																									
C																									
B																									
A																									
SEE SHEET 14		EC NO: S2015-1512		DRWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
D15																		MM ONLY		NTS		METRIC		⊙	
																		DRAWN BY		DATE		TITLE			
																		KCHO		2004/11/05		2.54MM PITCH			
																		CHECKED BY		DATE		DUAL ROW HEADER			
																		PTL IM		2004/12/08		SINGLE WAFER, T/H			
																		APPROVED BY		DATE		molex			
																		MLONG		2010/09/06					
																		MATERIAL NO.		DOCUMENT NO.		SD-87914-013		SHEET NO.	
																		SEE TABLE				10 OF 45			
																		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
																		A3							

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-1411	-----	-----	-----	-----	14	-----	1	17.78	15.24	10.92	5.84	2.79						
	87914-1421	-----	-----	-----	-----	14	-----	1	17.78	15.24	12.25	7.00	2.96						
	87914-1431	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.38	6.09	5.00						
	87914-1412	-----	-----	-----	-----	14	-----	2	17.78	15.24	10.92	5.84	2.79						
	87914-1422	-----	-----	-----	-----	14	-----	2	17.78	15.24	12.25	7.00	2.96						
	87914-1432	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.38	6.09	5.00						
E	87914-1413	-----	-----	-----	-----	14	-----	3	17.78	15.24	10.92	5.84	2.79	E					
	87914-1423	-----	-----	-----	-----	14	-----	3	17.78	15.24	12.25	7.00	2.96						
	87914-1433	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.38	6.09	5.00						
	87914-1414	-----	-----	-----	-----	14	-----	4	17.78	15.24	10.92	5.84	2.79						
	87914-1424	-----	-----	-----	-----	14	-----	4	17.78	15.24	12.25	7.00	2.96						
	87914-1434	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.38	6.09	5.00						
D	87914-1415	-----	-----	-----	-----	14	-----	5	17.78	15.24	10.92	5.84	2.79	D					
	87914-1425	-----	-----	-----	-----	14	-----	5	17.78	15.24	12.25	7.00	2.96						
	87914-1435	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.38	6.09	5.00						
	87914-1416	-----	-----	-----	-----	14	-----	6	17.78	15.24	10.92	5.84	2.79						
	87914-1426	-----	-----	-----	-----	14	-----	6	17.78	15.24	12.25	7.00	2.96						
	87914-1436	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.38	6.09	5.00						
C	87914-0007	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.42	8.08	3.05	C					

	10		9	8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
									A	B	F	M	P						
	87914-1441	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.42	8.08	3.05						
	87914-1442	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.42	8.08	3.05						
	87914-1443	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.42	8.08	3.05						
	87914-1444	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.42	8.08	3.05	E					
	87914-1445	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.42	8.08	3.05						
D															D				
C															C				
B															B				
A															A				
SEE SHEET 14 EC NO: S2015-1512 DRWN:HRAMAKR/SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV DESCRIPTION QUALITY SYMBOLS ▽F=0 ▽F=0 ▽F=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 SCALE NTS DESIGN UNITS METRIC THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex MATERIAL NO. SEE TABLE DOCUMENT NO. SD-87914-013 SHEET NO. 12 OF 45 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
fb_frame_A3_P_AM_T	9	8	7	6	5	4	3	2	1										

10		9		8		7		6		5		4		3		2		1		
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
								A	B	F	M	P								
F	87914-1611	-----	-----	-----	-----	16	-----	1	20.32	17.78	10.92	5.84	2.79							F
	87914-1621	-----	-----	-----	-----	16	-----	1	20.32	17.78	12.25	7.00	2.96							
	87914-1631	-----	-----	-----	-----	16	-----	1	20.32	17.78	13.38	6.09	5.00							
	87914-1612	-----	-----	-----	-----	16	-----	2	20.32	17.78	10.92	5.84	2.79							
	87914-1622	-----	-----	-----	-----	16	-----	2	20.32	17.78	12.25	7.00	2.96							
	87914-1632	-----	-----	-----	-----	16	-----	2	20.32	17.78	13.38	6.09	5.00							
E	87914-1613	-----	-----	-----	-----	16	-----	3	20.32	17.78	10.92	5.84	2.79							E
	87914-1623	-----	-----	-----	-----	16	-----	3	20.32	17.78	12.25	7.00	2.96							
	87914-1633	-----	-----	-----	-----	16	-----	3	20.32	17.78	13.38	6.09	5.00							
	87914-1614	-----	-----	-----	-----	16	-----	4	20.32	17.78	10.92	5.84	2.79							
	87914-1624	-----	-----	-----	-----	16	-----	4	20.32	17.78	12.25	7.00	2.96							
	87914-1634	-----	-----	-----	-----	16	-----	4	20.32	17.78	13.38	6.09	5.00							
D	87914-1615	-----	-----	-----	-----	16	-----	5	20.32	17.78	10.92	5.84	2.79							D
	87914-1625	-----	-----	-----	-----	16	-----	5	20.32	17.78	12.25	7.00	2.96							
	87914-1635	-----	-----	-----	-----	16	-----	5	20.32	17.78	13.38	6.09	5.00							
	87914-1616	-----	-----	-----	-----	16	-----	6	20.32	17.78	10.92	5.84	2.79							
	87914-1626	-----	-----	-----	-----	16	-----	6	20.32	17.78	12.25	7.00	2.96							
	87914-1636	-----	-----	-----	-----	16	-----	6	20.32	17.78	13.38	6.09	5.00							
C	87914-1600	-----	-----	-----	-----	16	-----	6	20.32	17.78	9.49	4.50	2.70							C
	87914-1637	-----	-----	-----	-----	16	-----	6	20.32	17.78	15.79	10.45	3.05							
B																				B

10		9		8		7		6		5		4		3		2		1			
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION													
								A	B	F	M	P	G								
F	87914-1811	-----	-----	-----	-----	18	----	1	22.86	20.32	10.92	5.84	2.79	----	F						
	87914-1821	-----	-----	-----	-----	18	----	1	22.86	20.32	12.25	7.00	2.96	----							
	87914-1831	-----	-----	-----	-----	18	----	1	22.86	20.32	13.38	6.09	5.00	----							
	87914-1812	-----	-----	-----	-----	18	----	2	22.86	20.32	10.92	5.84	2.79	----	E						
	87914-1822	-----	-----	-----	-----	18	----	2	22.86	20.32	12.25	7.00	2.96	----							
	87914-1832	-----	-----	-----	-----	18	----	2	22.86	20.32	13.38	6.09	5.00	----							
E	87914-1813	-----	-----	-----	-----	18	----	3	22.86	20.32	10.92	5.84	2.79	----	E						
	87914-1823	-----	-----	-----	-----	18	----	3	22.86	20.32	12.25	7.00	2.96	----							
	87914-1833	-----	-----	-----	-----	18	----	3	22.86	20.32	13.38	6.09	5.00	----							
	87914-1814	-----	-----	-----	-----	18	----	4	22.86	20.32	10.92	5.84	2.79	----	D						
	87914-1824	-----	-----	-----	-----	18	----	4	22.86	20.32	12.25	7.00	2.96	----							
	87914-1834	-----	-----	-----	-----	18	----	4	22.86	20.32	13.38	6.09	5.00	----							
D	87914-1815	-----	-----	-----	-----	18	----	5	22.86	20.32	10.92	5.84	2.79	----	D						
	87914-1825	-----	-----	-----	-----	18	----	5	22.86	20.32	12.25	7.00	2.96	----							
	87914-1835	-----	-----	-----	-----	18	----	5	22.86	20.32	13.38	6.09	5.00	----							
	87914-1816	-----	-----	-----	-----	18	----	6	22.86	20.32	10.92	5.84	2.79	----	C						
	87914-1826	-----	-----	-----	-----	18	----	6	22.86	20.32	12.25	7.00	2.96	----							
	87914-1836	-----	-----	-----	-----	18	----	6	22.86	20.32	13.38	6.09	5.00	----							
C	-----	-----	87914-1807	-----	-----	18	----	6	22.86	20.32	17.02	11.05	3.68	18.02	C						
															B						
B															B						
															A						
ADD P/N: 87914-1807		EC NO: SZ015-1512		DRW:N/PRAMAKRI SHNA 2015/06/25		CHK:D/ATSEE 2015/06/25		APPR:K/PRASAD 2015/07/15		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION	
REV		DESCRIPTION		F ₀ =0		F ₀ =0		F ₀ =0		4 PLACES ± --- ± ---		3 PLACES ± --- ± ---		2 PLACES ± 0.20 ± ---		1 PLACE ± --- ± ---		0 PLACE ± ±		ANGULAR ± 3 °	
D15																					

[illegible]

10		9		8		7		6		5		4		3		2		1								
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																		
								A	B	F	M	P														
F	87914-2211	-----	-----	-----	-----	22	-----	1	27.94	25.40	10.92	5.84	2.79													
	87914-2221	-----	-----	-----	-----	22	-----	1	27.94	25.40	12.25	7.00	2.96													
	87914-2231	-----	-----	-----	-----	22	-----	1	27.94	25.40	13.38	6.09	5.00													
	87914-2212	-----	-----	-----	-----	22	-----	2	27.94	25.40	10.92	5.84	2.79													
	87914-2222	-----	-----	-----	-----	22	-----	2	27.94	25.40	12.25	7.00	2.96													
	87914-2232	-----	-----	-----	-----	22	-----	2	27.94	25.40	13.38	6.09	5.00													
E	87914-2213	-----	-----	-----	-----	22	-----	3	27.94	25.40	10.92	5.84	2.79													
	87914-2223	-----	-----	-----	-----	22	-----	3	27.94	25.40	12.25	7.00	2.96													
	87914-2233	-----	-----	-----	-----	22	-----	3	27.94	25.40	13.38	6.09	5.00													
	87914-2214	-----	-----	-----	-----	22	-----	4	27.94	25.40	10.92	5.84	2.79													
D	87914-2224	-----	-----	-----	-----	22	-----	4	27.94	25.40	12.25	7.00	2.96													
	87914-2234	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.38	6.09	5.00													
	87914-2215	-----	-----	-----	-----	22	-----	5	27.94	25.40	10.92	5.84	2.79													
	87914-2225	-----	-----	-----	-----	22	-----	5	27.94	25.40	12.25	7.00	2.96													
	87914-2235	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.38	6.09	5.00													
	87914-2216	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79													
C	87914-2226	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96													
	87914-2236	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.38	6.09	5.00													
B																										
A	SEE SHEET 14		EC NO: S2015-1512		DRAWN: MRAKRI SHINA 2015/06/25		CHKD: ATSEE 2015/06/25		APPR: KPRASAD 2015/07/15		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
																			MM ONLY		NTS		METRIC			
																			DRAWN BY		DATE		TITLE			
																			KCHO		2004/11/05		2.54MM PITCH			
																			CHECKED BY		DATE		DUAL ROW HEADER			
																			PTL IM		2004/12/08		SINGLE WAFER, T/H			
																			APPROVED BY		DATE					
																			MLONG		2010/09/06					
																			MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
																			SEE TABLE		SD-87914-013		16 OF 45			
																		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
A3																										
D15																										
fb_frame_A3_P_AM_T																										
Rev. G 2012/01/11																										

10		9		8		7		6		5		4		3		2		1																																																				
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																														
								A	B	F	M	P																																																										
F	87914-2411	-----	-----	-----	-----	24	----	1	30.48	27.94	10.92	5.84	2.79																																																									
	87914-2421	-----	-----	-----	-----	24	----	1	30.48	27.94	12.25	7.00	2.96																																																									
	87914-2431	-----	-----	-----	-----	24	----	1	30.48	27.94	13.38	6.09	5.00																																																									
	87914-2412	-----	-----	-----	-----	24	----	2	30.48	27.94	10.92	5.84	2.79																																																									
	87914-2422	-----	-----	-----	-----	24	----	2	30.48	27.94	12.25	7.00	2.96																																																									
	87914-2432	-----	-----	-----	-----	24	----	2	30.48	27.94	13.38	6.09	5.00																																																									
E	87914-2413	-----	-----	-----	-----	24	----	3	30.48	27.94	10.92	5.84	2.79																																																									
	87914-2423	-----	-----	-----	-----	24	----	3	30.48	27.94	12.25	7.00	2.96																																																									
	87914-2433	-----	-----	-----	-----	24	----	3	30.48	27.94	13.38	6.09	5.00																																																									
	87914-2414	-----	-----	-----	-----	24	----	4	30.48	27.94	10.92	5.84	2.79																																																									
	87914-2424	-----	-----	-----	-----	24	----	4	30.48	27.94	12.25	7.00	2.96																																																									
	87914-2434	-----	-----	-----	-----	24	----	4	30.48	27.94	13.38	6.09	5.00																																																									
D	87914-2415	-----	-----	-----	-----	24	----	5	30.48	27.94	10.92	5.84	2.79																																																									
	87914-2425	-----	-----	-----	-----	24	----	5	30.48	27.94	12.25	7.00	2.96																																																									
	87914-2435	-----	-----	-----	-----	24	----	5	30.48	27.94	13.38	6.09	5.00																																																									
	87914-2416	-----	-----	-----	-----	24	----	6	30.48	27.94	10.92	5.84	2.79																																																									
	87914-2426	-----	-----	-----	-----	24	----	6	30.48	27.94	12.25	7.00	2.96																																																									
	87914-2436	-----	-----	-----	-----	24	----	6	30.48	27.94	13.38	6.09	5.00																																																									
C																																																																						
B																																																																						
A	<table><tr><td rowspan="5">SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15</td><td rowspan="5">DESCRIPTION REV</td><td rowspan="5">QUALITY SYMBOLS F=0 F=0 F=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="4">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>± ---</td><td>± ---</td><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td>± 0.20</td><td>± ---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td></tr><tr><td>± ---</td><td>± ---</td><td>MATERIAL NO.</td><td>DOCUMENT NO.</td></tr><tr><td colspan="2">ANGULAR ± 3 °</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td>SHEET NO. 17 OF 45</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																		SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15	DESCRIPTION REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08	± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06	± ---	± ---	MATERIAL NO.	DOCUMENT NO.	ANGULAR ± 3 °		SEE TABLE		SD-87914-013		SHEET NO. 17 OF 45	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15	DESCRIPTION REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																												
				4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																													
					± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08																																																														
					± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06																																																														
					± ---	± ---	MATERIAL NO.	DOCUMENT NO.																																																														
	ANGULAR ± 3 °		SEE TABLE		SD-87914-013		SHEET NO. 17 OF 45																																																															
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																		
	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1																																																											

	10		9		8		7		6		5		4		3		2		1																																																																				
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																														
									A	B	F	M	P																																																																										
F	87914-2611	-----	-----	-----	-----	26	-----	1	33.02	30.48	10.92	5.84	2.79	F																																																																									
	87914-2621	-----	-----	-----	-----	26	-----	1	33.02	30.48	12.25	7.00	2.96																																																																										
	87914-2631	-----	-----	-----	-----	26	-----	1	33.02	30.48	13.38	6.09	5.00																																																																										
	87914-2612	-----	-----	-----	-----	26	-----	2	33.02	30.48	10.92	5.84	2.79																																																																										
	87914-2622	-----	-----	-----	-----	26	-----	2	33.02	30.48	12.25	7.00	2.96																																																																										
E	87914-2632	-----	-----	-----	-----	26	-----	2	33.02	30.48	13.38	6.09	5.00	E																																																																									
	87914-2613	-----	-----	-----	-----	26	-----	3	33.02	30.48	10.92	5.84	2.79																																																																										
	87914-2623	-----	-----	-----	-----	26	-----	3	33.02	30.48	12.25	7.00	2.96																																																																										
	87914-2633	-----	-----	-----	-----	26	-----	3	33.02	30.48	13.38	6.09	5.00																																																																										
	87914-2614	-----	-----	-----	-----	26	-----	4	33.02	30.48	10.92	5.84	2.79																																																																										
D	87914-2624	-----	-----	-----	-----	26	-----	4	33.02	30.48	12.25	7.00	2.96	D																																																																									
	87914-2634	-----	-----	-----	-----	26	-----	4	33.02	30.48	13.38	6.09	5.00																																																																										
	87914-2615	-----	-----	-----	-----	26	-----	5	33.02	30.48	10.92	5.84	2.79																																																																										
	87914-2625	-----	-----	-----	-----	26	-----	5	33.02	30.48	12.25	7.00	2.96																																																																										
	87914-2635	-----	-----	-----	-----	26	-----	5	33.02	30.48	13.38	6.09	5.00																																																																										
C	87914-2616	-----	-----	-----	-----	26	-----	6	33.02	30.48	10.92	5.84	2.79	C																																																																									
	87914-2626	-----	-----	-----	-----	26	-----	6	33.02	30.48	12.25	7.00	2.96																																																																										
	87914-2636	-----	-----	-----	-----	26	-----	6	33.02	30.48	13.38	6.09	5.00																																																																										
B														B																																																																									
A														A																																																																									
<table><tr><td rowspan="5">SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15</td><td rowspan="5">DESCRIPTION REV</td><td>QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">$\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$</td><td></td><td></td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td></td><td></td><td>CHECKED BY PTLIM</td><td>DATE 2004/12/08</td></tr><tr><td></td><td></td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td><td colspan="4" rowspan="2">molex</td></tr><tr><td></td><td></td><td colspan="2">MATERIAL NO.</td><td>DOCUMENT NO.</td><td>SHEET NO.</td></tr><tr><td>D15</td><td></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td colspan="2">18 OF 45</td></tr><tr><td colspan="2"></td><td>SIZE A3</td><td colspan="17">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																				SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		$\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$			DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H						CHECKED BY PTLIM	DATE 2004/12/08			APPROVED BY MLONG	DATE 2010/09/06	molex						MATERIAL NO.		DOCUMENT NO.	SHEET NO.	D15		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		18 OF 45				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																														
		$\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$			DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																																
					CHECKED BY PTLIM	DATE 2004/12/08																																																																																	
					APPROVED BY MLONG	DATE 2010/09/06	molex																																																																																
					MATERIAL NO.						DOCUMENT NO.	SHEET NO.																																																																											
D15		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		18 OF 45																																																																															
		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																				
fb_frame_A3_P_AM_T Rev. G 2012/01/11	9		8		7		6		5		4		3		2		1																																																																						

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-2811	-----	-----	-----	-----	28	----	1	35.56	33.02	10.92	5.84	2.79						
	87914-2821	-----	-----	-----	-----	28	----	1	35.56	33.02	12.25	7.00	2.96						
	87914-2831	-----	-----	-----	-----	28	----	1	35.56	33.02	13.38	6.09	5.00						
	87914-2812	-----	-----	-----	-----	28	----	2	35.56	33.02	10.92	5.84	2.79						
	87914-2822	-----	-----	-----	-----	28	----	2	35.56	33.02	12.25	7.00	2.96						
	87914-2832	-----	-----	-----	-----	28	----	2	35.56	33.02	13.38	6.09	5.00						
E	87914-2813	-----	-----	-----	-----	28	----	3	35.56	33.02	10.92	5.84	2.79						
	87914-2823	-----	-----	-----	-----	28	----	3	35.56	33.02	12.25	7.00	2.96						
	87914-2833	-----	-----	-----	-----	28	----	3	35.56	33.02	13.38	6.09	5.00						
D	87914-2814	-----	-----	-----	-----	28	----	4	35.56	33.02	10.92	5.84	2.79						
	87914-2824	-----	-----	-----	-----	28	----	4	35.56	33.02	12.25	7.00	2.96						
	87914-2834	-----	-----	-----	-----	28	----	4	35.56	33.02	13.38	6.09	5.00						
	87914-2815	-----	-----	-----	-----	28	----	5	35.56	33.02	10.92	5.84	2.79						
C	87914-2825	-----	-----	-----	-----	28	----	5	35.56	33.02	12.25	7.00	2.96						
	87914-2835	-----	-----	-----	-----	28	----	5	35.56	33.02	13.38	6.09	5.00						
	87914-2816	-----	-----	-----	-----	28	----	6	35.56	33.02	10.92	5.84	2.79						
	87914-2826	-----	-----	-----	-----	28	----	6	35.56	33.02	12.25	7.00	2.96						
B	87914-2836	-----	-----	-----	-----	28	----	6	35.56	33.02	13.38	6.09	5.00						
A																			

SEE SHEET 14 EC NO: S2015-1512 DRAWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE		
		3 PLACES	± ---	± ---	CHECKED BY	DATE			
		2 PLACES	± 0.20	± ---	PTL IM	2004/12/08			
		1 PLACE	± ---	± ---	APPROVED BY	DATE			
		0 PLACE	±	±	MLONG	2010/09/06			
		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		19 OF 45	
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-3211	-----	-----	-----	-----	32	-----	1	40.64	38.10	10.92	5.84	2.79						
	87914-3221	-----	-----	-----	-----	32	-----	1	40.64	38.10	12.25	7.00	2.96						
	87914-3231	-----	-----	-----	-----	32	-----	1	40.64	38.10	13.38	6.09	5.00						
	87914-3212	-----	-----	-----	-----	32	-----	2	40.64	38.10	10.92	5.84	2.79						
	87914-3222	-----	-----	-----	-----	32	-----	2	40.64	38.10	12.25	7.00	2.96						
	87914-3232	-----	-----	-----	-----	32	-----	2	40.64	38.10	13.38	6.09	5.00						
E	87914-3213	-----	-----	-----	-----	32	-----	3	40.64	38.10	10.92	5.84	2.79						
	87914-3223	-----	-----	-----	-----	32	-----	3	40.64	38.10	12.25	7.00	2.96						
	87914-3233	-----	-----	-----	-----	32	-----	3	40.64	38.10	13.38	6.09	5.00						
	87914-3214	-----	-----	-----	-----	32	-----	4	40.64	38.10	10.92	5.84	2.79						
	87914-3224	-----	-----	-----	-----	32	-----	4	40.64	38.10	12.25	7.00	2.96						
	87914-3234	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.38	6.09	5.00						
	D	87914-3215	-----	-----	-----	-----	32	-----	5	40.64	38.10	10.92	5.84	2.79					
87914-3225		-----	-----	-----	-----	32	-----	5	40.64	38.10	12.25	7.00	2.96						
87914-3235		-----	-----	-----	-----	32	-----	5	40.64	38.10	13.38	6.09	5.00						
	87914-3216	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79						
	87914-3226	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96						
	87914-3236	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.38	6.09	5.00						
C																			
B																			
A	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAVAKR SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 21 OF 45		
	D15							SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	D							
F	87914-3411	-----	-----	-----	-----	34	-----	1	43.18	40.64	10.92	5.84	2.79							F
	87914-3421	-----	-----	-----	-----	34	-----	1	43.18	40.64	12.25	7.00	2.96							
	87914-3431	-----	-----	-----	-----	34	-----	1	43.18	40.64	13.38	6.09	5.00							
	87914-3412	-----	-----	-----	-----	34	-----	2	43.18	40.64	10.92	5.84	2.79							
	87914-3422	-----	-----	-----	-----	34	-----	2	43.18	40.64	12.25	7.00	2.96							
	87914-3432	-----	-----	-----	-----	34	-----	2	43.18	40.64	13.38	6.09	5.00							
E	87914-3413	-----	-----	-----	-----	34	-----	3	43.18	40.64	10.92	5.84	2.79							E
	87914-3423	-----	-----	-----	-----	34	-----	3	43.18	40.64	12.25	7.00	2.96							
	87914-3433	-----	-----	-----	-----	34	-----	3	43.18	40.64	13.38	6.09	5.00							
	87914-3414	-----	-----	-----	-----	34	-----	4	43.18	40.64	10.92	5.84	2.79							
	87914-3424	-----	-----	-----	-----	34	-----	4	43.18	40.64	12.25	7.00	2.96							
	87914-3434	-----	-----	-----	-----	34	-----	4	43.18	40.64	13.38	6.09	5.00							
D	87914-3415	-----	-----	-----	-----	34	-----	5	43.18	40.64	10.92	5.84	2.79							D
	87914-3425	-----	-----	-----	-----	34	-----	5	43.18	40.64	12.25	7.00	2.96							
	87914-3435	-----	-----	-----	-----	34	-----	5	43.18	40.64	13.38	6.09	5.00							
	87914-3416	-----	-----	-----	-----	34	-----	6	43.18	40.64	10.92	5.84	2.79							
	87914-3426	-----	-----	-----	-----	34	-----	6	43.18	40.64	12.25	7.00	2.96							
	87914-3436	-----	-----	-----	-----	34	-----	6	43.18	40.64	13.38	6.09	5.00							
C																				C
B																				B
A									QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		A	
	SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV								F _A =0		mm INCH		DRAWN BY DATE		TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
									F _B =0				KCHO 2004/11/05							
									F _C =0				CHECKED BY DATE							
													PTLIM 2004/12/08							
													APPROVED BY DATE							
					MLONG 2010/09/06															
					MATERIAL NO.		DOCUMENT NO.		SHEET NO.											
					SEE TABLE		SD-87914-013		22 OF 45											
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											

10		9		8		7		6		5		4		3		2		1																																									
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																			
								A	B	F	M	P																																															
F	87914-3811	-----	-----	-----	-----	38	----	1	48.26	45.72	10.92	5.84	2.79																																														
	87914-3821	-----	-----	-----	-----	38	----	1	48.26	45.72	12.25	7.00	2.96																																														
	87914-3831	-----	-----	-----	-----	38	----	1	48.26	45.72	13.38	6.09	5.00																																														
	87914-3812	-----	-----	-----	-----	38	----	2	48.26	45.72	10.92	5.84	2.79																																														
	87914-3822	-----	-----	-----	-----	38	----	2	48.26	45.72	12.25	7.00	2.96																																														
	87914-3832	-----	-----	-----	-----	38	----	2	48.26	45.72	13.38	6.09	5.00																																														
E	87914-3813	-----	-----	-----	-----	38	----	3	48.26	45.72	10.92	5.84	2.79																																														
	87914-3823	-----	-----	-----	-----	38	----	3	48.26	45.72	12.25	7.00	2.96																																														
	87914-3833	-----	-----	-----	-----	38	----	3	48.26	45.72	13.38	6.09	5.00																																														
	87914-3814	-----	-----	-----	-----	38	----	4	48.26	45.72	10.92	5.84	2.79																																														
	87914-3824	-----	-----	-----	-----	38	----	4	48.26	45.72	12.25	7.00	2.96																																														
	87914-3834	-----	-----	-----	-----	38	----	4	48.26	45.72	13.38	6.09	5.00																																														
D	87914-3815	-----	-----	-----	-----	38	----	5	48.26	45.72	10.92	5.84	2.79																																														
	87914-3825	-----	-----	-----	-----	38	----	5	48.26	45.72	12.25	7.00	2.96																																														
	87914-3835	-----	-----	-----	-----	38	----	5	48.26	45.72	13.38	6.09	5.00																																														
	87914-3816	-----	-----	-----	-----	38	----	6	48.26	45.72	10.92	5.84	2.79																																														
	87914-3826	-----	-----	-----	-----	38	----	6	48.26	45.72	12.25	7.00	2.96																																														
	87914-3836	-----	-----	-----	-----	38	----	6	48.26	45.72	13.38	6.09	5.00																																														
C																																																											
B																																																											
A	<table><tr><td rowspan="5">SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV D15</td><td rowspan="5">QUALITY SYMBOLS =0 =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="4">mm INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="4">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td></tr><tr><td colspan="2">MATERIAL NO.</td><td>DOCUMENT NO.</td><td>SHEET NO. 24 OF 45</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="12">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																		SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				CHECKED BY PTL IM	DATE 2004/12/08	APPROVED BY MLONG	DATE 2010/09/06	MATERIAL NO.		DOCUMENT NO.	SHEET NO. 24 OF 45	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																		
			4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																				
					CHECKED BY PTL IM	DATE 2004/12/08																																																					
					APPROVED BY MLONG	DATE 2010/09/06																																																					
					MATERIAL NO.						DOCUMENT NO.	SHEET NO. 24 OF 45																																															
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																							
	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1																																																

10		9		8		7		6		5		4		3		2		1				
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION														
								A	B	F	M	P										
F	87914-4211	-----	-----	-----	-----	42	----	1	53.34	50.80	10.92	5.84	2.79									
	87914-4221	-----	-----	-----	-----	42	----	1	53.34	50.80	12.25	7.00	2.96									
	87914-4212	-----	-----	-----	-----	42	----	2	53.34	50.80	10.92	5.84	2.79									
	87914-4222	-----	-----	-----	-----	42	----	2	53.34	50.80	12.25	7.00	2.96									
	87914-4213	-----	-----	-----	-----	42	----	3	53.34	50.80	10.92	5.84	2.79									
	87914-4223	-----	-----	-----	-----	42	----	3	53.34	50.80	12.25	7.00	2.96									
E	87914-4214	-----	-----	-----	-----	42	----	4	53.34	50.80	10.92	5.84	2.79									
	87914-4224	-----	-----	-----	-----	42	----	4	53.34	50.80	12.25	7.00	2.96									
	87914-4215	-----	-----	-----	-----	42	----	5	53.34	50.80	10.92	5.84	2.79									
	87914-4225	-----	-----	-----	-----	42	----	5	53.34	50.80	12.25	7.00	2.96									
D	87914-4216	-----	-----	-----	-----	42	----	6	53.34	50.80	10.92	5.84	2.79									
	87914-4226	-----	-----	-----	-----	42	----	6	53.34	50.80	12.25	7.00	2.96									
C																						
B																						
A	SEE SHEET 14		EC NO: S2015-1512		DRWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
															MM ONLY		NTS		METRIC			
															DRAWN BY		DATE		TITLE			
															KCHO		2004/11/05		2.54MM PITCH			
															CHECKED BY		DATE		DUAL ROW HEADER			
															PTL IM		2004/12/08		SINGLE WAFER, T/H			
															APPROVED BY		DATE					
															MLONG		2010/09/06					
															MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
															SEE TABLE		SD-87914-013				26 OF 45	
														SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
														A3								
								</														

	10		9		8		7		6		5		4		3		2		1																																																
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																										
									A	B	F	M	P																																																						
F	87914-4411	-----	-----	-----	-----	44	-----	1	55.88	53.34	10.92	5.84	2.79																																																						
	87914-4421	-----	-----	-----	-----	44	-----	1	55.88	53.34	12.25	7.00	2.96																																																						
	87914-4412	-----	-----	-----	-----	44	-----	2	55.88	53.34	10.92	5.84	2.79																																																						
	87914-4422	-----	-----	-----	-----	44	-----	2	55.88	53.34	12.25	7.00	2.96																																																						
	87914-4413	-----	-----	-----	-----	44	-----	3	55.88	53.34	10.92	5.84	2.79																																																						
	87914-4423	-----	-----	-----	-----	44	-----	3	55.88	53.34	12.25	7.00	2.96																																																						
E	87914-4414	-----	-----	-----	-----	44	-----	4	55.88	53.34	10.92	5.84	2.79																																																						
	87914-4424	-----	-----	-----	-----	44	-----	4	55.88	53.34	12.25	7.00	2.96																																																						
	87914-4415	-----	-----	-----	-----	44	-----	5	55.88	53.34	10.92	5.84	2.79																																																						
	87914-4425	-----	-----	-----	-----	44	-----	5	55.88	53.34	12.25	7.00	2.96																																																						
	87914-4416	-----	-----	-----	-----	44	-----	6	55.88	53.34	10.92	5.84	2.79																																																						
	87914-4426	-----	-----	-----	-----	44	-----	6	55.88	53.34	12.25	7.00	2.96																																																						
D																																																																			
C																																																																			
B																																																																			
A																																																																			
<table><tr><td rowspan="5">SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15</td><td rowspan="5">QUALITY SYMBOLS =0 =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY PTLIM</td><td>DATE 2004/12/08</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td><td colspan="4" rowspan="2">DOCUMENT NO. SD-87914-013</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td colspan="2">MATERIAL NO.</td><td colspan="2">SHEET NO. 27 OF 45</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																					SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				4 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08	3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06	DOCUMENT NO. SD-87914-013				2 PLACES	± 0.20	± ---	MATERIAL NO.		SHEET NO. 27 OF 45		1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																											
			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																												
		4 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08																																																													
		3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06	DOCUMENT NO. SD-87914-013																																																												
		2 PLACES	± 0.20	± ---	MATERIAL NO.						SHEET NO. 27 OF 45																																																								
1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																														

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-4611	-----	-----	-----	-----	46	----	1	58.42	55.88	10.92	5.84	2.79						
	87914-4621	-----	-----	-----	-----	46	----	1	58.42	55.88	12.25	7.00	2.96						
	87914-4612	-----	-----	-----	-----	46	----	2	58.42	55.88	10.92	5.84	2.79						
	87914-4622	-----	-----	-----	-----	46	----	2	58.42	55.88	12.25	7.00	2.96						
	87914-4613	-----	-----	-----	-----	46	----	3	58.42	55.88	10.92	5.84	2.79						
	87914-4623	-----	-----	-----	-----	46	----	3	58.42	55.88	12.25	7.00	2.96						
E	87914-4614	-----	-----	-----	-----	46	----	4	58.42	55.88	10.92	5.84	2.79						
	87914-4624	-----	-----	-----	-----	46	----	4	58.42	55.88	12.25	7.00	2.96						
	87914-4615	-----	-----	-----	-----	46	----	5	58.42	55.88	10.92	5.84	2.79						
	87914-4625	-----	-----	-----	-----	46	----	5	58.42	55.88	12.25	7.00	2.96						
	87914-4616	-----	-----	-----	-----	46	----	6	58.42	55.88	10.92	5.84	2.79						
	87914-4626	-----	-----	-----	-----	46	----	6	58.42	55.88	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15							QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
											MM ONLY		NTS	METRIC					
										mm INCH	DRAWN BY DATE	TITLE							
									4 PLACES ± --- ± ---	KCHO 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex								
									3 PLACES ± --- ± ---	CHECKED BY DATE									
									2 PLACES ± 0.20 ± ---	PTL IM 2004/12/08									
									1 PLACE ± --- ± ---	APPROVED BY DATE									
									0 PLACE ± ±	MLONG 2010/09/06									
									ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.	SHEET NO.						
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9																	

	10		9		8		7		6		5		4		3		2		1																																								
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																		
									A	B	F	M	P																																														
F	87914-4811	-----	-----	-----	-----	48	----	1	60.96	58.42	10.92	5.84	2.79			F																																											
	87914-4821	-----	-----	-----	-----	48	----	1	60.96	58.42	12.25	7.00	2.96																																														
	87914-4812	-----	-----	-----	-----	48	----	2	60.96	58.42	10.92	5.84	2.79																																														
	87914-4822	-----	-----	-----	-----	48	----	2	60.96	58.42	12.25	7.00	2.96																																														
	87914-4813	-----	-----	-----	-----	48	----	3	60.96	58.42	10.92	5.84	2.79																																														
	87914-4823	-----	-----	-----	-----	48	----	3	60.96	58.42	12.25	7.00	2.96																																														
E	87914-4814	-----	-----	-----	-----	48	----	4	60.96	58.42	10.92	5.84	2.79			E																																											
	87914-4824	-----	-----	-----	-----	48	----	4	60.96	58.42	12.25	7.00	2.96																																														
	87914-4815	-----	-----	-----	-----	48	----	5	60.96	58.42	10.92	5.84	2.79																																														
	87914-4825	-----	-----	-----	-----	48	----	5	60.96	58.42	12.25	7.00	2.96																																														
	87914-4816	-----	-----	-----	-----	48	----	6	60.96	58.42	10.92	5.84	2.79																																														
	87914-4826	-----	-----	-----	-----	48	----	6	60.96	58.42	12.25	7.00	2.96																																														
D																D																																											
C														C																																													
B														B																																													
A	SEE SHEET 14 EC NO: S2015-1512 DRAWN:MRAWAKR / SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV DESCRIPTION								QUALITY SYMBOLS $\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$		GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table>				mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.20	± ---	1 PLACE	± ---	± ---	0 PLACE	±	±	DIMENSION STYLE MM ONLY <table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>KCHO</td><td>2004/11/05</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>PTL IM</td><td>2004/12/08</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>MLONG</td><td>2010/09/06</td></tr></table>		DRAWN BY	DATE	KCHO	2004/11/05	CHECKED BY	DATE	PTL IM	2004/12/08	APPROVED BY	DATE	MLONG	2010/09/06	SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-87914-013		SHEET NO. 29 OF 45	
		mm	INCH																																																								
	4 PLACES	± ---	± ---																																																								
	3 PLACES	± ---	± ---																																																								
	2 PLACES	± 0.20	± ---																																																								
	1 PLACE	± ---	± ---																																																								
	0 PLACE	±	±																																																								
	DRAWN BY	DATE																																																									
	KCHO	2004/11/05																																																									
	CHECKED BY	DATE																																																									
PTL IM	2004/12/08																																																										
APPROVED BY	DATE																																																										
MLONG	2010/09/06																																																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																															

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
--------------------------------------	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-5011	-----	-----	-----	-----	50	-----	1	63.50	60.96	10.92	5.84	2.79						
	87914-5021	-----	-----	-----	-----	50	-----	1	63.50	60.96	12.25	7.00	2.96						
	87914-5012	-----	-----	-----	-----	50	-----	2	63.50	60.96	10.92	5.84	2.79						
	87914-5022	-----	-----	-----	-----	50	-----	2	63.50	60.96	12.25	7.00	2.96						
	87914-5013	-----	-----	-----	-----	50	-----	3	63.50	60.96	10.92	5.84	2.79						
E	87914-5023	-----	-----	-----	-----	50	-----	3	63.50	60.96	12.25	7.00	2.96						
	87914-5014	-----	-----	-----	-----	50	-----	4	63.50	60.96	10.92	5.84	2.79						
	87914-5024	-----	-----	-----	-----	50	-----	4	63.50	60.96	12.25	7.00	2.96						
	87914-5015	-----	-----	-----	-----	50	-----	5	63.50	60.96	10.92	5.84	2.79						
	87914-5025	-----	-----	-----	-----	50	-----	5	63.50	60.96	12.25	7.00	2.96						
D	87914-5016	-----	-----	-----	-----	50	-----	6	63.50	60.96	10.92	5.84	2.79						
	87914-5026	-----	-----	-----	-----	50	-----	6	63.50	60.96	12.25	7.00	2.96						
	87914-0002	-----	-----	-----	-----	50	-----	8	63.50	60.96	18.54	11.58	4.47						
C																			
B																			
A																			

SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
			± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08					
			± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06					
			± ---	± ---	MATERIAL NO.	DOCUMENT NO.					
			±	±	SEE TABLE						SD-87914-013
		ANGULAR ± 3 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
F	87914-5211	-----	-----	-----	-----	52	----	1	66.04	63.50	10.92	5,84	2.79	F						
	87914-5221	-----	-----	-----	-----	52	----	1	66.04	63.50	12.25	7.00	2.96							
	87914-5212	-----	-----	-----	-----	52	----	2	66.04	63.50	10.92	5,84	2.79							
	87914-5222	-----	-----	-----	-----	52	----	2	66.04	63.50	12.25	7.00	2.96							
	87914-5213	-----	-----	-----	-----	52	----	3	66.04	63.50	10.92	5,84	2.79							
	87914-5223	-----	-----	-----	-----	52	----	3	66.04	63.50	12.25	7.00	2.96							
E	87914-5214	-----	-----	-----	-----	52	----	4	66.04	63.50	10.92	5,84	2.79	E						
	87914-5224	-----	-----	-----	-----	52	----	4	66.04	63.50	12.25	7.00	2.96							
	87914-5215	-----	-----	-----	-----	52	----	5	66.04	63.50	10.92	5,84	2.79							
	87914-5225	-----	-----	-----	-----	52	----	5	66.04	63.50	12.25	7.00	2.96							
	87914-5216	-----	-----	-----	-----	52	----	6	66.04	63.50	10.92	5,84	2.79							
	87914-5226	-----	-----	-----	-----	52	----	6	66.04	63.50	12.25	7.00	2.96							
D														D						
C														C						
B														B						
A	SEE SHEET 14 EC NO: S2015-1512 DRWN: NARAYAKRISHNA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV					QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	A				
											DRAWN BY DATE		TITLE							
											KCHO 2004/11/05		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H							
											CHECKED BY DATE									
											PTLIM 2004/12/08									
											APPROVED BY DATE									
											MLONG 2010/09/06									
											MATERIAL NO.		DOCUMENT NO.							
											SEE TABLE		SD-87914-013							
											SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
											fb_frame_A3_P_AM_T Rev. G 2012/01/11						9	8	7	6

10		9		8		7		6		5		4		3		2		1									
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																			
								A	B	F	M	P															
F	87914-5411	-----	-----	-----	-----	54	-----	1	68.58	66.04	10.92	5.84	2.79							F							
	87914-5421	-----	-----	-----	-----	54	-----	1	68.58	66.04	12.25	7.00	2.96														
	87914-5412	-----	-----	-----	-----	54	-----	2	68.58	66.04	10.92	5.84	2.79														
	87914-5422	-----	-----	-----	-----	54	-----	2	68.58	66.04	12.25	7.00	2.96														
	87914-5413	-----	-----	-----	-----	54	-----	3	68.58	66.04	10.92	5.84	2.79														
	87914-5423	-----	-----	-----	-----	54	-----	3	68.58	66.04	12.25	7.00	2.96														
E	87914-5414	-----	-----	-----	-----	54	-----	4	68.58	66.04	10.92	5.84	2.79							E							
	87914-5424	-----	-----	-----	-----	54	-----	4	68.58	66.04	12.25	7.00	2.96														
	87914-5415	-----	-----	-----	-----	54	-----	5	68.58	66.04	10.92	5.84	2.79														
	87914-5425	-----	-----	-----	-----	54	-----	5	68.58	66.04	12.25	7.00	2.96														
	87914-5416	-----	-----	-----	-----	54	-----	6	68.58	66.04	10.92	5.84	2.79														
	87914-5426	-----	-----	-----	-----	54	-----	6	68.58	66.04	12.25	7.00	2.96														
D																				D							
C																				C							
B																				B							
A																				A							
										SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15		QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 32 OF 45	
										DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO. SD-87914-013											
fb_frame_A3_P_AM_T Rev. G 2012/01/11										9		8		7		6		5		4		3		2		1	

	10	9	8	7	6	5	4	3	2	1												
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F								
									A	B	F	M	P									
	87914-5611	-----	-----	-----	-----	56	----	1	71.12	68.58	10.92	5.84	2.79									
	87914-5621	-----	-----	-----	-----	56	----	1	71.12	68.58	12.25	7.00	2.96									
	87914-5612	-----	-----	-----	-----	56	----	2	71.12	68.58	10.92	5.84	2.79									
	87914-5622	-----	-----	-----	-----	56	----	2	71.12	68.58	12.25	7.00	2.96									
	87914-5613	-----	-----	-----	-----	56	----	3	71.12	68.58	10.92	5.84	2.79									
	87914-5623	-----	-----	-----	-----	56	----	3	71.12	68.58	12.25	7.00	2.96									
E	87914-5614	-----	-----	-----	-----	56	----	4	71.12	68.58	10.92	5.84	2.79	E								
	87914-5624	-----	-----	-----	-----	56	----	4	71.12	68.58	12.25	7.00	2.96									
	87914-5615	-----	-----	-----	-----	56	----	5	71.12	68.58	10.92	5.84	2.79									
	87914-5625	-----	-----	-----	-----	56	----	5	71.12	68.58	12.25	7.00	2.96									
	87914-5616	-----	-----	-----	-----	56	----	6	71.12	68.58	10.92	5.84	2.79									
	87914-5626	-----	-----	-----	-----	56	----	6	71.12	68.58	12.25	7.00	2.96									
D														D								
C														C								
B														B								
A	SEE SHEET 14 EC NO: S2015-1512 DRWN:NRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 DESCRIPTION REV D15					QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	A						
											MM ONLY		NTS	METRIC								
											DRAWN BY		DATE			2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H						
											KCHO		2004/11/05									
											CHECKED BY		DATE									
											PTLIM		2004/12/08									
											APPROVED BY		DATE									
											MLONG		2010/09/06									
											MATERIAL NO.		DOCUMENT NO.									
											SEE TABLE		SD-87914-013			SHEET NO. 33 OF 45						
											DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
											fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1	

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F						
	A	B	F	M	P															
	87914-5811	-----	-----	-----	-----	58	-----	1	73.66	71.12	10.92	5.84	2.79							
	87914-5821	-----	-----	-----	-----	58	-----	1	73.66	71.12	12.25	7.00	2.96							
	87914-5812	-----	-----	-----	-----	58	-----	2	73.66	71.12	10.92	5.84	2.79							
	87914-5822	-----	-----	-----	-----	58	-----	2	73.66	71.12	12.25	7.00	2.96							
	87914-5813	-----	-----	-----	-----	58	-----	3	73.66	71.12	10.92	5.84	2.79							
	87914-5823	-----	-----	-----	-----	58	-----	3	73.66	71.12	12.25	7.00	2.96							
E	87914-5814	-----	-----	-----	-----	58	-----	4	73.66	71.12	10.92	5.84	2.79	E						
	87914-5824	-----	-----	-----	-----	58	-----	4	73.66	71.12	12.25	7.00	2.96							
	87914-5815	-----	-----	-----	-----	58	-----	5	73.66	71.12	10.92	5.84	2.79							
	87914-5825	-----	-----	-----	-----	58	-----	5	73.66	71.12	12.25	7.00	2.96							
	87914-5816	-----	-----	-----	-----	58	-----	6	73.66	71.12	10.92	5.84	2.79							
	87914-5826	-----	-----	-----	-----	58	-----	6	73.66	71.12	12.25	7.00	2.96							
D														D						
		</																		

	10		9		8		7		6		5		4		3		2		1		
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
									A	B	F	M	P								
F	87914-6011	-----	-----	-----	-----	60	-----	1	76.20	73.66	10.92	5.84	2.79								F
	87914-6021	-----	-----	-----	-----	60	-----	1	76.20	73.66	12.25	7.00	2.96								
	87914-6012	-----	-----	-----	-----	60	-----	2	76.20	73.66	10.92	5.84	2.79								
	87914-6022	-----	-----	-----	-----	60	-----	2	76.20	73.66	12.25	7.00	2.96								
E	87914-6013	-----	-----	-----	-----	60	-----	3	76.20	73.66	10.92	5.84	2.79								E
	87914-6023	-----	-----	-----	-----	60	-----	3	76.20	73.66	12.25	7.00	2.96								
	87914-6014	-----	-----	-----	-----	60	-----	4	76.20	73.66	10.92	5.84	2.79								
	87914-6024	-----	-----	-----	-----	60	-----	4	76.20	73.66	12.25	7.00	2.96								
	87914-6015	-----	-----	-----	-----	60	-----	5	76.20	73.66	10.92	5.84	2.79								
	87914-6025	-----	-----	-----	-----	60	-----	5	76.20	73.66	12.25	7.00	2.96								
D	87914-6016	-----	-----	-----	-----	60	-----	6	76.20	73.66	10.92	5.84	2.79								D
	87914-6026	-----	-----	-----	-----	60	-----	6	76.20	73.66	12.25	7.00	2.96								
C																					C
B																					B

A	SEE SHEET 14 EC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 DESCRIPTION REV D15												QUALITY SYMBOLS ▽_F=0 ▽_E=0 ▽_P=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE MLONG 2010/09/06		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex					
													MATERIAL NO.		DOCUMENT NO.		SHEET NO.									
													SEE TABLE		SD-87914-013		35 OF 45									
													SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
													fb_frame_A3_P_AM_T Rev. G 2012/01/11													
													987654321													

[illegible]

	10		9		8		7		6		5		4		3		2		1		
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F							
									A	B	F	M	P								
	87914-6411	-----	-----	-----	-----	64	----	1	81.28	78.74	10.92	5.84	2.79								
	87914-6421	-----	-----	-----	-----	64	----	1	81.28	78.74	12.25	7.00	2.96								
	87914-6412	-----	-----	-----	-----	64	----	2	81.28	78.74	10.92	5.84	2.79								
	87914-6422	-----	-----	-----	-----	64	----	2	81.28	78.74	12.25	7.00	2.96								
	87914-6413	-----	-----	-----	-----	64	----	3	81.28	78.74	10.92	5.84	2.79								
	87914-6423	-----	-----	-----	-----	64	----	3	81.28	78.74	12.25	7.00	2.96								
E	87914-6414	-----	-----	-----	-----	64	----	4	81.28	78.74	10.92	5.84	2.79	E							
	87914-6424	-----	-----	-----	-----	64	----	4	81.28	78.74	12.25	7.00	2.96								
	87914-6415	-----	-----	-----	-----	64	----	5	81.28	78.74	10.92	5.84	2.79								
	87914-6425	-----	-----	-----	-----	64	----	5	81.28	78.74	12.25	7.00	2.96								
	87914-6416	-----	-----	-----	-----	64	----	6	81.28	78.74	10.92	5.84	2.79								
	87914-6426	-----	-----	-----	-----	64	----	6	81.28	78.74	12.25	7.00	2.96								
D																				D	
C																				C	
B																				B	
A	SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15								QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		A		
													MM ONLY		NTS	METRIC					
										4 PLACES	± ---	± ---	DRAWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 37 OF 45				
										3 PLACES	± ---	± ---	CHECKED BY	DATE							
										2 PLACES	± 0.20	± ---	PTL IM	2004/12/08							
1 PLACE	± ---	± ---	APPROVED BY	DATE																	
0 PLACE	±	±	MLONG	2010/09/06	DOCUMENT NO.		SD-87914-013														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
F	87914-6611	-----	-----	-----	-----	66	----	1	83.82	81.28	10.92	5.84	2.79							
	87914-6621	-----	-----	-----	-----	66	----	1	83.82	81.28	12.25	7.00	2.96							
	87914-6612	-----	-----	-----	-----	66	----	2	83.82	81.28	10.92	5.84	2.79							
	87914-6622	-----	-----	-----	-----	66	----	2	83.82	81.28	12.25	7.00	2.96							
	87914-6613	-----	-----	-----	-----	66	----	3	83.82	81.28	10.92	5.84	2.79							
E	87914-6623	-----	-----	-----	-----	66	----	3	83.82	81.28	12.25	7.00	2.96							
	87914-6614	-----	-----	-----	-----	66	----	4	83.82	81.28	10.92	5.84	2.79							
	87914-6624	-----	-----	-----	-----	66	----	4	83.82	81.28	12.25	7.00	2.96							
	87914-6615	-----	-----	-----	-----	66	----	5	83.82	81.28	10.92	5.84	2.79							
	87914-6625	-----	-----	-----	-----	66	----	5	83.82	81.28	12.25	7.00	2.96							
D	87914-6616	-----	-----	-----	-----	66	----	6	83.82	81.28	10.92	5.84	2.79							
	87914-6626	-----	-----	-----	-----	66	----	6	83.82	81.28	12.25	7.00	2.96							
C																				
B																				
A	SEE SHEET 14 IEC NO: S2015-1512 DRW:NARAYAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV QUALITY SYMBOLS =0 =0 =0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE SCALE NTS DESIGN UNITS METRIC THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex DOCUMENT NO. SD-87914-013 SHEET NO. 38 OF 45 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
	fb_frame_A3_P_AM_T Rev. G 2012/01/11	9		8		7		6		5		4		3		2		1		

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					A	B	F	M	P		
F	87914-6811	-----	-----	-----	-----	68	----	1	86.36	83.82	10.92	5.84	2.79						
	87914-6821	-----	-----	-----	-----	68	----	1	86.36	83.82	12.25	7.00	2.96						
	87914-6812	-----	-----	-----	-----	68	----	2	86.36	83.82	10.92	5.84	2.79						
	87914-6822	-----	-----	-----	-----	68	----	2	86.36	83.82	12.25	7.00	2.96						
	87914-6813	-----	-----	-----	-----	68	----	3	86.36	83.82	10.92	5.84	2.79						
	87914-6823	-----	-----	-----	-----	68	----	3	86.36	83.82	12.25	7.00	2.96						
E	87914-6814	-----	-----	-----	-----	68	----	4	86.36	83.82	10.92	5.84	2.79						
	87914-6824	-----	-----	-----	-----	68	----	4	86.36	83.82	12.25	7.00	2.96						
	87914-6815	-----	-----	-----	-----	68	----	5	86.36	83.82	10.92	5.84	2.79						
	87914-6825	-----	-----	-----	-----	68	----	5	86.36	83.82	12.25	7.00	2.96						
	87914-6816	-----	-----	-----	-----	68	----	6	86.36	83.82	10.92	5.84	2.79						
	87914-6826	-----	-----	-----	-----	68	----	6	86.36	83.82	12.25	7.00	2.96						
D																			
C																			
B																			
A																			

SEE SHEET 14

IEC NO: S2015-1512

DRW:WIPRAKRI SHNA 2015/06/25

CHKD:ATSEE 2015/06/25

APPR:KPRASAD 2015/07/15

REV

QUALITY SYMBOLS

=0

=0

=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

mm

INCH

4 PLACES ± --- ± ---

3 PLACES ± --- ± ---

2 PLACES ± 0.20 ± ---

1 PLACE ± --- ± ---

0 PLACE ± ±

ANGULAR ± 3 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY DATE

KCHO 2004/11/05

CHECKED BY DATE

PTLIM 2004/12/08

APPROVED BY DATE

MLONG 2010/09/06

MATERIAL NO.

SEE TABLE

SIZE

A3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE

NTS

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

2.54MM PITCH

DUAL ROW HEADER

SINGLE WAFER, T/H

molex

DOCUMENT NO.

SD-87914-013

SHEET NO.

39 OF 45

10		9		8		7		6		5		4		3		2		1	
fb_frame_A3_P_AM_T																			
Rev. G 2012/01/11																			

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-7011	-----	-----	-----	-----	70	-----	1	88.90	86.36	10.92	5.84	2.79						
	87914-7021	-----	-----	-----	-----	70	-----	1	88.90	86.36	12.25	7.00	2.96						
	87914-7012	-----	-----	-----	-----	70	-----	2	88.90	86.36	10.92	5.84	2.79						
	87914-7022	-----	-----	-----	-----	70	-----	2	88.90	86.36	12.25	7.00	2.96						
	87914-7013	-----	-----	-----	-----	70	-----	3	88.90	86.36	10.92	5.84	2.79						
	87914-7023	-----	-----	-----	-----	70	-----	3	88.90	86.36	12.25	7.00	2.96						
E	87914-7014	-----	-----	-----	-----	70	-----	4	88.90	86.36	10.92	5.84	2.79						
	87914-7024	-----	-----	-----	-----	70	-----	4	88.90	86.36	12.25	7.00	2.96						
	87914-7015	-----	-----	-----	-----	70	-----	5	88.90	86.36	10.92	5.84	2.79						
	87914-7025	-----	-----	-----	-----	70	-----	5	88.90	86.36	12.25	7.00	2.96						
	87914-7016	-----	-----	-----	-----	70	-----	6	88.90	86.36	10.92	5.84	2.79						
	87914-7026	-----	-----	-----	-----	70	-----	6	88.90	86.36	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV DESCRIPTION D15							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
									mm		INCH		DRAWN BY DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
									4 PLACES ± --- ± ---		KCHO 2004/11/05								
									3 PLACES ± --- ± ---		CHECKED BY DATE								
									2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08								
									1 PLACE ± --- ± ---		APPROVED BY DATE								
									0 PLACE ± ±		MLONG 2010/09/06		DOCUMENT NO. SD-87914-013		SHEET NO. 40 OF 45				
									ANGULAR ± 3 °										
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

987654321

[illegible]

10		9		8		7		6		5		4		3		2		1																																
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																										
								A	B	F	M	P																																						
F	87914-7411	-----	-----	-----	-----	74	-----	1	93.98	91.44	10.92	5.84	2.79																																					
	87914-7421	-----	-----	-----	-----	74	-----	1	93.98	91.44	12.25	7.00	2.96																																					
	87914-7412	-----	-----	-----	-----	74	-----	2	93.98	91.44	10.92	5.84	2.79																																					
	87914-7422	-----	-----	-----	-----	74	-----	2	93.98	91.44	12.25	7.00	2.96																																					
	87914-7413	-----	-----	-----	-----	74	-----	3	93.98	91.44	10.92	5.84	2.79																																					
E	87914-7423	-----	-----	-----	-----	74	-----	3	93.98	91.44	12.25	7.00	2.96																																					
	87914-7414	-----	-----	-----	-----	74	-----	4	93.98	91.44	10.92	5.84	2.79																																					
	87914-7424	-----	-----	-----	-----	74	-----	4	93.98	91.44	12.25	7.00	2.96																																					
	87914-7415	-----	-----	-----	-----	74	-----	5	93.98	91.44	10.92	5.84	2.79																																					
	87914-7425	-----	-----	-----	-----	74	-----	5	93.98	91.44	12.25	7.00	2.96																																					
D	87914-7416	-----	-----	-----	-----	74	-----	6	93.98	91.44	10.92	5.84	2.79																																					
	87914-7426	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96																																					
C																																																		
B																																																		
A																																																		
<table><tr><td rowspan="5">SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV</td><td rowspan="5">QUALITY SYMBOLS F=0 F=0 F=0</td><td rowspan="5">GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td rowspan="5">DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE</td><td rowspan="5">SCALE NTS</td><td rowspan="5">DESIGN UNITS METRIC</td><td rowspan="5">THIRD ANGLE PROJECTION</td><td colspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td><td rowspan="5">molex</td><td rowspan="5">DOCUMENT NO. SD-87914-013</td><td rowspan="5">SHEET NO. 42 OF 45</td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr><tr><td colspan="2"></td></tr><tr><td colspan="12">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																			SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE	SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		molex	DOCUMENT NO. SD-87914-013	SHEET NO. 42 OF 45									THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE	SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		molex	DOCUMENT NO. SD-87914-013	SHEET NO. 42 OF 45																																							
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																		

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	C	D	E							
F	87914-7611	-----	-----	-----	-----	76	-----	1	96.52	93.98	10.92	5.84	2.79						
	87914-7621	-----	-----	-----	-----	76	-----	1	96.52	93.98	12.25	7.00	2.96						
	87914-7612	-----	-----	-----	-----	76	-----	2	96.52	93.98	10.92	5.84	2.79						
	87914-7622	-----	-----	-----	-----	76	-----	2	96.52	93.98	12.25	7.00	2.96						
	87914-7613	-----	-----	-----	-----	76	-----	3	96.52	93.98	10.92	5.84	2.79						
	87914-7623	-----	-----	-----	-----	76	-----	3	96.52	93.98	12.25	7.00	2.96						
E	87914-7614	-----	-----	-----	-----	76	-----	4	96.52	93.98	10.92	5.84	2.79						
	87914-7624	-----	-----	-----	-----	76	-----	4	96.52	93.98	12.25	7.00	2.96						
	87914-7615	-----	-----	-----	-----	76	-----	5	96.52	93.98	10.92	5.84	2.79						
	87914-7625	-----	-----	-----	-----	76	-----	5	96.52	93.98	12.25	7.00	2.96						
	87914-7616	-----	-----	-----	-----	76	-----	6	96.52	93.98	10.92	5.84	2.79						
	87914-7626	-----	-----	-----	-----	76	-----	6	96.52	93.98	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15							QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
								=0 =0 =0			mm	INCH	DRAWN BY	DATE	TITLE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			
									4 PLACES	± ---	± ---	KCHO	2004/11/05						
									3 PLACES	± ---	± ---	CHECKED BY	DATE						
									2 PLACES	± 0.20	± ---	PTL IM	2004/12/08						
									1 PLACE	± ---	± ---	APPROVED BY	DATE						
								0 PLACE	±	±	MLONG	2010/09/06							
								ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.		SHEET NO.						
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		43 OF 45					
								SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F						
	A	B	F	M	P															
	87914-7811	-----	-----	-----	-----	78	-----	1	99.06	96.52	10.92	5.84	2.79							
	87914-7821	-----	-----	-----	-----	78	-----	1	99.06	96.52	12.25	7.00	2.96							
	87914-7812	-----	-----	-----	-----	78	-----	2	99.06	96.52	10.92	5.84	2.79							
	87914-7822	-----	-----	-----	-----	78	-----	2	99.06	96.52	12.25	7.00	2.96							
	87914-7813	-----	-----	-----	-----	78	-----	3	99.06	96.52	10.92	5.84	2.79							
	87914-7823	-----	-----	-----	-----	78	-----	3	99.06	96.52	12.25	7.00	2.96							
E	87914-7814	-----	-----	-----	-----	78	-----	4	99.06	96.52	10.92	5.84	2.79	E						
	87914-7824	-----	-----	-----	-----	78	-----	4	99.06	96.52	12.25	7.00	2.96							
	87914-7815	-----	-----	-----	-----	78	-----	5	99.06	96.52	10.92	5.84	2.79							
	87914-7825	-----	-----	-----	-----	78	-----	5	99.06	96.52	12.25	7.00	2.96							
	87914-7816	-----	-----	-----	-----	78	-----	6	99.06	96.52	10.92	5.84	2.79							
	87914-7826	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96							
D														D						
C														C						
B														B						
A	SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15								QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		A	
mm									INCH		MM ONLY		NTS	METRIC	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
4 PLACES									± --- ± ---		DRAWN BY DATE		TITLE							
3 PLACES									± --- ± ---		KCHO 2004/11/05									
2 PLACES		± 0.20 ± ---		CHECKED BY DATE		PTLIM 2004/12/08				molex										
1 PLACE		± --- ± ---		APPROVED BY DATE		MLONG 2010/09/06														
0 PLACE		± ±		MATERIAL NO.		SEE TABLE		DOCUMENT NO.		SD-87914-013		SHEET NO.								
												44 OF 45								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSIONS											
								A	B	F	M	P							
F	87914-8011	-----	-----	-----	-----	80	-----	1	101.60	99.06	10.92	5.84	2.79						
	87914-8021	-----	-----	-----	-----	80	-----	1	101.60	99.06	12.25	7.00	2.96						
	87914-8012	-----	-----	-----	-----	80	-----	2	101.60	99.06	10.92	5.84	2.79						
	87914-8022	-----	-----	-----	-----	80	-----	2	101.60	99.06	12.25	7.00	2.96						
	87914-8013	-----	-----	-----	-----	80	-----	3	101.60	99.06	10.92	5.84	2.79						
	87914-8023	-----	-----	-----	-----	80	-----	3	101.60	99.06	12.25	7.00	2.96						
E	87914-8014	-----	-----	-----	-----	80	-----	4	101.60	99.06	10.92	5.84	2.79						
	87914-8024	-----	-----	-----	-----	80	-----	4	101.60	99.06	12.25	7.00	2.96						
	87914-8015	-----	-----	-----	-----	80	-----	5	101.60	99.06	10.92	5.84	2.79						
	87914-8025	-----	-----	-----	-----	80	-----	5	101.60	99.06	12.25	7.00	2.96						
	87914-8016	-----	-----	-----	-----	80	-----	6	101.60	99.06	10.92	5.84	2.79						
	87914-8026	-----	-----	-----	-----	80	-----	6	101.60	99.06	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15							QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
								=0 =0 =0	mm INCH	MM ONLY		DRAWN BY	DATE	TITLE					
										4 PLACES	± ---	± ---	KCHO	2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
										3 PLACES	± ---	± ---	CHECKED BY	DATE					
										2 PLACES	± 0.20	± ---	PTL IM	2004/12/08					
										1 PLACE	± ---	± ---	APPROVED BY	DATE					
										0 PLACE	±	±	MLONG	2010/09/06					
								ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-87914-013		45 OF 45				
								SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---