

Interference Suppression Film Capacitor - Class X1 Radial MKP 480 V_{AC} - 3-Phase Across the Line



FEATURES

- AEC-Q200 qualified (rev. D, 85 °C maximum application temperature) for pitch 10 mm, 15 mm, and 22.5 mm
- Internal series construction
- Stable capacitance in severe ambient conditions 85 °C, 85 % RH, 400 V_{AC}, 500 h for C > 100 nF
- THB: 40 °C / 90 % RH for 1000 h at rated voltage in compliance with AEC-Q200
- Complying with IEC 60384-14: AMD1 Grade IA
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

 AUTOMOTIVE
GRADE
Available

RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- 3-phase and continuous across the line X1 applications
- Standard and continuous in series with the mains operation


 See also application note: www.vishay.com/doc?28153

| QUICK REFERENCE DATA | |
|---|--|
| Capacitance range (E12 series) | 0.001 µF to 1.0 µF (preferred values according to E6) |
| Capacitance tolerance | ± 20 %; ± 10 %; (± 5 % on request) |
| Climatic testing class according to IEC 60068-1 | 55 / 110 / 56 / C for product volumes ≤ 1750 mm ³ 55 / 110 / 56 / B for product volumes > 1750 mm ³ |
| Rated AC voltage | 480 V _{AC} ; 50 Hz to 60 Hz |
| Permissible DC voltage | 1000 V _{DC} at 85 °C 800 V _{DC} at 110 °C |
| Maximum application temperature | 110 °C |
| Reference standards | IEC 60384-14 ed-4 (2013) and EN 60384-14 IEC 60065 requires pass. flamm. class B for volumes > 1750 mm ³ , class C for volume < 1750 mm ³ CSA-E384-14; UL60384-14 CQC GB/T6346.14-2015 |
| Dielectric | Polypropylene film |
| Electrodes | Metallized |
| Construction | Series construction |
| Encapsulation | Plastic case, epoxy resin sealed, flame retardant UL-class 94 V-0 |
| Leads | Tinned wire |
| Marking | C-value; tolerance; rated voltage; sub-class; manufacturer's type; code for dielectric material; manufacturer location, year and week; manufacturer's logo or name; safety approvals |

Note

- For more detailed data and test requirements, contact rfi@vishay.com

| DIMENSIONS in millimeters |
|---------------------------|
| |

COMPOSITION OF CATALOG NUMBER

Notes

- For detailed tape specifications refer to packaging information www.vishay.com/doc?28139
- ⁽¹⁾ Packaging will be bulk for all capacitors with pitch ≤ 15 mm and such with long leads (> 5 mm). Capacitors with short leads up to 5 mm and pitch > 15 mm will be in tray and asking code will be "T"



| SPECIFIC REFERENCE DATA | | |
|--|-----------------------------|--------------------------|
| DESCRIPTION | VALUE | |
| Rated AC voltage (U_{RAC}) | 480 V | |
| Permissible DC voltage (U_{RDC}) | 1000 V | |
| Tangent of loss angle | At 1 kHz | At 10 kHz |
| $C < 470 \text{ nF}$ | $\leq 10 \times 10^{-4}$ | $\leq 20 \times 10^{-4}$ |
| $470 \text{ nF} \leq C \leq 1 \mu\text{F}$ | $\leq 20 \times 10^{-4}$ | $\leq 70 \times 10^{-4}$ |
| Rated voltage pulse slope (dU/dt) _R at 670 V _{DC} | | |
| Pitch = 10 mm | 800 V/ μ s | |
| Pitch = 15 mm | 600 V/ μ s | |
| Pitch = 22.5 mm | 400 V/ μ s | |
| Pitch = 27.5 mm | 250 V/ μ s | |
| R between leads, for $C \leq 0.33 \mu\text{F}$ at 100 V; 1 min | $> 15\,000 \text{ M}\Omega$ | |
| RC between leads, for $C > 0.33 \mu\text{F}$ at 100 V; 1 min | $> 5000 \text{ s}$ | |
| R between leads and case; 100 V; 1 min | $> 30\,000 \text{ M}\Omega$ | |
| Withstanding (DC) voltage (cut off current 10 mA) ⁽¹⁾ ; rise time $\leq 1000 \text{ V/s}$: | 3400 V; 1 min | |
| Withstanding (AC) voltage between leads and case | 2460 V; 1 min | |
| Maximum application temperature | 110 °C | |

Note

⁽¹⁾ See "Voltage Proof Test for Metalized Film Capacitors": www.vishay.com/doc?28169

| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | |
|---|---------------------------|--|----------------------------|--|---|-------------|--|-------------|--|-----|
| U_{RAC} (V) | CAP. (μF) | DIMENSIONS ⁽⁴⁾ w x h x l (mm) | MASS (g) ⁽³⁾ | CATALOG NUMBER F339X1... AND PACKAGING | | | | | | |
| | | | | LOOSE IN BOX | | | | | TAPED REEL | |
| | | | | SHORT LEADS | | | LONG LEADS | | | |
| | | | | $l_t = 3.5 \text{ mm} +1 \text{ mm}/-0.5 \text{ mm}$ (PITCH $\leq 10 \text{ mm}$) or $3.5 \text{ mm} \pm 0.3 \text{ mm}$ (PITCH $\geq 15 \text{ mm}$) | $l_t = 5.0 \text{ mm} \pm 1.0 \text{ mm}$ | SPQ | $l_t = 25.0 \text{ mm} \pm 2.0 \text{ mm}$ | SPQ | $\varnothing = 500 \text{ mm}$ ⁽¹⁾⁽²⁾ $H = 18.5 \text{ mm}$; $P_0 = 12.7 \text{ mm}$ | SPQ |
| PITCH = 10 mm \pm 0.4 mm; $d_t = 0.60 \text{ mm} \pm 0.06 \text{ mm}$; C-TOL. = $\pm 20 \%$ | | | | | | | | | | |
| 0.0010 | 4.0 x 10.0 x 12.5 | 0.6 | 21048MDA2B0 | 21048MDM2B0 | 1000 | 21048MDI2B0 | 1250 | 21048MD02W0 | 1400 | |
| 0.0015 | | | 21548MDA2B0 | 21548MDM2B0 | | 21548MDI2B0 | | 21548MD02W0 | | |
| 0.0022 | | | 22248MDA2B0 | 22248MDM2B0 | | 22248MDI2B0 | | 22248MD02W0 | | |
| 0.0033 | | | 23348MDA2B0 | 23348MDM2B0 | | 23348MDI2B0 | | 23348MD02W0 | | |
| 0.0047 | 5.0 x 11.0 x 12.5 | 0.82 | 24748MDA2B0 | 24748MDM2B0 | 1000 | 24748MDI2B0 | 1000 | 24748MD02W0 | 1100 | |
| 0.0068 | 6.0 x 12.0 x 12.5 | 1.1 | 26848MDA2B0 | 26848MDM2B0 | 750 | 26848MDI2B0 | 750 | 26848MD02W0 | 900 | |
| 0.010 | | | 31048MDA2B0 | 31048MDM2B0 | | 31048MDI2B0 | | 31048MD02W0 | | |
| PITCH = 15 mm \pm 0.4 mm; $d_t = 0.60 \text{ mm} \pm 0.06 \text{ mm}$; C-TOL. = $\pm 20 \%$ | | | | | | | | | | |
| 0.010 | 5.0 x 11.0 x 17.5 | 1.0 | 31048MFP2B0 | 31048MFM2B0 | 1250 | 31048MFI2B0 | 1000 | 31048MF02W0 | 1100 | |
| 0.015 | | | 31548MFP2B0 | 31548MFM2B0 | | 31548MFI2B0 | | 31548MF02W0 | | |
| 0.022 | | | 32248MFP2B0 | 32248MFM2B0 | | 32248MFI2B0 | | 32248MF02W0 | | |
| 0.033 | | | 33348MFP2B0 | 33348MFM2B0 | | 33348MFI2B0 | | 33348MF02W0 | | |
| 0.047 | 6.0 x 12.0 x 17.5 | 1.4 | 34748MFP2B0 | 34748MFM2B0 | 1000 | 34748MFI2B0 | 1000 | 34748MF02W0 | 900 | |
| PITCH = 15 mm \pm 0.4 mm; $d_t = 0.80 \text{ mm} \pm 0.08 \text{ mm}$; C-TOL. = $\pm 20 \%$ | | | | | | | | | | |
| 0.068 | 8.5 x 15.0 x 17.5 | 2.4 | 36848MFP2B0 | 36848MFM2B0 | 750 | 36848MFI2B0 | 500 | 36848MF02W0 | 650 | |
| 0.100 | 10 x 16.5 x 17.5 | 3.0 | 41048MFP2B0 | 41048MFM2B0 | 500 | 41048MFI2B0 | 450 | 41048MF02W0 | 600 | |
| PITCH = 22.5 mm \pm 0.4 mm; $d_t = 0.80 \text{ mm} \pm 0.08 \text{ mm}$; C-TOL. = $\pm 20 \%$ | | | | | | | | | | |
| 0.047 | 6.0 x 15.5 x 26.0 | 2.4 | 34748MIP2T0 | 34748MIM2T0 | 300 | 34748MII2B0 | 250 | 34748MI02W0 | 600 | |
| 0.068 | | | 36848MIP2T0 | 36848MIM2T0 | | 36848MII2B0 | | 36848MI02W0 | | |
| 0.10 | | | 41048MIP2T0 | 41048MIM2T0 | | 41048MII2B0 | | 41048MI02W0 | | |
| 0.15 | 7.0 x 16.5 x 26.0 | 2.9 | 41548MIP2T0 | 41548MIM2T0 | 200 | 41548MII2B0 | 250 | 41548MI02W0 | 500 | |
| 0.22 | 8.5 x 18.0 x 26.0 | 3.8 | 42248MIP2T0 | 42248MIM2T0 | 200 | 42248MII2B0 | 250 | 42248MI02W0 | 450 | |
| 0.33 | 12 x 22.0 x 26.0 | 7.8 | 43348MIP2T0 | 43348MIM2T0 | 150 | 43348MII2B0 | 200 | 43348MI02W0 | 300 | |






| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | | | |
|---|--------------------|--|----------------------------|--|-------------------------------------|-------------|--------------------------------------|-------------|------------|-----|--|-----|
| U _{RAC} (V) | CAP. (μF) | DIMENSIONS ⁽⁴⁾ w x h x l (mm) | MASS (g) ⁽³⁾ | CATALOG NUMBER F339X1... AND PACKAGING | | | | | | | | |
| | | | | LOOSE IN BOX | | | | | TAPED REEL | | | |
| | | | | SHORT LEADS | | | LONG LEADS | | SPQ | SPQ | Ø = 500 mm ⁽¹⁾⁽²⁾ H = 18.5 mm; P ₀ = 12.7 mm | SPQ |
| | | | | l _t = 3.5 mm +1 mm/-0.5 mm (PITCH ≤ 10 mm) or 3.5 mm ± 0.3 mm (PITCH ≥ 15 mm) | l _t = 5.0 mm ± 1.0 mm | SPQ | l _t = 25.0 mm ± 2.0 mm | SPQ | | | | |
| PITCH = 27.5 mm ± 0.4 mm; d_t = 0.80 mm ± 0.08 mm; C-TOL. = ± 20 % | | | | | | | | | | | | |
| 0.15 | 9.0 x 19.0 x 31.5 | 5.5 | 41548MKP2T0 | 41548MKM2T0 | 100 | 41548MKI2B0 | 150 | | | | | |
| 0.22 | | | 42248MKP2T0 | 42248MKM2T0 | | 42248MKI2B0 | | | | | | |
| 0.33 | 11.0 x 21.0 x 31.0 | 7.4 | 43348MKP2T0 | 43348MKM2T0 | 100 | 43348MKI2B0 | 125 | | | | | |
| 0.47 | 13.0 x 23.0 x 31.0 | 9.2 | 44748MKP2T0 | 44748MKM2T0 | 100 | 44748MKI2B0 | 125 | | | | | |
| 0.68 | 15.0 x 25.0 x 31.5 | 12.3 | 46848MKP2T0 | 46848MKM2T0 | 100 | 46848MKI2B0 | 125 | | | | | |
| 1.0 | 18.0 x 28.0 x 31.5 | 16.1 | 51048MKP2T0 | 51048MKM2T0 | 100 | 51048MKI2B0 | 100 | | | | | |
| PITCH = 10.0 mm ± 0.4 mm; d_t = 0.60 mm ± 0.06 mm; C-TOL. = ± 10 % | | | | | | | | | | | | |
| 0.0010 | 4.0 x 10.0 x 12.5 | 0.6 | 21048KDA2B0 | 21048KDM2B0 | 1000 | 21048KDI2B0 | 1250 | 21048KD02W0 | 1400 | | | |
| 0.0012 | | | 21248KDA2B0 | 21248KDM2B0 | | 21248KDI2B0 | | 21248KD02W0 | | | | |
| 0.0015 | | | 21548KDA2B0 | 21548KDM2B0 | | 21548KDI2B0 | | 21548KD02W0 | | | | |
| 0.0018 | | | 21848KDA2B0 | 21848KDM2B0 | | 21848KDI2B0 | | 21848KD02W0 | | | | |
| 0.0022 | | | 22248KDA2B0 | 22248KDM2B0 | | 22248KDI2B0 | | 22248KD02W0 | | | | |
| 0.0027 | | | 22748KDA2B0 | 22748KDM2B0 | | 22748KDI2B0 | | 22748KD02W0 | | | | |
| 0.0033 | | | 23348KDA2B0 | 23348KDM2B0 | | 23348KDI2B0 | | 23348KD02W0 | | | | |
| 0.0039 | | | 23948KDA2B0 | 23948KDM2B0 | | 23948KDI2B0 | | 23948KD02W0 | | | | |
| 0.0047 | 5.0 x 11.0 x 12.5 | 0.82 | 24748KDA2B0 | 24748KDM2B0 | 1000 | 24748KDI2B0 | 1000 | 24748KD02W0 | 1100 | | | |
| 0.0056 | | | 25648KDA2B0 | 25648KDM2B0 | | 25648KDI2B0 | | 25648KD02W0 | | | | |
| 0.0068 | 6.0 x 12.0 x 12.5 | 1.1 | 26848KDA2B0 | 26848KDM2B0 | 750 | 26848KDI2B0 | 750 | 26848KD02W0 | 900 | | | |
| 0.0082 | | | 28248KDA2B0 | 28248KDM2B0 | | 28248KDI2B0 | | 28248KD02W0 | | | | |
| PITCH = 15.0 mm ± 0.4 mm; d_t = 0.60 mm ± 0.06 mm; C-TOL. = ± 10 % | | | | | | | | | | | | |
| 0.010 | 5.0 x 11.0 x 17.5 | 1.0 | 31048KFP2B0 | 31048KFM2B0 | 1250 | 31048KFI2B0 | 1000 | 31048KF02W0 | 1100 | | | |
| 0.012 | | | 31248KFP2B0 | 31248KFM2B0 | | 31248KFI2B0 | | 31248KF02W0 | | | | |
| 0.015 | | | 31548KFP2B0 | 31548KFM2B0 | | 31548KFI2B0 | | 31548KF02W0 | | | | |
| 0.018 | | | 31848KFP2B0 | 31848KFM2B0 | | 31848KFI2B0 | | 31848KF02W0 | | | | |
| 0.022 | | | 32248KFP2B0 | 32248KFM2B0 | | 32248KFI2B0 | | 32248KF02W0 | | | | |
| 0.027 | | | 32748KFP2B0 | 32748KFM2B0 | | 32748KFI2B0 | | 32748KF02W0 | | | | |
| 0.033 | 6.0 x 12.0 x 17.5 | 1.4 | 33348KFP2B0 | 33348KFM2B0 | 1000 | 33348KFI2B0 | 1000 | 33348KF02W0 | 900 | | | |
| 0.039 | | | 33948KFP2B0 | 33948KFM2B0 | | 33948KFI2B0 | | 33948KF02W0 | | | | |
| PITCH = 15.0 mm ± 0.4 mm; d_t = 0.80 mm ± 0.08 mm; C-TOL. = ± 10 % | | | | | | | | | | | | |
| 0.047 | 7.0 x 13.5 x 17.5 | 1.8 | 34748KFP2B0 | 34748KFM2B0 | 750 | 34748KFI2B0 | 500 | 34748KF02W0 | 800 | | | |
| 0.056 | | | 35648KFP2B0 | 35648KFM2B0 | | 35648KFI2B0 | | 35648KF02W0 | | | | |
| 0.068 | 8.5 x 15.0 x 17.5 | 2.4 | 36848KFP2B0 | 36848KFM2B0 | 750 | 36848KFI2B0 | 500 | 36848KF02W0 | 650 | | | |
| 0.082 | | | 38248KFP2B0 | 38248KFM2B0 | | 38248KFI2B0 | | 38248KF02W0 | | | | |
| 0.100 | 10.0 x 16.5 x 17.5 | 3.0 | 41048KFP2B0 | 41048KFM2B0 | 500 | 41048KFI2B0 | 450 | 41048KF02W0 | 600 | | | |

| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | |
|--|---|--|----------------------------|--|-------------------------------------|-------------|--------------------------------------|-----|--|-----|
| U _{RAC} (V) | CAP. (µF) | DIMENSIONS ⁽⁴⁾ w x h x l (mm) | MASS (g) ⁽³⁾ | CATALOG NUMBER F339X1... AND PACKAGING | | | | | | |
| | | | | LOOSE IN BOX | | | | | TAPED REEL | |
| | | | | SHORT LEADS | | | LONG LEADS | | | |
| | | | | l _t = 3.5 mm +1 mm/-0.5 mm (PITCH ≤ 10 mm) or 3.5 mm ± 0.3 mm (PITCH ≥ 15 mm) | l _t = 5.0 mm ± 1.0 mm | SPQ | l _t = 25.0 mm ± 2.0 mm | SPQ | Ø = 500 mm ⁽¹⁾⁽²⁾ H = 18.5 mm; P ₀ = 12.7 mm | SPQ |
| 480 | PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 10 % | | | | | | | | | |
| | 0.047 | 6.0 x 15.5 x 26.0 | 2.4 | 34748KIP2T0 | 34748KIM2T0 | 300 | 34748KII2B0 | 250 | 34748KI02W0 | 600 |
| | 0.056 | | | 35648KIP2T0 | 35648KIM2T0 | | 35648KII2B0 | | 35648KI02W0 | |
| | 0.068 | | | 36848KIP2T0 | 36848KIM2T0 | | 36848KII2B0 | | 36848KI02W0 | |
| | 0.082 | | | 38248KIP2T0 | 38248KIM2T0 | | 38248KII2B0 | | 38248KI02W0 | |
| | 0.10 | | | 41048KIP2T0 | 41048KIM2T0 | | 41048KII2B0 | | 41048KI02W0 | |
| | 0.12 | 7.0 x 16.5 x 26.0 | 2.9 | 41248KIP2T0 | 41248KIM2T0 | 200 | 41248KII2B0 | 250 | 41248KI02W0 | 500 |
| | 0.15 | 8.5 x 18.0 x 26.0 | 3.8 | 41548KIP2T0 | 41548KIM2T0 | 200 | 41548KII2B0 | 250 | 41548KI02W0 | 450 |
| | 0.18 | | | 41848KIP2T0 | 41848KIM2T0 | | 41848KII2B0 | | 41848KI02W0 | |
| | 0.22 | 10.0 x 19.5 x 26.0 | 6.8 | 42248KIP2T0 | 42248KIM2T0 | 200 | 42248KII2B0 | 200 | 42248KI02W0 | 350 |
| | 0.27 | 12.0 x 22.0 x 26.0 | 7.8 | 42748KIP2T0 | 42748KIM2T0 | 150 | 42748KII2B0 | 200 | 42748KI02W0 | 300 |
| | 0.33 | | | 43348KIP2T0 | 43348KIM2T0 | | 43348KII2B0 | | 43348KI02W0 | |
| | PITCH = 27.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 10 % | | | | | | | | | |
| | 0.15 | 9.0 x 19.0 x 31.5 | 5.5 | 41548KKP2T0 | 41548KKM2T0 | 100 | 41548KKI2B0 | 150 | | |
| | 0.18 | | | 41848KKP2T0 | 41848KKM2T0 | | 41848KKI2B0 | | | |
| | 0.22 | | | 42248KKP2T0 | 42248KKM2T0 | | 42248KKI2B0 | | | |
| | 0.27 | 11.0 x 21.0 x 31.0 | 7.4 | 42748KKP2T0 | 42748KKM2T0 | 100 | 42748KKI2B0 | 125 | | |
| | 0.33 | | | 43348KKP2T0 | 43348KKM2T0 | | 43348KKI2B0 | | | |
| | 0.39 | 13.0 x 23.0 x 31.0 | 9.2 | 43948KKP2T0 | 43948KKM2T0 | 100 | 43948KKI2B0 | 125 | | |
| | 0.47 | | | 44748KKP2T0 | 44748KKM2T0 | | 44748KKI2B0 | | | |
| 0.56 | 15.0 x 25.0 x 31.5 | 12.3 | 45648KKP2T0 | 45648KKM2T0 | 100 | 45648KKI2B0 | 125 | | | |
| 0.68 | 18.0 x 28.0 x 31.5 | 16.1 | 46848KKP2T0 | 46848KKM2T0 | 100 | 46848KKI2B0 | 100 | | | |
| 0.82 | | | 48248KKP2T0 | 48248KKM2T0 | | 48248KKI2B0 | | | | |
| 1.0 | 21.0 x 31.0 x 31.0 | 20.3 | 51048KKP2T0 | 51048KKM2T0 | 50 | 51048KKI2B0 | 75 | | | |

Notes

- SPQ = Standard Packing Quantity
- (1) Reel diameter = 356 mm is available on request
- (2) H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to "Packaging Information"
- (3) Weight for short lead product only
- (4) For tolerances see chapter "Space Requirements for Printed-Circuit Board Applications and Dimension Tolerances"

| APPROVALS | | | | |
|---|---------------------|----------------|---------------|--|
| SAFETY APPROVALS X1 | VOLTAGE | VALUE | FILE NUMBERS | LINK |
| EN 60384-14 (ENEC) (= IEC 60384-14 ed-4 (2013)) | 480 V _{AC} | 1 nF to 1.0 µF | 40033060 | www.vishay.com/doc?28230 |
| UL 60384-14 | 480 V _{AC} | 1 nF to 1.0 µF | E354331A | www.vishay.com/doc?28209 |
| CSA-E384-14 | 480 V _{AC} | 1 nF to 1.0 µF | E354331A | www.vishay.com/doc?28209 |
| CQC | 480 V _{AC} | 1 nF to 1.0 µF | L-16001150859 | www.vishay.com/doc?28233 |
| | | | F-16001161460 | www.vishay.com/doc?28234 |
| CB-test certificate | 480 V _{AC} | 1 nF to 1.0 µF | DE1-58018 | www.vishay.com/doc?28219 |
| The ENEC-approval together with the CB-certificate replace all national marks of the following countries (they have already signed the ENEC-agreement): Austria; Belgium; Czech. Republic; Denmark; Finland; France; Germany; Greece; Hungary; Ireland; Italy; Luxembourg; Netherlands; Norway; Portugal; Slovenian; Spain; Sweden, Switzerland and United Kingdom. | | | | |
|    | | | | |

MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting on printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information www.vishay.com/docs?28139

Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that the stand-off pips are in good contact with the printed-circuit board:


- For original pitch ≤ 15 mm the capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

Space Requirements for Printed-Circuit Board Applications and Dimension Tolerances

For the maximum product dimensions and maximum space requirements for length ($l_{max.}$), width ($w_{max.}$) and height ($h_{max.}$) following tolerances must be taken in account in the envelopment of the components as shown in the drawings below.

- For products with pitch ≤ 15 mm, $\Delta w = \Delta l = 0.3$ mm and $\Delta h = 0.1$ mm
- For products with 15 mm $<$ pitch ≤ 27.5 mm, $\Delta w = \Delta l = 0.5$ mm and $\Delta h = 0.1$ mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



For the minimum product dimensions for length ($l_{min.}$), width ($w_{min.}$) and height ($h_{min.}$) following tolerances of the components are valid:

$l_{min.} = l - \Delta l$, $w_{min.} = w - \Delta w$ and $h_{min.} = h - \Delta h$ following

- For products with pitch ≤ 10 mm, $\Delta l = 0.3$ mm and $\Delta w = \Delta h = 0.3$ mm
- For products with pitch = 15 mm, $\Delta l = 0.5$ mm and $\Delta w = \Delta h = 0.5$ mm
- For products with 15 mm $<$ pitch ≤ 27.5 mm, $\Delta l = 1.0$ mm and $\Delta w = \Delta h = 0.5$ mm

SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile we refer to the document "Soldering Guidelines for Film Capacitors": www.vishay.com/doc?28171

STORAGE TEMPERATURE

$T_{stg} = -25$ °C to $+35$ °C with RH maximum 75 % without condensation


RATINGS AND CHARACTERISTICS REFERENCE CONDITIONS

Unless otherwise specified, all electrical values apply to an ambient free temperature of 23 °C ± 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % ± 2 %.


For reference testing, a conditioning period shall be applied over 96 h ± 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.




CHARACTERISTICS




Capacitance as a function of ambient temperature (typical curve)




Tangent of loss angle as a function of frequency (typical curve)




Impedance as a function of frequency (typical curve)




Resonant frequency as a function of capacitance (typical curve)



Max. RMS voltage as a function of frequency




Max. RMS current as a function of frequency



Insulation resistance as a function of ambient temperature (typical curve)

APPLICATION NOTES

- For X1 electromagnetic interference suppression in **standard and 3-phase across the line applications** (50 Hz/60 Hz) with a maximum mains voltage of 480 V_{AC}
- For series impedance applications we refer to the application note: www.vishay.com/doc?28153
- To ensure withstanding high humidity requirements in the application it is recommended not to damage the epoxy adhesion at the leads. Therefore the leads may not be damaged or bent before soldering.
- For capacitors connected in parallel, normally the proof voltage must be reduced in function of the total parallel capacitance value.



Proof voltage as function of total parallel capacitance

- These capacitors are not intended for continuous pulse applications. For these situations, capacitors of the AC and pulse programs must be used.
- The maximum ambient temperature must not exceed 110 °C.
- Rated voltage pulse slope:
if the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by 670 V_{DC} and divided by the applied voltage.



INSPECTION REQUIREMENTS

General Notes

Sub-clause numbers of tests and performance requirements refer to the “Sectional Specification, Publication IEC 60384-14 ed-4 (2013) and Specific Reference Data”.


| GROUP C INSPECTION REQUIREMENTS | | |
|---|---|--|
| SUB-CLAUSE NUMBER AND TEST | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1 | | |
| 4.1 Dimensions (detail) | | As specified in chapters “General Data” of this specification |
| Initial measurements | Capacitance Tangent of loss angle at 10 kHz for $C \leq 1 \mu\text{F}$ Tangent of loss angle at 1 kHz for $C > 1 \mu\text{F}$ | |
| 4.3 Robustness of terminations | Tensile: load 10 N; 10 s Bending: load 5 N; 4 x 90° | No visible damage |
| 4.4 Resistance to soldering heat | No pre-drying Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s | |
| SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1 | | |
| 4.19 Component solvent resistance | Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: min. 1 h, max. 2 h | |
| 4.4.2 Final measurements | Visual examination Capacitance Tangent of loss angle Insulation resistance | No visible damage Legible marking $ \Delta C/C \leq 5\%$ of the value measured initially Increase of $\tan \delta \leq 0.008$ for $\leq 1 \mu\text{F}$ Increase of $\tan \delta \leq 0.005$ for $C > 1 \mu\text{F}$ Compared to values measured initially As specified in section “Insulation Resistance” of this specification |
| SUB-GROUP C1B OTHER PART OF SAMPLE OF SUB-GROUP C1 | | |
| Initial measurements | Capacitance Tangent of loss angle at 10 kHz for $C \leq 1 \mu\text{F}$ Tangent of loss angle at 1 kHz for $C > 1 \mu\text{F}$ | |
| 4.20 Solvent resistance of the marking | Isopropyl alcohol at room temperature Method: 1 Rubbing material: cotton wool Immersion time: 5 min ± 0.5 min | No visible damage Legible marking |
| 4.6 Rapid change of temperature | $\theta A = -55 \text{ °C}$ $\theta B = +110 \text{ °C}$ 5 cycles Duration t = 30 min | |



| GROUP C INSPECTION REQUIREMENTS | | |
|--|---|--|
| SUB-CLAUSE NUMBER AND TEST | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C1B OTHER PART OF SAMPLE OF SUB-GROUP C1 | | |
| 4.6.1 Inspection | Visual examination | No visible damage |
| 4.7 Vibration | Mounting: see section "Mounting" of this specification Procedure B4: frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s ² (whichever is less severe) Total duration 6 h | |
| 4.7.2 Final inspection | Visual examination | No visible damage |
| 4.9 Shock | Mounting: see section "Mounting" for more information Pulse shape: half sine Acceleration: 490 m/s ² Duration of pulse: 11 ms | |
| 4.9.2 Final measurements | Visual examination Capacitance Tangent of loss angle Insulation resistance | No visible damage $ \Delta C/C \leq 5\%$ of the value measured initially Increase of $\tan \delta \leq 0.008$ for $\leq 1 \mu\text{F}$ Increase of $\tan \delta \leq 0.005$ for $C > 1 \mu\text{F}$ Compared to values measured initially As specified in section "Insulation Resistance" of this specification |
| SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B | | |
| 4.11 Climatic sequence | | |
| 4.11.1 Initial measurements | Capacitance Measured in 4.4.2 and 4.9.2 Tangent of loss angle: measured initially in C1A and C1B | |
| 4.11.2 Dry heat | Temperature: 110 °C | |
| 4.11.3 Damp heat cyclic Test Db First cycle | Duration: 16 h | |
| 4.11.4 Cold | Temperature: -55 °C | |
| 4.11.5 Damp heat cyclic Test Db remaining cycles | Duration: 2 h | |
| 4.11.6 Final measurements | Visual examination Capacitance Tangent of loss angle Voltage proof 1900 V _{DC} ; 1 min between terminations Insulation resistance | No visible damage Legible marking $ \Delta C/C \leq 5\%$ of the value measured in 4.11.1. Increase of $\tan \delta \leq 0.008$ for $\leq 1 \mu\text{F}$ Increase of $\tan \delta \leq 0.005$ for $C > 1 \mu\text{F}$ Compared to values measured in 4.11.1 No permanent breakdown or flash-over $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |



| GROUP C INSPECTION REQUIREMENTS | | |
|--|---|--|
| SUB-CLAUSE NUMBER AND TEST | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP C2A | | |
| 4.12A Damp heat steady state with load | RH: 85 %, temp: 85 °C, load: 400 V _{AC} , duration: 500 h for C > 100 nF | |
| 4.12.1A Initial measurements | Capacitance Tangent of loss angle at 1 kHz | |
| 4.12.3A Final measurements | Visual examination | No visible damage Legible marking |
| | Capacitance | $ \Delta C/C \leq 10\%$ of the value measured in 4.12.1A. |
| | Tangent of loss angle | Increase of $\tan \delta \leq 0.008$ Compared to values measured in 4.12.1A. |
| | Voltage proof 1900 V _{DC} ; 1 min between terminations | No permanent breakdown or flash-over |
| | Insulation resistance | $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |
| SUB-GROUP C3 | | |
| 4.13.1 Initial measurements | Capacitance Tangent of loss angle at 10 kHz for C \leq 1 μ F Tangent of loss angle at 1 kHz for C > 1 μ F | |
| 4.13 Impulse voltage | 3 successive impulses, full wave, peak voltage: X1: 4.0 kV for C \leq 1 μ F X1: 4.0 kV/ \sqrt{C} for C > 1 μ F Max. 24 pulses | No self healing breakdowns or flash-over |
| 4.14 Endurance | Duration: 1000 h 1.25 x U _{RAC} at 110 °C Once in every hour the voltage is increased to 1000 V _{RMS} for 0.1 s via resistor of 47 $\Omega \pm 5\%$ | |
| 4.14.7 Final measurements | Visual examination | No visible damage Legible marking |
| | Capacitance | $ \Delta C/C \leq 10\%$ compared to values measured in 4.13.1. |
| | Tangent of loss angle | Increase of $\tan \delta \leq 0.008$ for $\leq 1 \mu F$ Increase of $\tan \delta \leq 0.005$ for C > 1 μF Compared to values measured in 4.13.1 |
| | Voltage proof 1900 V _{DC} ; 1 min between terminations 2460 V _{AC} ; 1 min between terminations and case | No permanent breakdown or flash-over |
| | Insulation resistance | $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |

| GROUP C INSPECTION REQUIREMENTS | | | | | | | | | | | | | | |
|--|---|---|---------|---------|----------------|---|------|-----------------|---|------|-----------|------|---|--|
| SUB-CLAUSE NUMBER AND TEST | CONDITIONS | PERFORMANCE REQUIREMENTS | | | | | | | | | | | | |
| SUB-GROUP C4 | | | | | | | | | | | | | | |
| 4.15 Charge and discharge | 10 000 cycles charged to 670 V _{DC} Discharge resistance: $R = \frac{670 V_{DC}}{1.5 \times C (dU/dt)}$ | | | | | | | | | | | | | |
| 4.15.1 Initial measurements | Capacitance Tangent of loss angle at 10 kHz for C ≤ 1 μF Tangent of loss angle at 1 kHz for C > 1 μF | | | | | | | | | | | | | |
| 4.15.3 Final measurements | Capacitance Tangent of loss angle Insulation resistance | $ \Delta C/C \leq 10\%$ compared to values measured in 4.15.1. Increase of tan δ ≤ 0.008 for ≤ 1 μF Increase of tan δ ≤ 0.005 for C > 1 μF Compared to values measured in 4.15.1 ≥ 50 % of values specified in section "Insulation Resistance" of this specification | | | | | | | | | | | | |
| SUB-GROUP C5 | | | | | | | | | | | | | | |
| 4.16 Radio frequency characteristic | Resonance frequency | ≥ 0.9 times the value as specified in section "Resonant Frequency" of this specification | | | | | | | | | | | | |
| SUB-GROUP C6 | | | | | | | | | | | | | | |
| 4.17 Passive flammability Class B for volume > 1750mm ³ Class C for volume ≤ 1750 mm ³ | Bore of gas jet: Ø 0.5 mm Fuel: butane Test duration for actual volume V in mm ³ : <table border="1"> <thead> <tr> <th>Volume</th> <th>Class B</th> <th>Class C</th> </tr> </thead> <tbody> <tr> <td>250 < V ≤ 500:</td> <td>-</td> <td>10 s</td> </tr> <tr> <td>500 < V ≤ 1750:</td> <td>-</td> <td>20 s</td> </tr> <tr> <td>V > 1750:</td> <td>60 s</td> <td>-</td> </tr> </tbody> </table> One flame application  | Volume | Class B | Class C | 250 < V ≤ 500: | - | 10 s | 500 < V ≤ 1750: | - | 20 s | V > 1750: | 60 s | - | After removing test flame from capacitor, the capacitor must not continue to burn for more than 10 s. No burning particle must drop from the sample. |
| Volume | Class B | Class C | | | | | | | | | | | | |
| 250 < V ≤ 500: | - | 10 s | | | | | | | | | | | | |
| 500 < V ≤ 1750: | - | 20 s | | | | | | | | | | | | |
| V > 1750: | 60 s | - | | | | | | | | | | | | |
| SUB-GROUP C7 | | | | | | | | | | | | | | |
| 4.18 Active flammability | 20 cycles of 4 kV discharges on the test capacitor connected to U _{RAC} | The cheese cloth around the capacitors shall not burn with a flame. No electrical measurements are required. | | | | | | | | | | | | |



| GROUP C INSPECTION REQUIREMENTS | | |
|---|---|---|
| SUB-CLAUSE NUMBER AND TEST | CONDITIONS | PERFORMANCE REQUIREMENTS |
| SUB-GROUP ADD1 | | |
| A.1 Damp heat steady state with voltage | RH: 40 %; temperature: 93 °C; Voltage: 480 V _{AC} , duration: 21 days | |
| A.1.1 Initial measurements | Capacitance Tangent of loss angle: at 10 kHz | |
| A.1.2 Final measurements | Visual examination Capacitance Tangent of loss angle Insulation resistance | No visible damage Legible marking $ \Delta C/C \leq 10\%$ of the value with initial measurement A 1.1 Increase of $\tan \delta: \leq 0.024$ compared to values with initial measurement A 1.1 $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |

| TEST CONDITIONS AND REQUIRMENTS ACCORDING AEC-Q200 REVISION D | | | | |
|---|--------------------------------------|------------------------|---|--|
| NO. | TEST NAME | REFERENCE | TEST CONDITION | PERFORMANCE REQUIREMENTS |
| 1 | Pre- and post-stress electrical test | User Spec | - | - |
| 3 | High temperature exposure (storage) | MIL-STD-202 Method 108 | Temperature: 105 °C; unpowered duration:1000 h | $ \Delta C/C \leq 10\%$ Increase in $\tan \delta = 0.008$ for $C \leq 1 \mu F$ at 10 kHz Insulation resistance $\geq 50\%$ of initial requirement |
| 4 | Temperature cycling | JESD22 Method JA-104 | Total No. of cycles: 1000 cycles Lower temperature: -40 °C Upper temperature: +85 °C Dwell each 30 min as per Rev. D | $ \Delta C/C \leq 10\%$ Increase in $\tan \delta = 0.008$ for $C \leq 1 \mu F$ at 10 kHz Insulation resistance $\geq 50\%$ of initial requirement |
| 6 | Moisture resistance | MIL-STD-202 Method 106 | 10 cycles at 24 h/cycle Unpowered | $ \Delta C/C \leq 10\%$ Increase in $\tan \delta = 0.008$ for $C \leq 1 \mu F$ at 10 kHz Insulation resistance $\geq 50\%$ of initial requirement |
| 7 | Biased humidity | MIL-STD-202 Method 103 | Temperature: 40 °C; RH: 93%; U _{RAC} duration: 1000 h | $ \Delta C/C \leq 10\%$ Increase in $\tan \delta = 0.008$ for $C \leq 1 \mu F$ at 10 kHz Insulation resistance $\geq 50\%$ of initial requirement |
| 8 | Operational life | MIL-STD-202 Method 108 | Temperature: +85 °C; load = U _{RAC} ; duration= 1000 h | $ \Delta C/C \leq 10\%$ Increase in $\tan \delta = 0.008$ for $C \leq 1 \mu F$ at 10 kHz Insulation resistance $\geq 50\%$ of initial requirement |
| 11 | Terminal strength (lead) | MIL-STD-202 Method 211 | Leaded device lead integrity only | No visual damage |
| 12 | Resistance to solvents | MIL-STD-202 Method 215 | Also aqueous chemical - OKEM clean or equivalent; do not use banned solvents | No visual damage and legible marking |
| 13 | Mechanical shock | MIL-STD-202 Method 213 | Figure a of Method 213, Condition C | No visual damage |



| TEST CONDITIONS AND REQUIRMENTS ACCORDING AEC-Q200 REVISION D | | | | |
|---|------------------------------|------------------------|---|--|
| NO. | TEST NAME | REFERENCE | TEST CONDITION | PERFORMANCE REQUIREMENTS |
| 14 | Vibration | MIL-STD-202 Method 204 | 5 g's for 20 min., 12 cycles, 3 orientations | No visual damage |
| 15 | Resistance to soldering heat | MIL-STD-202 Method 210 | 260 °C, 10 s | $ \Delta C/C \leq \pm 5 \%$ Increase in $\tan \delta = 0.008$ for $C \leq 1 \mu F$ at 10 kHz Insulation resistance $\geq 50 \%$ of initial requirement |
| 18 | Solderability | J-STD-002 | 235 °C, 5 s | Good tinning as evidence by free flowing of the solder with wetting of terminations $> 95 \%$ |
| 19 | Electrical characterization | User spec | - | |
| 20 | Flammability | UL-94 | Electrical test not required | After removing test flame from capacitor, the capacitor must not continue to burn for more than 10 s for $V > 1750 \text{ mm}^3$; no burning particle must drop from the sample |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.