










- 5 UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
- 6 MATERIAL: STEEL PER ASTM-A-109.
- 7 MATERIAL: BRASS PER MIL-C-50 AND ASTM-B-36 UNS NO. C26000.
- 8 FINISH: TIN PER ASTM-B-545 .000400 MIN THK OVER COPPER PER AMS2418 .000050 MIN THK.
- 9 FINISH: CADMIUM PLATED PER QQ-P-416.
- 10 FINISH: GOLD PER MIL-G-45204 TYPE II, GRADE C, CLASS 1 OVER COPPER PER MIL-C-14550, CLASS IV.
- 11 INK STAMP WESTINGHOUSE PART NO. 97942-645A935H03, FAR SIDE.
- 12 FINISH: ZINC PLATE PER ASTM-B-633, .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+)



	.120	-	5-208552-4
	.120	-	5-208552-1
	.120	T5935-0103-006	208552-7
	.120	-	208552-6
	.154	311P405-22S-B-15	208552-5
	.120	-	208552-4
	.120	97942-645A935H03	208552-3
	.120	311P405-22S-B-12	208552-2
	.120	-	208552-1
REMARKS	ØA	CUSTOMER PART NO.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 07-JAN-88 T. SHUEY CHK. A. EMADI APP'D. A. EMADI 27-JAN-88	 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY AMPLITUDE 24C7 SIZE 5, COAX MIX
		PRODUCT SPEC — APPLICATION SPEC —		
MATERIAL —		WEIGHT —		
FINISH —		SIZE CASE CODE DRAWING NO. RESTRICTED TO — A1 00779 C=208552 —		
CUSTOMER DRAWING				
SCALE 4:1 SHEET 1 OF 1 REV T				