

SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Terminal body (Contact pin): Brass
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
 - Solid wire(AWG): 14-24
 - Stranded wire(AWG): 14-24
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:  

RoHS Compliant

PART NUMBER:

OSTHAXX0150

No. of Poles

02 2 Poles

03 3 Poles

... ..

24 24 Poles

COLOR

0: Black

5: Green (Standard)


6: Blue

8: Grey




THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE							
OSTHA-5.08mm series horizontal (180° wire inlet)							
PART NO.				DWG NO.			
OSTHAXX0150				OSTHAXX0150.DWG			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		
Shi Jun 2006.11.01		Marvin 2006.11.01	Steady 2006.10.11	Steady 2006.10.11			
SHEET: 01/01						UNIT: mm	Tolerance
						SCALE: NONE	X. ±0.50
						REV: D	X.X ±0.30
							X.XX ±0.10
							X° ±1°



N=Number of contacts



P.C.B. LAYOUT

