





PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM'A"
89038-X01/X01LF	1.6	2.90
89038-X11/X11LF	2.4	3.53




PRODUCT AFTER PC BOARD APPLICATION.



PC BOARD THICKNESS ±0.20
SEE TABLE

NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 μm SnPb 90-97 OR 2-8 μm PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 6 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH T. SIDES OF PRODUCT
- 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED INGS-22-008.
- 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL:
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL
-9YY/9YYLF	TELCORDIA CO

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
l	tr	ec	n	dr	date	linear	projection
J	0004-0004	CLW	041221				
K	0006-0470	Cen	11/23/06				
L	0007-0071	Cen	05/25/07				
M	0008-0071	TER	8/26/08				
G	V00578	LLA	000316	chr	Slee	930203	
H	V00847	LLA	000530	app	J.Vint	930203	
sheet	revision	M	M	M			
Index	sheet	1	2	3			




PDM: Rev:M

STATUS: Released

Printed: Nov 14, 2008

All rights strictly reserved. Reproduction or use in any form without written authority from the proprietor.
Tous droits strictement réservés. Reproduction ou utilisation en toute forme sans autorisation écrite du propriétaire.
FCI

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
89038-X02/X02LF	1.6	2.90
89038-X12/X12LF	2.4	3.53




PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL:
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL
-9YY/9YYLF	TELCORDIA CO

PC BOARD THICKNESS ±0.20
SEE TABLE

PRODUCT AFTER PC BOARD APPLICATION.

- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR 2-8 μ m PURE Sn
 - 4 INDICATED HOLES ARE UNPLATED.
 - 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
 - 6 SET BACK FOR PRESS BLOCK.
 - 7 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
 - 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.




14.64 REF. SEE NOTE 6



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

nat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltn	ecn	nodr	date	linear	projection	title	www.fciconnection
M				angles	ϕ	RA FEMALE SIGNAL 96 mm PRESS PEG	
dr	J. de Bl.	970529		engr	P. Schalk	970529	product family METRAL(tm)
chr	P. Schalk	970529		app	H. Coolmans	970529	code 213
sheet	revision			scale	5d	A2	89038
Index	sheet						sheet 2 of 2

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM 'A'
89038-X03/X03LF	1.6	2.90
89038-X13/X13LF	2.4	3.53




PRODUCT AFTER PC BOARD APPLICATION.

PC BOARD THICKNESS ± 0.20
SEE TABLE

NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 μm SnPb 90-97 OR 2-8 μm PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 6 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
- 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL:
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL
-9YY/9YYLF	TELCORDIA CO

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
l	tr	ec	n	n	dr	date	date
M				linear			
				angles			
				dr	Heaven Cen	11/23/06	
				engr	Collins Lu	11/23/06	
				chr	Beer Fu	11/23/06	
				app	Joseph Hala	11/23/06	
sheet	revision			scale	5d		
Index	sheet						
title		product family		size		code	
RA FEMALE SIGNAL		96 mm PRESS PEG		A2		213	
size		dwg no		89038		sheet	
						3 of ~	

PDM: Rev:M

STATUS: Released

Printed: Nov 14, 2008