

SPECIFICATIONS

ELECTRICAL

FREQUENCY RANGE_____DC TO 18 GHz

ATTENUATION_____0-6 dB _____±0.3 dB
 _____7-10, 20 dB _____±0.5 dB
 _____11-19, 21-30 dB _____±0.7 dB
 _____40 dB _____±1.0 dB
 _____50, 60 dB _____±2.0 dB

(AVAILABLE IN 1/2 dB VALUES 0.5 - 10.5 dB)

VSWR(MAX)_____DC-4 _____1.15
 _____4-12.4 _____1.25
 _____12.4-18 _____1.35

POWER_____2 WATTS (AVG) 0.5 dB AND ABOVE
 _____50 WATTS FOR 0 dB UNIT
 _____500 WATTS (PEAK)

DERATED LINEARLY FROM 100% AT +25° C TO 10% AT +125 C

* 5μ S PULSE W, 0.05% DUTY CYCLE

IMPEDANCE:_____50 OHMS

MECHANICAL

OPERATING TEMP RANGE -65 TO +125°

1.24 LENGTH / WEIGHT MAX. 0.40oz. (11.3g)

1.80 LENGTH / WEIGHT MAX. 0.60oz. (15.3g)

MATERIAL

OUTER CONDUCTOR: STAINLESS STEEL NON MAGNETIC,
 PASSIVATED FINISH.

CENTER CONDUCTOR: BERYLLIUM COPPER, GOLD PLATED FINISH.

DIELECTRIC: TEFLON.

MATERIALS & FINISHES TYPICALLY PER MIL-PRF-39012

ORDERING INFORMATION

2082-6191 -01 THRU -03

2082-6192 -04 THRU -06

2082-6193 -07 THRU -10

2082-6194 -11 THRU -20

2082-6195 -30 AND -40(1.24LG)

2082-6196 -40, -50, -60

2081-619X-dB FOR MALE TO MALE


2080-619X-dB FOR FEMALE TO FEMALE

PRODUCTION
RELEASE

NOTE:
THIS DRAWING INCORPORATES
THIRD ANGLE PROJECTION
INTERPRET IN ACCORDANCE WITH
ANSI Y14.5-1995

REVISIONS

REV	DESCRIPTION	DATE	APPROVED
E	REVISED TO C SIZE SHT, UPDATED FORMAT	09/09/10	D.S.S



DRAWING PRACTICES PER ANSI-Y14.5
MIL-STD-100 & 1000
DIMENSIONS ARE IN INCHES AND
APPLY BEFORE/AFTER PROCESSING
SURFACE
ROUGHNESS

FINISH:
SEE NOTES

MATERIAL:
SEE NOTES

UNLESS OTHERWISE SPECIFIED
TOLERANCES IN:
DECIMALS INCH MM
.XX" .075" [1.9]
.XXX" .050" [1.3]
.XXXX" .030 [0.76]

UNLESS OTHERWISE NOTED
DIA CONCENTRIC <.003 T.I.R.

DRAWN
T. MAIN
CHECKED
DATE
07/28/2010
DATE
09/09/2010
ENG.
D. SAUNDERS

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF XMA CORP. OWN
SPECTRA AND SHALL NOT BE REPRODUCED,
COPIED, NOR USED, IN WHOLE OR IN PART,
AS A BASIS FOR THE DESIGN, MANUFACTURE
OR SALE OF OTHER ITEMS WITHOUT THE
EXPRESS WRITTEN PERMISSION OF XMA
CORP. CUSTOMERS AND VENDORS MAY
COPY FOR INTERNAL REVIEW USE AS NEEDED

WWW.XMACorp.com Sales@XMACorp.com
XMA Omni Spectra®
 XMA Corp. 150 Dow St. Manchester, NH 03045 (603) 222-2256 fax 222-2259

TITLE
FIXED COAXIAL ATTENUATOR
 SIZE C CAGE CODE 3HT76 DWG NO. 2082-619X-XX
 SCALE 4:1 PLATING AREA XXX SHEET 1 OF 1