


600 V - 3 A high efficiency ultrafast diode



DO-201AD

Features

- Ultrafast switching
- Low forward voltage drop
- Low thermal resistance
- Low leakage current (platinum doping)
- Planar technology
- ECOPACK compliant

Applications

- Switching diode
- Auxiliary power supply

Description

The STTH3R06, which uses ST ultrafast high voltage planar technology, is specially suited for free-wheeling, clamping, snubbing, demagnetization in power supplies and other power switching applications.

Product status	
STTH3R06	
Product summary	
Symbol	Value
$I_{F(AV)}$	3 A
V_{RRM}	600 V
$T_{j(max.)}$	175 °C
$V_{F(typ.)}$	1.00 V
$t_{rr(max.)}$	35 ns

1 Characteristics

Table 1. Absolute ratings (limiting values at 25 °C, unless otherwise specified)

Symbol	Parameter			Value	Unit
V _{RRM}	Repetitive peak reverse voltage			600	V
I _{F(RMS)}	Repetitive peak reverse voltage			10	A
I _{F(AV)}	Average forward current δ = 0.5, square wave	DO-201AD	T _L = 80 °C	3	A
		SMB	T _L = 55 °C		
		SMC	T _L = 80 °C		
I _{FSM}	Surge non repetitive forward current	DO-201AD	t _p = 10 ms sinusoidal	55	A
		SMB / SMC		45	
T _{stg}	Storage temperature range			-65 to +175	°C
T _j	Maximum operating junction temperature			+175	°C

Table 2. Thermal resistance parameter

Symbol	Parameter			Max. value	Unit
$R_{th(j-l)}$	Junction to lead		SMC	20	°C/W
			SMB	25	
	Junction to lead	Lead length = 10 mm	DO-201AD	20	
$R_{th(j-a)}$	Junction to ambient			75	

For more information, refer to the following application note :

- AN5088 : Rectifiers thermal management, handling and mounting recommendations

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
$I_R^{(1)}$	Reverse leakage current	$T_j = 25\text{ °C}$	$V_R = V_{RRM}$	-		3	μA
		$T_j = 150\text{ °C}$		-	15	100	
$V_F^{(2)}$	Forward voltage drop	$T_j = 25\text{ °C}$	$I_F = 3\text{ A}$	-		1.7	V
		$T_j = 150\text{ °C}$		-	1.0	1.25	

1. Pulse test: $t_p = 5\text{ ms}$, $\delta < 2\%$

2. Pulse test: $t_p = 380\text{ }\mu\text{s}$, $\delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 1.03 \times I_{F(AV)} + 0.09 \times I_{F(RMS)}^2$$

For more information, refer to the following application notes related to the power losses :

- AN604: Calculation of conduction losses in a power rectifier
- AN4021: Calculation of reverse losses on a power diode

Table 4. Dynamic characteristics ($T_J = 25\text{ °C}$ unless otherwise stated)

Symbol	Parameters	Test conditions	Min.	Typ.	Max.	Unit
t_{rr}	Reverse recovery time	$I_F = 0.5\text{ A}$, $I_{rr} = 0.25\text{ A}$, $I_R = 1\text{ A}$	-		30	ns
		$I_F = 1\text{ A}$, $dI_F/dt = -50\text{ A}/\mu\text{s}$, $V_R = 30\text{ V}$	-	35		
t_{fr}	Forward recovery time	$I_F = 3\text{ A}$, $dI_F/dt = 100\text{ A}/\mu\text{s}$, $V_{FR} = 1.1\text{ V}_{F(max.)}$	-		100	ns
V_{FP}	Forward recovery voltage	$I_F = 3\text{ A}$, $dI_F/dt = 100\text{ A}/\mu\text{s}$	-		10	V

1.1 Characteristics (curves)







Figure 1. Conduction losses versus average current

Figure 2. Forward voltage drop versus forward current

Figure 3. Relative variation of thermal impedance junction to ambient versus pulse duration (epoxy printed circuit FR4, $L_{leads} = 10$ mm, $S_{Cu} = 1\text{cm}^2$)

Figure 4. Peak reverse recovery current versus di_F/dt (typical values)

Figure 5. Reverse recovery time versus di_F/dt (typical values)

Figure 6. Reverse recovery charges versus di_F/dt (typical values)








Figure 7. Softness factor versus di_F/dt (typical values)

Figure 8. Relative variations of dynamic parameters versus junction temperature

Figure 9. Transient peak forward voltage versus di_F/dt (typical values)

Figure 10. Forward recovery time versus di_F/dt (typical values)

Figure 11. Junction capacitance versus reverse voltage applied (typical values)

Figure 12. Thermal resistance junction to ambient versus copper surface under each lead (typical values) (SMB)


Figure 13. Thermal resistance versus lead length (DO-201AD)





Figure 14. Thermal resistance junction to ambient versus copper surface under each lead (typical values) (SMC)



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 DO-201AD package information

- Epoxy meets UL 94, V0

Figure 15. DO-201AD package outline




Table 5. DO-201AD package mechanical data

Ref.	Dimensions					
	Millimeters			Inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A		-	9.50		-	0.374
B	25.40	-		1.000	-	
C		-	5.30		-	0.209
D ⁽¹⁾		-	1.30		-	0.051
E		-	1.25			0.049
Note 2 ⁽²⁾	15.00			0.590		

- The lead diameter D is not controlled over zone E
- The minimum length, which must stay straight between the right angles after bending, is 15 mm (0.59")

2.2 SMB package information

- Epoxy meets UL94, V0
- Lead-free package

Figure 16. SMB package outline





Table 6. SMB package mechanical data

Ref.	Dimensions			
	Millimeters		Inches (for reference only)	
	Min.	Max.	Min.	Max.
A1	1.90	2.45	0.074	0.097
A2	0.05	0.20	0.001	0.008
b	1.95	2.20	0.076	0.087
c	0.15	0.40	0.005	0.016
D	3.30	3.95	0.129	0.156
E	5.10	5.60	0.200	0.221
E1	4.05	4.60	0.159	0.182
L	0.75	1.50	0.029	0.060

Figure 17. SMB recommended footprint



2.3 SMC package information

- Epoxy meets UL94, V0

Figure 18. SMC package outline





Table 7. SMC package mechanical data

Ref.	Dimensions			
	Millimeters		Inches (for reference only)	
	Min.	Max.	Min.	Max.
A1	1.90	2.45	0.0748	0.0965
A2	0.05	0.20	0.0020	0.0079
b	2.90	3.20	0.1142	0.1260
c	0.15	0.40	0.0059	0.0157
D	5.55	6.25	0.2185	0.2461
E	7.75	8.15	0.3051	0.3209
E1	6.60	7.15	0.2598	0.2815
E2	4.40	4.70	0.1732	0.1850
L	0.75	1.50	0.0295	0.0591

Figure 19. SMC recommended footprint



3 Ordering information

Table 8. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STTH3R06	STTH3R06	DO-201AD	1.16 g	600	Ammopack
STTH3R06-RL	STTH3R06	DO-201AD	1.16 g	1900	Tape and reel
STTH3R06U	3R6U	SMB	0.107 g	2500	Tape and reel
STTH3R06S	R6S	SMC	0.245 g	2500	Tape and reel

Revision history

Table 9. Document revision history

Date	Revision	Changes
Mar-2003	1	First issue
07-Sep-2004	2	SMB and SMC packages added
14-Oct-2005	3	Changed marking of STTH3R06U from R06U to 3R6U on page 1. Added ECOPACK statement.
21-Oct-2021	4	Updated pin names. Minor text changes.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics – All rights reserved