



PART NUMBER
CDIRBS2W




A

B

C

D

ELECTRICAL SCHEMATIC



APPROVALS

APPROVALS COVERAGE UL104/ASME17.1/CSA B44.1
FOR COMMERCIAL USE

ELECTRICAL RATINGS

VOLTAGE	24 VAC	24 VDC
CURRENT	0.35A, 60Hz	0.2A

ENVIRONMENTAL

OPERATING TEMPERATURE	+4° TO +38°C (+40° TO +100°F)
STORAGE TEMPERATURE	-40° TO 60° C (-40° TO +140°F)

MATERIAL OF CONSTRUCTION

ACTUATOR KEY	INVESTMENT CAST STAINLESS STEEL WITH POWDER COAT FINISH WHITE COLOR
CAM	INVESTMENT CAST STAINLESS STEEL
COVER	DIE CAST ZINC WITH POWDER COAT FINISH WHITE COLOR
HOUSING	DIE CAST ZINC WITH POWDER COAT FINISH WHITE COLOR

Honeywell

SWITCH ASSEMBLY

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
DECIMAL TOL NO PLACE ... ± .400
1 PLACE ... ± .030
2 PLACE ... ± .010
3 PLACE ... ± .005
ANGULAR TOL - ± 2° CHAMFER - ± 3°

MATERIAL	SIZE	CAGE CODE	DWG NO	TYPE	REV
-	D	-	CDIRBS2W	I	A
FINISH	-	-	-	REF WT:	-
SCALE	1 : 1	REF WT:	-	SHEET	1 of 1
RELEASE DATE	2012-12-05	DRW:	K. NAVEEN	2012-12-05	HONEYWELL CONFIDENTIAL
APPLICABLE DOCUMENTS:	ASME Y14.100-2004	RDE:	K. BALAJI	2012-12-05	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE, NOR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM HONEYWELL
ASME Y14.5-2009	QA:	-	-	-	2012-12-05
COMPUTER GENERATED DRAWING: PRO/ENGINEER	CHK:	K. BALAJI	-	-	2012-12-05