

NORYL PPXTM RESIN PPX7110

REGION AMERICAS

DESCRIPTION

NORYL PPXTM 7110 resin is a non-reinforced alloy of polyphenylene ether (PPE) + Polypropylene (PP). This injection moldable grade exhibits high impact resistance and good heat resistance along with hydrolytic and dimensional stability. NORYL PPX7110 resin is an excellent candidate for applications requiring high impact, chemical resistance, and good heat performance.

TYPICAL PROPERTY VALUES

Revision 20190925

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
MECHANICAL			
Tensile Stress, yld, Type I, 50 mm/min	35	MPa	ASTM D 638
Tensile Stress, brk, Type I, 50 mm/min	32	MPa	ASTM D 638
Tensile Strain, yld, Type I, 50 mm/min	6.5	%	ASTM D 638
Tensile Strain, brk, Type I, 50 mm/min	195	%	ASTM D 638
Tensile Modulus, 50 mm/min	1340	MPa	ASTM D 638
Flexural Stress, yld, 1.3 mm/min, 50 mm span	51	MPa	ASTM D 790
Flexural Modulus, 1.3 mm/min, 50 mm span	1550	MPa	ASTM D 790
IMPACT			
Izod Impact, notched, 23°C	437	J/m	ASTM D 256
Izod Impact, notched, -30°C	149	J/m	ASTM D 256
Instrumented Impact Total Energy, 23°C	37	J	ASTM D 3763
Instrumented Impact Total Energy, -30°C	27	J	ASTM D 3763
THERMAL			
Vicat Softening Temp, Rate B/50	138	°C	ASTM D 1525
HDT, 0.45 MPa, 3.2 mm, unannealed	113	°C	ASTM D 648
HDT, 1.82 MPa, 3.2mm, unannealed	77	°C	ASTM D 648
CTE, -40°C to 40°C, flow	8.1E-05	1/°C	ASTM E 831
CTE, -40°C to 40°C, xflow	1.12E-04	1/°C	ASTM E 831
PHYSICAL			
Specific Gravity	0.97	-	ASTM D 792
Mold Shrinkage, flow, 3.2 mm	0.8 – 1.2	%	SABIC method
Melt Flow Rate, 260°C/5.0 kgf	10.6	g/10 min	ASTM D 1238
FLAME CHARACTERISTICS⁽¹⁾			
UL Yellow Card Link	E121562-221229	-	-
UL Recognized, 94HB Flame Class Rating	≥1	mm	UL 94
INJECTION MOLDING			
Drying Temperature	60 – 65	°C	
Drying Time	2 – 4	hrs	
Drying Time (Cumulative)	8	hrs	
Maximum Moisture Content	0.02	%	
Melt Temperature	260 – 290	°C	
Nozzle Temperature	260 – 290	°C	
Front - Zone 3 Temperature	250 – 290	°C	

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
Middle - Zone 2 Temperature	240 – 280	°C	
Rear - Zone 1 Temperature	225 – 275	°C	
Mold Temperature	30 – 50	°C	
Back Pressure	0.3 – 0.7	MPa	
Screw Speed	20 – 100	rpm	
Shot to Cylinder Size	30 – 70	%	
Vent Depth	0.038 – 0.051	mm	
SHEET EXTRUSION			
Drying Temperature	60 – 65	°C	
Drying Time	2 – 4	hrs	
Drying Time (Cumulative)	4	hrs	
Melt Temperature	270 – 280	°C	
Barrel - Zone 1 Temperature	145 – 155	°C	
Barrel - Zone 2 Temperature	255 – 265	°C	
Barrel - Zone 3 Temperature	270 – 280	°C	
Barrel - Zone 4 Temperature	270 – 280	°C	
Adapter Temperature	265 – 270	°C	
Die Temperature	265 – 270	°C	

(1) UL Ratings shown on the technical datasheet might not cover the full range of thicknesses and colors. For details, please see the UL Yellow Card.

DISCLAIMER

Any sale by SABIC, its subsidiaries and affiliates (each a "seller"), is made exclusively under seller's standard conditions of sale (available upon request) unless agreed otherwise in writing and signed on behalf of the seller. While the information contained herein is given in good faith, SELLER MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING MERCHANTABILITY AND NONINFRINGEMENT OF INTELLECTUAL PROPERTY, NOR ASSUMES ANY LIABILITY, DIRECT OR INDIRECT, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OR PURPOSE OF THESE PRODUCTS IN ANY APPLICATION. Each customer must determine the suitability of seller materials for the customer's particular use through appropriate testing and analysis. No statement by seller concerning a possible use of any product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right.