

# SN54ALS01, SN74ALS01 QUADRUPLE 2-INPUT POSITIVE-NAND GATES WITH OPEN-COLLECTOR OUTPUTS

D2661, APRIL 1982 - REVISED MAY 1986

- Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs
- Dependable Texas Instruments Quality and Reliability

## description


These devices contain four independent 2-input NAND gates. They perform the Boolean functions  $Y = \overline{A \cdot B}$  or  $Y = \overline{A} + \overline{B}$  in positive logic. The open-collector outputs require pull-up resistors to perform correctly. They may be connected to other open-collector outputs to implement active-low wired-OR or active-high wired-AND functions. Open-collector devices are often used to generate higher  $V_{OH}$  levels.

The SN54ALS01 is characterized for operation over the full military temperature range of  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ . The SN74ALS01 is characterized for operation from  $0^{\circ}\text{C}$  to  $70^{\circ}\text{C}$ .

FUNCTION TABLE (each gate)

| INPUTS |   | OUTPUT |
|--------|---|--------|
| A      | B | Y      |
| H      | H | L      |
| L      | X | H      |
| X      | L | H      |

## logic symbol†




† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.


Pin numbers shown are for D, J, and N packages.

SN54ALS01 ... J PACKAGE  
SN74ALS01 ... D OR N PACKAGE

(TOP VIEW)




SN54ALS01 ... FK PACKAGE  
(TOP VIEW)



NC - No internal connection

## logic diagram (positive logic)



PRODUCTION DATA documents contain information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

TEXAS  
INSTRUMENTS

POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

Copyright © 1982, Texas Instruments Incorporated

# SN54ALS01, SN74ALS01

## QUADRUPLE 2-INPUT POSITIVE-NAND GATES

### WITH OPEN-COLLECTOR OUTPUTS

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

|                                                 |                  |
|-------------------------------------------------|------------------|
| Supply voltage, $V_{CC}$                        | 7 V              |
| Input voltage                                   | 7 V              |
| Off-state output voltage                        | 7 V              |
| Operating free-air temperature range: SN54ALS01 | -55 °C to 125 °C |
| SN74ALS01                                       | 0 °C to 70 °C    |
| Storage temperature range                       | -65 °C to 150 °C |

recommended operating conditions

|          |                                | SN54ALS01 |     |     | SN74ALS01 |     |     | UNIT |
|----------|--------------------------------|-----------|-----|-----|-----------|-----|-----|------|
|          |                                | MIN       | NOM | MAX | MIN       | NOM | MAX |      |
| $V_{CC}$ | Supply voltage                 | 4.5       | 5   | 5.5 | 4.5       | 5   | 5.5 | V    |
| $V_{IH}$ | High-level input voltage       | 2         |     |     | 2         |     |     | V    |
| $V_{IL}$ | Low-level input voltage        |           |     | 0.7 |           |     | 0.8 | V    |
| $V_{OH}$ | High-level output voltage      |           |     | 5.5 |           |     | 5.5 | V    |
| $I_{OL}$ | Low-level output current       |           |     | 4   |           |     | 8   | mA   |
| $T_A$    | Operating free-air temperature | -55       |     | 125 | 0         |     | 70  | °C   |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER | TEST CONDITIONS   |                  | SN54ALS01 |      |      | SN74ALS01 |      |      | UNIT |
|-----------|-------------------|------------------|-----------|------|------|-----------|------|------|------|
|           |                   |                  | MIN       | TYP† | MAX  | MIN       | TYP† | MAX  |      |
| $V_{IK}$  | $V_{CC} = 4.5$ V, | $I_I = -18$ mA   |           |      | -1.5 |           |      | -1.5 | V    |
| $I_{OH}$  | $V_{CC} = 4.5$ V, | $V_{OH} = 5.5$ V |           |      | 0.1  |           |      | 0.1  | mA   |
| $V_{OL}$  | $V_{CC} = 4.5$ V, | $I_{OL} = 4$ mA  | 0.25      | 0.4  |      | 0.25      | 0.4  |      | V    |
|           | $V_{CC} = 4.5$ V, | $I_{OL} = 8$ mA  |           |      |      | 0.35      | 0.5  |      |      |
| $I_I$     | $V_{CC} = 5.5$ V, | $V_I = 7$ V      |           |      | 0.1  |           |      | 0.1  | mA   |
| $I_{IH}$  | $V_{CC} = 5.5$ V, | $V_I = 2.7$ V    |           |      | 20   |           |      | 20   | μA   |
| $I_{IL}$  | $V_{CC} = 5.5$ V, | $V_I = 0.4$ V    |           |      | -0.1 |           |      | -0.1 | mA   |
| $I_{CCH}$ | $V_{CC} = 5.5$ V, | $V_I = 0$ V      | 0.43      | 0.85 |      | 0.43      | 0.85 |      | mA   |
| $I_{CCL}$ | $V_{CC} = 5.5$ V, | $V_I = 4.5$ V    | 1.62      | 3    |      | 1.62      | 3    |      | mA   |

† All typical values are at  $V_{CC} = 5$  V,  $T_A = 25$  °C.

switching characteristics (see Note 1)

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | VCC = 4.5 V to 5.5 V,<br>CL = 50 pF,<br>RL = 2 kΩ,<br>TA = MIN to MAX |     |           |     | UNIT |
|-----------|-----------------|----------------|-----------------------------------------------------------------------|-----|-----------|-----|------|
|           |                 |                | SN54ALS01                                                             |     | SN74ALS01 |     |      |
|           |                 |                | MIN                                                                   | MAX | MIN       | MAX |      |
| tPLH      | A or B          | Y              | 23                                                                    | 66  | 23        | 54  | ns   |
| tPHL      | A or B          | Y              | 8                                                                     | 39  | 8         | 28  | ns   |

NOTE 1: Load circuit and voltage waveforms are shown in Section 1.