

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

3 WAY
3 POLIG

4 WAY
4 POLIG

5 WAY
5 POLIG

PCB HOLES
PCB THICKNESS 1.6mm MAX.
PCB LOCHBILD
PCB DICKE 1.6mm MAX.

11

12

13

1

2

3

4

5

6

7

14

4

3

8

9

10

12.3 ± 0.1

11.6 ± 0.1

R 1.5

5

5-1437719-4

AS SHOWN
WIE GEZEICHNET

LOC

DIST

REV

DATE

DWN

APVD

REVISIONS

DESCRIPTION

DATE

DWN

APVD

1

2

3

4

5

MATERIAL / MATERIAL: PBT, UL-94 V2

SHELL MATERIAL / GEHAUSEMATERIAL: CUZN

FINISH / BESCHICHTUNG: TRIBOR 4µm

WIRE GAGE / DRAHTGRÖSSE IN mm²: 0.25

CONTACT RESISTANCE / KONTAKTWIDERSTAND: => 5 m Ω

CODING / CODIERUNG

RATED CURRENT PER CONTACT / NENNSTROM PRO KONTAKT: 3 A

SHELL PROTECTION CLASS / SCHUTZKLASSE: IP 65 / DIN 40050

TERMINATION: SOLDERING / VERBINDUNG: LÖTKONTAKTE

TEST VOLTAGE / PRUEFSPANNUNG: 500 VAC

OPERATING VOLTAGE / BETRIEBSSPANNUNG: 60 VAC

OPERATING TEMPERATURE: -40 °C TO +80 °C / ARBEITSTEMPERATUR: -40 °C BIS +80 °C

MATING CYCLES / STECKZYKLEN: 500 MAX.

TECHNICAL DATA
TECHNISCHE DATEN

TYCO-NO./TYCO NR.

6-1437719-0

5-1437719-7

5-1437719-4

1

1

1

SEAL / DICHTUNG

14

1

PLATE 5 POS. / PLATTE 5 POL.

13

1

PLATE 4 POS. / PLATTE 4 POL.

12

1

PLATE 3 POS. / PLATTE 3 POL.

11

1

INSULATION TUBE 5 POS. / ISOLIERHUELSE 5 POL.

10

1

INSULATION TUBE 4 POS. / ISOLIERHUELSE 4 POL.

9

1

INSULATION TUBE 3 POS. / ISOLIERHUELSE 3 POL.

8

2

2

2

SOCKET APPLIED BY PRESSURE / BUCHSENKONTAKT EINGEPRESST

7

3

2

1

SOCKET APPLIED BY PRESSURE / BUCHSENKONTAKT EINGEPRESST

6

1

1

1

NUT / MUTTER

5

1

1

1

SEAL / DICHTUNG

4

1

1

1

SEAL / DICHTUNG

3

1

1

1

HOUSING / GEHAUSE

2

1

1

1

GROUND ON PCB SPRING / VERBINDUNGSFEDER ZUR PCB MASSE

1

-

-

-

REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REV.)

QTY REQD PER ASSY

T01-0560-S05

T01-0560-S04

T01-0560-S03

DESCRIPTION /
BESCHREIBUNG

ITEM-NO.
TEIL-NR.

PARTS LIST /
TEILE LISTE

CATALOG-NO.

CATALOG-NO.

CATALOG-NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
N. GEISTER
18JUN2001

CHK
H. SCHERER
18JUN2001

APVD
G. FELDMEIER
18JUN2001

NAME
T01 FEMALE PLUG CONN. PANEL MNT. PCB VER, 3-5 POS. 90 DGR,
T01 BUCHSENSTECKER, EINBAU, PCB VERSION 3-5 POL, 90 GRAD

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± 0.3

1 PLC ± 0.3

2 PLC ± 0.3

3 PLC ± 0.3

4 PLC ± 0.3

ANGLES ± 1°

MATERIAL

5

FINISH

-

WEIGHT

-

RESTRICTED TO

-

RESTRICTED CUSTOMER

SCALE 1:1

SHEET 1 OF 1

REV A2

SIZE
A1

CAGE CODE
00779

DRAWING NO
5-1437719-4

TE Connectivity

4805 (3/11)