


Features

1. High current transfer ratio
(CTR:MIN.500% at $I_F=1.6\text{mA}$)
2. High speed response
(t_{PHL} .TYP.0.2 μs at $R=270\Omega$)
3. High common mode rejection
voltage (CM_H .TYP500V/ μs)
4. TTL compatible output

Applications


1. Interfaces for computer peripherals
2. Computers, measuring instruments,
control equipment
3. Telephone sets.
4. Signal transmission between circuits of
different potentials and impedances.

Outside Dimension:Unit (mm)



Tolerance:±0.2 mm

Schematic:Top View



Absolute Maximum Ratings

(Ta=25°C)

Parameter	Symbol	Rating	Unit
Input	Forward current	20	mA
	*1 Peak forward current	40	mA
	*2 Peak transient forward current	1	A
	Reverse voltage	5	V
	Power dissipation	35	mW
Output	Supply voltage	-0.5 to 18	V
	Output voltage	-0.5 to 18	V
	Emitter-base reverse withstand voltage (Pin 5 to 7)	0.5	V
	*3 Average output current	60	mA
	Power dissipation	100	mW
*4 Isolation voltage	Viso	2500	Vrms
Operating temperature	Topr	0 to +70	°C
Storage temperature	Tstg	-55 to +125	°C
*5 Soldering temperature	Tsol	260	°C

*1 50% duty cycle,Pulse width : 1ms



*2 Pulse width≤1 μs ,300pps

*3 Decreases at the rate of 0.7mA/°C if the external temperature is more than 25°C.



*4 40 to 60% RH,AC for 1 minute

*5 For 10 seconds

*8 Tset Circuit Propagation Delay Time



*10 Tset Circuit for Instantaneous Common Mode Rejection Voltage



Electro-optical Characteristics

(Ta=0 to +70°C unless otherwise specified)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
*6 Current transfer ratio	CTR(1)	I _F =0.5mA, V _O =0.4V, V _{CC} =4.5V	400	1800	-	%
	CTR(2)	I _F =1.6mA, V _O =0.4V, V _{CC} =4.5V	500	1600	-	%
Logic (0) output voltage	V _{OL} (1)	I _F =6.4mA, I _O =1.6mA, V _{CC} =4.5V	-	0.1	0.4	V
	V _{OL} (2)	I _F =5mA, I _O =15mA, V _{CC} =4.5V	-	0.1	0.4	V
	V _{OL} (3)	I _F =12mA, I _O =24mA, V _{CC} =4.5V	-	0.1	0.4	V
Logic (1) output current	I _{OH}	I _F =0, V _{CC} =V _O =18V	-	0.05	100	μA
Logic (0) supply current	I _{CCL}	I _F =1.6mA, V _{CC} =5V, V _O =open	-	0.5	-	mA
Logic (1) supply current	I _{CCH}	I _F =0, V _{CC} =5V, V _O =open	-	10	-	nA
Input forward voltage	V _F	I _F =1.6mA, Ta=25°C	-	1.5	1.7	V
Input forward voltage temperature coefficient	ΔV _F /ΔTa	I _F =1.6mA	-	-1.9	-	mV/°C
Input reverse voltage	BV _R	I _R =10μA, Ta=25°C	5.0	-	-	V
Input capacitance	C _{IN}	V _F =0, f=1MHz	-	60	-	pF
*7 Leak current(input-output)	I _{I-O}	V _{I-O} =3kV DC, 45%RH, t=5s, Ta=25°C	-	-	1.0	μA
*7 Isolation resistance(input-output)	R _{I-O}	V _{I-O} =500V DC	-	10 ¹²	-	Ω
*7 Capacitance(input-output)	C _{I-O}	f=1MHz	-	0.6	-	pF

*6 Current transfer ratio is a ratio of
input current and output current expressed in %.

*7 Measured as 2-pin element (Short 1, 2, 3, 4 and 5, 6, 7, 8)

Switching Characteristics

(Ta=25°C, V_{CC}=5V)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
*8 Propagation delay time Output (1)→(0)	t _{PHL}	R _L =4.7kΩ, I _F =0.5mA	-	5	25	μS
		R _L =270Ω, I _F =12mA	-	0.3	1	μS
*8 Propagation delay time Output (0)→(1)	t _{PLH}	R _L =4.7kΩ, I _F =0.5mA	-	10	60	μS
		R _L =270Ω, I _F =12mA	-	1.5	7	μS
*9 *10 Instantaneous common mode rejection voltage "Output (1)"	CM _H	I _F =0, V _{CM} =10V _{p-p} , R _L =2.2kΩ	-	500	-	V/μS
*9 *10 Instantaneous common mode rejection voltage "Output (0)"	CM _L	I _F =1.6mA, V _{CM} =10V _{p-p} , R _L =2.2kΩ	-	-500	-	V/μS

*9 Instantaneous common mode rejection voltage "output(1)" represents a common voltage variation that can hold the output above (1) level (V_O>2.0V).

*10 Instantaneous common mode rejection voltage "output(1)" represents a common voltage variation that can hold the output above (0) level (V_O<0.8V).