# SERIES 714...01X • .100" GRID ULTRA LOW PROFILE CARRIERS • SINGLE AND DOUBLE ROW STRIPS




**FIG. 1**




**FIG. 2**




**FIG. 3**




**FIG. 4**

- Ultra low profile receptacles sit .018" above the board
- Series 714 use MM #0552-1 and MM #0552-2 pin receptacles. See page 158 for details
- Hi-Rel, 3-finger BeCu #11 contact is rated at 3 amps. See page 251 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



## ORDERING INFORMATION

| | |
|---|---|
| **FIG. 1** | **Single Row (.039" min. mounting hole)**<br>714-XX-1__-31-012000<br>**Specify number of pins** 01-64 |
| **FIG. 2** | **Single Row (.039" min. mounting hole)**<br>714-XX-1__-31-018000<br>**Specify number of pins** 01-64 |
| **FIG. 3** | **Double Row (.039" min. mounting hole)**<br>714-XX-2__-31-012000<br>**Specify number of pins** 04-64 |
| **FIG. 4** | **Double Row (.039" min. mounting hole)**<br>714-XX-2__-31-018000<br>**Specify number of pins** 04-64 |

RoHS-2 2011/65/EU

XX=Plating Code See Below

*For Electrical, Mechanical & Enviromental Data, See page 264*

| SPECIFY PLATING CODE XX= | | 91 | 93 | | 41 ◆ | 43 ◆ | |
|---|---|---|---|---|---|---|---|
| Sleeve (Pin) | | 200 µ" Sn/Pb | 200 µ" Sn/Pb | | 200 µ" Sn | 200 µ" Sn | |
| Contact (Clip) | | 10 µ" Au | 30 µ" Au | | 10 µ" Au | 30 µ" Au | |



MILL-MAX® Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com