




RECOMMEND P.C.B. HOLES



CIRCUIT: SPST

CONTACT CONFIGURATION

NOTES:

1. ALL DIMENSIONS IN MM
2. TERM. NOS. FOR REF ONLY
3. RATING: DC 12V, 50mA
4. TRAVEL: 0.25±0.1mm
5. CONTACT RESISTANCE: 100m Ohms Max.
6. MECHANICAL/ELECTRICAL LIFE: 30,000 CYCLES
7. PACKAGE: BULK 1,000 PER BAG
8. 2002/95/EC (ROHS) COMPLIANT
9. OPERATING FORCE: 260 GRAMS



D	ADDED NOTE 9	10/15/14	AS
C	UPDATED NOTES	11/7/06	TN
B	REVISED & REDRAWN		
REV.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TOLERANCES			
0.0	±0.4		
0.00	±0.25		

TITLE			
TL1107AF260W			
SCALE	DATE	DR	DWG
4:1	11/7/06	TN	P010313
			REV
			D