

		<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th colspan="4" style="text-align: center;">REVISIONS</th> </tr> <tr> <th>REV</th> <th>ECR NO</th> <th>DESCRIPTION</th> <th>DATE</th> </tr> </thead> <tbody> <tr> <td>A</td> <td>23737</td> <td>NEW RELEASE</td> <td>08/19/04</td> </tr> </tbody> </table> <div style="border: 1px solid black; padding: 10px; margin-top: 10px;"> </div> <p>NOTES:</p> <ol style="list-style-type: none"> 1- ALL DIMENSIONS ARE IN INCHES 2- FILAMENT SHAPE MUST BE UNIFORM, WITH COILS EVENLY SPACED AND FREE OF TWIST OR SHORTING 3- LAMPS SHALL BE CLEAN WITH NO FOREIGN MATERIALS OR GLASS CHIPS INSIDE 4- LAMP ENVELOPE SHALL BE CLEAR AND FREE OF BUBBLES, SCRATCHES, OR DISCOLORATION 5- CLEAR GLASS PROPERLY ANNEALED, SHALL BE UNIFORM IN SHAPE AND SUBSTANTIALLY FREE OF PRISMATIC ACTION 6- LAMPS SHALL BE CAPABLE OF OPERATION AND STORAGE FROM -65° TO 80°C WITHOUT DEGRADATION 7- LAMPS SHALL BE PROPERLY PACKAGED IN CONTAINERS SUITABLE TO PREVENT ANY DAMAGE DURING SHIPMENT 8- MFR'S IDENTIFICATION AND BULB NUMBER TO APPEAR ON THE GLASS WITHIN THIS LENGTH 9- BULBS MUST COMPLY WITH SAE/USCAR-3 10- PARTS TO BE LEAD FREE. 	REVISIONS				REV	ECR NO	DESCRIPTION	DATE	A	23737	NEW RELEASE	08/19/04																													
REVISIONS																																											
REV	ECR NO	DESCRIPTION	DATE																																								
A	23737	NEW RELEASE	08/19/04																																								
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 50%;">CML PART NO.</td> <td style="width: 50%;">192HLF</td> </tr> <tr> <td>DESIGN VOLTAGE</td> <td>13.0</td> </tr> <tr> <td>DESIGN AMPS</td> <td>0.33 ± 10%</td> </tr> <tr> <td>CANDLE POWER (APPROX.)</td> <td>3.0 ± .20%</td> </tr> <tr> <td>RATED LIFE HOURS</td> <td>1000</td> </tr> <tr> <td>FILAMENT SHAPE</td> <td>C-2V</td> </tr> </table> <p style="text-align: center;">SDRC FILE NAME: B18566</p>	CML PART NO.	192HLF	DESIGN VOLTAGE	13.0	DESIGN AMPS	0.33 ± 10%	CANDLE POWER (APPROX.)	3.0 ± .20%	RATED LIFE HOURS	1000	FILAMENT SHAPE	C-2V	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td colspan="2" style="text-align: center;">DIM ARE IN INCHES</td> <td colspan="2" style="text-align: center;"><input checked="" type="checkbox"/> FOR INSPECTION USE ONLY <input type="checkbox"/> SPC DOCUMENTATION REQ. (X R CHARTS)</td> </tr> <tr> <td style="text-align: center;">DRAWN BY RHM</td> <td style="text-align: center;">DATE 8/19/04</td> <td style="text-align: center;">PART NO 192HLF</td> <td rowspan="2" style="text-align: center; vertical-align: middle;"> CHICAGO MINIATURE LAMP, INC. 147 CENTRAL AVE. HACKENSACK, NJ 07601 </td> </tr> <tr> <td style="text-align: center;">CHECKED BY T-3 1/4 8/20/04</td> <td style="text-align: center;">DATE</td> <td style="text-align: center;">MODEL NO</td> </tr> <tr> <td style="text-align: center;">ENG. APPRV. Hans S. 8/20/04</td> <td style="text-align: center;">DATE</td> <td style="text-align: center;">MOLD NO</td> </tr> <tr> <td colspan="2" style="text-align: center;">UNLESS OTHERWISE SPECIFIED</td> <td style="text-align: center;">TITLE T-3 1/4 WEDGE BASE LAMP</td> </tr> <tr> <td colspan="2" style="text-align: center;">TOLERANCES ON: +/- .015</td> <td style="text-align: center;">MATERIAL</td> </tr> <tr> <td colspan="2" style="text-align: center;">ANGLE +/-. 5 DEG.</td> <td style="text-align: center;">FINISH</td> </tr> <tr> <td style="text-align: center;">DIST. V/S</td> <td style="text-align: center;">DWG NO B18566</td> <td style="text-align: center;">REV A</td> </tr> <tr> <td colspan="2" style="text-align: center;">SCALE 3:1</td> <td style="text-align: center;">SHEET</td> </tr> </table>	DIM ARE IN INCHES		<input checked="" type="checkbox"/> FOR INSPECTION USE ONLY <input type="checkbox"/> SPC DOCUMENTATION REQ. (X R CHARTS)		DRAWN BY RHM	DATE 8/19/04	PART NO 192HLF	 CHICAGO MINIATURE LAMP, INC. 147 CENTRAL AVE. HACKENSACK, NJ 07601	CHECKED BY T-3 1/4 8/20/04	DATE	MODEL NO	ENG. APPRV. Hans S. 8/20/04	DATE	MOLD NO	UNLESS OTHERWISE SPECIFIED		TITLE T-3 1/4 WEDGE BASE LAMP	TOLERANCES ON: +/- .015		MATERIAL	ANGLE +/-. 5 DEG.		FINISH	DIST. V/S	DWG NO B18566	REV A	SCALE 3:1		SHEET	
CML PART NO.	192HLF																																										
DESIGN VOLTAGE	13.0																																										
DESIGN AMPS	0.33 ± 10%																																										
CANDLE POWER (APPROX.)	3.0 ± .20%																																										
RATED LIFE HOURS	1000																																										
FILAMENT SHAPE	C-2V																																										
DIM ARE IN INCHES		<input checked="" type="checkbox"/> FOR INSPECTION USE ONLY <input type="checkbox"/> SPC DOCUMENTATION REQ. (X R CHARTS)																																									
DRAWN BY RHM	DATE 8/19/04	PART NO 192HLF	 CHICAGO MINIATURE LAMP, INC. 147 CENTRAL AVE. HACKENSACK, NJ 07601																																								
CHECKED BY T-3 1/4 8/20/04	DATE	MODEL NO																																									
ENG. APPRV. Hans S. 8/20/04	DATE	MOLD NO																																									
UNLESS OTHERWISE SPECIFIED		TITLE T-3 1/4 WEDGE BASE LAMP																																									
TOLERANCES ON: +/- .015		MATERIAL																																									
ANGLE +/-. 5 DEG.		FINISH																																									
DIST. V/S	DWG NO B18566	REV A																																									
SCALE 3:1		SHEET																																									

ORIGINAL
WHEN RED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Chicago Miniature:](#)

[192HLF](#)