

## Surface Mount Multilayer Ceramic Chip Capacitors for Commercial Applications



### FEATURES

- C0G (NP0) and X7R dielectrics offered
- C0G (NP0) is an ultra-stable dielectric offering a very low Temperature Coefficient of Capacitance (TCC)
- C0G (NP0) offers low dissipation
- Excellent aging characteristics
- Ideal for decoupling and filtering (X7R)
- Ideal for surge suppression and high voltage applications
- Wide range of case sizes, voltage ratings and capacitance values
- Wet build process
- Reliable Noble Metal Electrode (NME) system
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)  
Available

### APPLICATIONS

- Timing and tuning circuits
- Sensor and scanner applications
- Decoupling and filtering
- Surge suppression

### ELECTRICAL SPECIFICATIONS

#### COG (NP0) DIELECTRIC

##### GENERAL SPECIFICATION

###### Note

Electrical characteristics at +25 °C unless otherwise specified

**Operating Temperature:** -55 °C to +150 °C  
(above +125 °C changed characteristics)

**Capacitance Range:** 1 pF to 56 nF

**Voltage Range:** 25 V<sub>DC</sub> to 1000 V<sub>DC</sub>

**Temperature Coefficient of Capacitance (TCC):**  
0 ppm/°C ± 30 ppm/°C from -55 °C to +125 °C

##### Dissipation Factor (DF):

0.1 % maximum at 1.0 V<sub>RMS</sub> and  
1 MHz for values ≤ 1000 pF

0.1 % maximum at 1.0 V<sub>RMS</sub> and  
1 kHz for values > 1000 pF

##### Insulating Resistance:

at +25 °C 100 000 MΩ min. or 1000 ΩF whichever is less  
at +125 °C 10 000 MΩ min. or 100 ΩF whichever is less

**Aging Rate:** 0 % maximum per decade

##### Dielectric Strength Test:

performed per method 103 of EIA 198-2-E.

Applied test voltages

|                                                    |                        |
|----------------------------------------------------|------------------------|
| ≤ 200 V <sub>DC</sub> -rated:                      | 250 % of rated voltage |
| 500 V <sub>DC</sub> -rated:                        | 200 % of rated voltage |
| 630 V <sub>DC</sub> , 1000 V <sub>DC</sub> -rated: | 150 % of rated voltage |

#### X7R DIELECTRIC

##### GENERAL SPECIFICATION

###### Note

Electrical characteristics at +25 °C unless otherwise specified

**Operating Temperature:** -55 °C to +150 °C  
(above +125 °C changed characteristics)

**Capacitance Range:** 120 pF to 6.8 μF

**Voltage Range:** 16 V<sub>DC</sub> to 1000 V<sub>DC</sub>

**Temperature Coefficient of Capacitance (TCC):**  
± 15 % from -55 °C to +125 °C, with 0 V<sub>DC</sub> applied

##### Dissipation Factor (DF):

16 V / 25 V ratings: 3.5 % maximum at 1.0 V<sub>RMS</sub> and 1 kHz  
> 25 V ratings: 2.5 % maximum at 1.0 V<sub>RMS</sub> and 1 kHz

##### Insulating Resistance:

at +25 °C 100 000 MΩ min. or 1000 ΩF whichever is less  
at +125 °C 10 000 MΩ min. or 100 ΩF whichever is less

**Aging Rate:** 1 % maximum per decade

##### Dielectric Strength Test:

performed per method 103 of EIA 198-2-E.

Applied test voltages

|                                                    |                             |
|----------------------------------------------------|-----------------------------|
| ≤ 250 V <sub>DC</sub> -rated:                      | 250 % of rated voltage      |
| 500 V <sub>DC</sub> -rated:                        | min. 150 % of rated voltage |
| 630 V <sub>DC</sub> , 1000 V <sub>DC</sub> -rated: | min. 120 % of rated voltage |



| QUICK REFERENCE DATA |      |                     |             |             |
|----------------------|------|---------------------|-------------|-------------|
| DIELECTRIC           | CASE | MAXIMUM VOLTAGE (V) | CAPACITANCE |             |
|                      |      |                     | MINIMUM     | MAXIMUM     |
| C0G (NP0)            | 0402 | 100                 | 1.0 pF      | 220 pF      |
|                      | 0603 | 250                 | 1.0 pF      | 1.0 nF      |
|                      | 0805 | 500                 | 1.0 pF      | 4.7 nF      |
|                      | 1206 | 630                 | 1.0 pF      | 10 nF       |
|                      | 1210 | 630                 | 56 pF       | 12 nF       |
|                      | 1808 | 1000                | 27 pF       | 10 nF       |
|                      | 1812 | 1000                | 27 pF       | 22 nF       |
|                      | 1825 | 500                 | 100 pF      | 39 nF       |
|                      | 2220 | 1000                | 270 pF      | 47 nF       |
|                      | 2225 | 1000                | 270 pF      | 56 nF       |
| X7R                  | 0402 | 100                 | 120 pF      | 47 nF       |
|                      | 0603 | 200                 | 330 pF      | 150 nF      |
|                      | 0805 | 250                 | 330 pF      | 470 nF      |
|                      | 1206 | 630                 | 330 pF      | 1.0 $\mu$ F |
|                      | 1210 | 630                 | 390 pF      | 1.0 $\mu$ F |
|                      | 1808 | 1000                | 470 pF      | 270 nF      |
|                      | 1812 | 1000                | 1.0 nF      | 1.0 $\mu$ F |
|                      | 1825 | 1000                | 10 nF       | 2.7 $\mu$ F |
|                      | 2220 | 500                 | 15 nF       | 2.2 $\mu$ F |
|                      | 2225 | 1000                | 33 nF       | 4.7 $\mu$ F |
|                      | 3640 | 500                 | 27 nF       | 6.8 $\mu$ F |

**Note**

- Detail ratings see “Selection Chart”




| ORDERING INFORMATION                                                                 |                          |                                                                                                                                                     |                                                                                                                                                                                                                                                 |                                                                                                                                                    |                                                                                                                 |                                                                                                                          |                                                                                                                                                                                                                                                                                                                 |                       |
|--------------------------------------------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|
| VJ0805 <sup>(1)</sup>                                                                | Y                        | 102                                                                                                                                                 | K                                                                                                                                                                                                                                               | X                                                                                                                                                  | A                                                                                                               | A                                                                                                                        | T                                                                                                                                                                                                                                                                                                               | ### <sup>(3)(6)</sup> |
| CASE CODE                                                                            | DIELECTRIC               | CAPACITANCE NOMINAL CODE                                                                                                                            | CAPACITANCE TOLERANCE                                                                                                                                                                                                                           | TERMINATION                                                                                                                                        | DC VOLTAGE RATING <sup>(2)</sup>                                                                                | MARKING                                                                                                                  | PACKAGING                                                                                                                                                                                                                                                                                                       | PROCESS CODE          |
| 0402<br>0603<br>0805<br>1206<br>1210<br>1808<br>1812<br>1825<br>2220<br>2225<br>3640 | A = C0G (NP0)<br>Y = X7R | Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier.<br><b>Examples:</b><br>1R8 = 1.8 pF<br>102 = 1000 pF | B = $\pm 0.10$ pF<br>C = $\pm 0.25$ pF<br>D = $\pm 0.5$ pF<br>F = $\pm 1$ %<br>G = $\pm 2$ %<br>J = $\pm 5$ %<br>K = $\pm 10$ %<br>M = $\pm 20$ %<br><b>Note</b><br>C0G (NP0):<br>B, C, D < 10 pF<br>F, G, J, K $\geq 10$ pF<br>X7R:<br>J, K, M | X = Ni barrier<br>100 % tin plated<br>matte finish<br>F, E = AgPd <sup>(4)</sup><br>B = polymer<br>100 % tin plated<br>matte finish <sup>(5)</sup> | J = 16 V<br>X = 25 V<br>A = 50 V<br>B = 100 V<br>C = 200 V<br>P = 250 V<br>E = 500 V<br>L = 630 V<br>G = 1000 V | A = unmarked<br>M = marked<br><b>Note</b><br>Marking is only available for 0805 and 1206 with termination code "X" / "B" | C = 7" reel / paper tape<br>T = 7" reel / plastic tape<br>P = 11 1/4" / 13" reel / paper tape<br>R = 11 1/4" / 13" reel / plastic tape<br>O = 7" reel / flamed paper tape<br>I = 11 1/4" / 13" reel / flamed paper tape<br><b>Note</b><br>"I" and "O" are used for "F", "E" termination size 0402 / 0603 / 0805 |                       |

**Notes**

- (1) Case size designator may be replaced by four digit drawing number used to control non-standard products and / or special requirements
- (2) DC voltage rating should not be exceeded in application. Other application factors may affect the MLCC performance. Consult for questions: [mlcc@vishay.com](mailto:mlcc@vishay.com)
- (3) Process code may be added with up to three digits, used to control non-standard products and / or special requirements
- (4) Termination code "E" is for conductive epoxy assembly
- (5) Polymer termination for size 0603 and larger. Packaging only in plastic tape "T" / "R"
- (6) Variable plastic / paper tape, see ratings in "Selection Charts"

| ENVIRONMENTAL STATUS |                                              |                |              |
|----------------------|----------------------------------------------|----------------|--------------|
| TERMINATION CODE     | TERMINATION DESCRIPTION                      | RoHS COMPLIANT | VISHAY GREEN |
| X                    | Ni barrier 100 % tin plated matte finish     | Yes            | Yes          |
| E                    | AgPd                                         | Yes            | Yes          |
| B                    | Polymer layer, 100 % tin plated matte finish | Yes            | No           |
| F                    | AgPd                                         | Yes            | No           |

## DIMENSIONS in inches (millimeters)



| CASE CODE | STYLE  | LENGTH<br>(L)                                     | WIDTH<br>(W)                                      | MAXIMUM<br>THICKNESS<br>(T) | TERMINATION<br>(P) |                 |
|-----------|--------|---------------------------------------------------|---------------------------------------------------|-----------------------------|--------------------|-----------------|
|           |        |                                                   |                                                   |                             | MINIMUM            | MAXIMUM         |
| 0402      | VJ0402 | 0.040 + 0.004 / - 0.002<br>(1.00 + 0.10 / - 0.05) | 0.020 + 0.004 / - 0.002<br>(0.50 + 0.10 / - 0.05) | 0.024<br>(0.60)             | 0.004<br>(0.10)    | 0.016<br>(0.41) |
| 0603      | VJ0603 | 0.063 ± 0.006<br>(1.60 ± 0.15)                    | 0.031 ± 0.006<br>(0.80 ± 0.15)                    | 0.038<br>(0.97)             | 0.012<br>(0.30)    | 0.022<br>(0.55) |
| 0805      | VJ0805 | 0.079 ± 0.008<br>(2.00 ± 0.20)                    | 0.049 ± 0.008<br>(1.25 ± 0.20)                    | 0.057<br>(1.45)             | 0.010<br>(0.25)    | 0.030<br>(0.76) |
| 1206      | VJ1206 | 0.126 ± 0.010<br>(3.20 ± 0.25)                    | 0.063 ± 0.010<br>(1.60 ± 0.25)                    | 0.067<br>(1.70)             | 0.010<br>(0.25)    | 0.030<br>(0.76) |
| 1210      | VJ1210 | 0.126 ± 0.010<br>(3.20 ± 0.25)                    | 0.098 ± 0.010<br>(2.50 ± 0.25)                    | 0.067<br>(1.70)             | 0.010<br>(0.25)    | 0.030<br>(0.76) |
| 1808      | VJ1808 | 0.180 ± 0.012<br>(4.57 ± 0.30)                    | 0.080 ± 0.010<br>(2.03 ± 0.25)                    | 0.086<br>(2.18)             | 0.010<br>(0.25)    | 0.035<br>(0.90) |
| 1812      | VJ1812 | 0.177 ± 0.012<br>(4.50 ± 0.30)                    | 0.126 ± 0.008<br>(3.20 ± 0.20)                    | 0.086<br>(2.18)             | 0.010<br>(0.25)    | 0.035<br>(0.90) |
| 1825      | VJ1825 | 0.177 ± 0.012<br>(4.50 ± 0.30)                    | 0.252 ± 0.010<br>(6.40 ± 0.25)                    | 0.086<br>(2.18)             | 0.010<br>(0.25)    | 0.035<br>(0.90) |
| 2220      | VJ2220 | 0.220 ± 0.010<br>(5.59 ± 0.25)                    | 0.200 ± 0.010<br>(5.08 ± 0.25)                    | 0.086<br>(2.18)             | 0.010<br>(0.25)    | 0.037<br>(0.95) |
| 2225      | VJ2225 | 0.220 ± 0.010<br>(5.59 ± 0.25)                    | 0.250 ± 0.010<br>(6.35 ± 0.25)                    | 0.086<br>(2.18)             | 0.010<br>(0.25)    | 0.037<br>(0.95) |
| 3640      | VJ3640 | 0.360 ± 0.015<br>(9.14 ± 0.38)                    | 0.400 ± 0.015<br>(10.20 ± 0.38)                   | 0.086<br>(2.18)             | 0.010<br>(0.25)    | 0.039<br>(1.00) |

### Note

- Polymer (B-termination) have increased dimensions:  
length 0.006"(0.15 mm)



| SELECTION CHART            |        |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
|----------------------------|--------|-----------|----|-----|--------|-----|-----|-----|--------|-----|-----|-----|-----------------------|-----|-----|-----|-----|-----------------------|-----|-----|-----|-----|
| DIELECTRIC                 |        | C0G (NP0) |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| STYLE                      |        | VJ0402    |    |     | VJ0603 |     |     |     | VJ0805 |     |     |     | VJ1206 <sup>(1)</sup> |     |     |     |     | VJ1210 <sup>(1)</sup> |     |     |     |     |
| CASE CODE                  |        | 0402      |    |     | 0603   |     |     |     | 0805   |     |     |     | 1206                  |     |     |     |     | 1210                  |     |     |     |     |
| VOLTAGE (V <sub>DC</sub> ) |        | 25        | 50 | 100 | 50     | 100 | 200 | 250 | 50     | 100 | 200 | 500 | 50                    | 100 | 200 | 500 | 630 | 50                    | 100 | 200 | 500 | 630 |
| VOLTAGE CODE               |        | X         | A  | B   | A      | B   | C   | P   | A      | B   | C   | E   | A                     | B   | C   | E   | L   | A                     | B   | C   | E   | L   |
| CAP. CODE                  | CAP.   |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 1R0                        | 1.0 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 1R2                        | 1.2 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 1R5                        | 1.5 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 1R8                        | 1.8 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 2R2                        | 2.2 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 2R7                        | 2.7 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 3R3                        | 3.3 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 3R9                        | 3.9 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 4R7                        | 4.7 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 5R6                        | 5.6 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 6R8                        | 6.8 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 8R2                        | 8.2 pF | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 100                        | 10 pF  | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 120                        | 12 pF  | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 150                        | 15 pF  | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 180                        | 18 pF  | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 220                        | 22 pF  | ••        | •• | ••  | ••     | ••  | ••  | ••  | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 270                        | 27 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 330                        | 33 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 390                        | 39 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 470                        | 47 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     |     |     |
| 560                        | 56 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     | •   | •   |
| 680                        | 68 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     | •   | •   |
| 820                        | 82 pF  | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | ••                    | ••  | ••  | ••  | ••  |                       |     |     | •   | •   |
| 101                        | 100 pF | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | •                     | •   | •   | •   | •   |                       |     |     | •   | •   |
| 121                        | 120 pF | ••        | •• | ••  | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 151                        | 150 pF | ••        | •• |     | ••     | ••  | ••  |     | ••     | ••  | ••  | ••  | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 181                        | 180 pF | ••        | •• |     | ••     | ••  | •   |     | ••     | ••  | ••  | ••  | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 221                        | 220 pF | ••        | •• |     | ••     | ••  | •   |     | ••     | ••  | ••  | •   | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 271                        | 270 pF |           |    |     | ••     | ••  | •   |     | ••     | ••  | ••  | •   | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 331                        | 330 pF |           |    |     | ••     | ••  |     |     | ••     | ••  | ••  | •   | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 391                        | 390 pF |           |    |     | ••     | ••  |     |     | ••     | ••  | ••  | •   | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 471                        | 470 pF |           |    |     | ••     |     |     |     | ••     | ••  | •   | •   | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 561                        | 560 pF |           |    |     | ••     |     |     |     | ••     | ••  | •   |     | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 681                        | 680 pF |           |    |     | ••     |     |     |     | ••     | ••  | •   |     | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 821                        | 820 pF |           |    |     | ••     |     |     |     | ••     | ••  | •   |     | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 102                        | 1.0 nF |           |    |     | ••     |     |     |     | ••     | ••  | •   |     | •                     | •   | •   | •   | •   | •                     | •   | •   | •   | •   |
| 122                        | 1.2 nF |           |    |     |        |     |     |     | ••     | •   |     |     | •                     | •   | •   |     |     | •                     | •   | •   | •   | •   |
| 152                        | 1.5 nF |           |    |     |        |     |     |     | ••     | •   |     |     | •                     | •   | •   |     |     | •                     | •   | •   | •   | •   |
| 182                        | 1.8 nF |           |    |     |        |     |     |     | •      |     |     |     | •                     | •   | •   |     |     | •                     | •   | •   | •   | •   |
| 222                        | 2.2 nF |           |    |     |        |     |     |     | •      |     |     |     | •                     | •   | •   |     |     | •                     | •   | •   |     | •   |
| 272                        | 2.7 nF |           |    |     |        |     |     |     | •      |     |     |     | •                     | •   | •   |     |     | •                     | •   | •   |     |     |
| 332                        | 3.3 nF |           |    |     |        |     |     |     | •      |     |     |     | •                     | •   | •   |     |     | •                     | •   | •   |     |     |
| 392                        | 3.9 nF |           |    |     |        |     |     |     | •      |     |     |     | •                     | •   |     |     |     | •                     | •   | •   |     |     |
| 472                        | 4.7 nF |           |    |     |        |     |     |     | •      |     |     |     | •                     | •   |     |     |     | •                     | •   | •   |     |     |
| 562                        | 5.6 nF |           |    |     |        |     |     |     |        |     |     |     | •                     | •   |     |     |     | •                     | •   | •   |     |     |
| 682                        | 6.8 nF |           |    |     |        |     |     |     |        |     |     |     | •                     | •   |     |     |     | •                     | •   | •   |     |     |
| 822                        | 8.2 nF |           |    |     |        |     |     |     |        |     |     |     | •                     | •   |     |     |     | •                     | •   | •   |     |     |
| 103                        | 10 nF  |           |    |     |        |     |     |     |        |     |     |     | •                     | •   |     |     |     | •                     | •   |     |     |     |
| 123                        | 12 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     | •                     | •   |     |     |     |
| 153                        | 15 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 183                        | 18 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 223                        | 22 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 273                        | 27 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 333                        | 33 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 393                        | 39 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 473                        | 47 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |
| 563                        | 56 nF  |           |    |     |        |     |     |     |        |     |     |     |                       |     |     |     |     |                       |     |     |     |     |

## Notes

•• RoHS-compliant

•• Paper tape • Plastic tape

<sup>(1)</sup> See soldering recommendations within this data book, or visit [www.vishay.com/doc?45034](http://www.vishay.com/doc?45034)



## SELECTION CHART

| DIELECTRIC                 |        | COG (NP0)             |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
|----------------------------|--------|-----------------------|-----|-----|-----|------|-----------------------|-----|-----|-----|------|-----------------------|-----|-----|-----|
| STYLE                      |        | VJ1808 <sup>(1)</sup> |     |     |     |      | VJ1812 <sup>(1)</sup> |     |     |     |      | VJ1825 <sup>(1)</sup> |     |     |     |
| CASE CODE                  |        | 1808                  |     |     |     |      | 1812                  |     |     |     |      | 1825                  |     |     |     |
| VOLTAGE (V <sub>DC</sub> ) |        | 50                    | 100 | 200 | 500 | 1000 | 50                    | 100 | 200 | 500 | 1000 | 50                    | 100 | 200 | 500 |
| VOLTAGE CODE               |        | A                     | B   | C   | E   | G    | A                     | B   | C   | E   | G    | A                     | B   | C   | E   |
| CAP. CODE                  | CAP.   |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 1R0                        | 1.0 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 1R2                        | 1.2 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 1R5                        | 1.5 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 1R8                        | 1.8 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 2R2                        | 2.2 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 2R7                        | 2.7 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 3R3                        | 3.3 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 3R9                        | 3.9 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 4R7                        | 4.7 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 5R6                        | 5.6 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 6R8                        | 6.8 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 8R2                        | 8.2 pF |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 100                        | 10 pF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 120                        | 12 pF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 150                        | 15 pF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 180                        | 18 pF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 220                        | 22 pF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 270                        | 27 pF  |                       |     | •   |     | •    |                       |     |     |     | •    |                       |     |     |     |
| 330                        | 33 pF  |                       |     | •   |     | •    |                       |     |     |     |      |                       |     |     |     |
| 390                        | 39 pF  |                       |     | •   |     | •    | •                     | •   | •   | •   | •    |                       |     |     |     |
| 470                        | 47 pF  |                       |     | •   |     | •    | •                     | •   | •   | •   | •    |                       |     |     |     |
| 560                        | 56 pF  |                       |     | •   |     | •    | •                     | •   | •   | •   | •    |                       |     |     |     |
| 680                        | 68 pF  |                       |     | •   |     | •    | •                     | •   | •   | •   | •    |                       |     |     |     |
| 820                        | 82 pF  |                       |     | •   |     | •    | •                     | •   | •   | •   | •    |                       |     |     |     |
| 101                        | 100 pF |                       |     | •   |     | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 121                        | 120 pF |                       |     | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 151                        | 150 pF |                       |     | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 181                        | 180 pF |                       |     | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 221                        | 220 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 271                        | 270 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 331                        | 330 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 391                        | 390 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 471                        | 470 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 561                        | 560 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 681                        | 680 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 821                        | 820 pF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    |                       |     |     | •   |
| 102                        | 1.0 nF | •                     | •   | •   | •   | •    | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 122                        | 1.2 nF | •                     | •   | •   | •   |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 152                        | 1.5 nF | •                     | •   | •   | •   |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 182                        | 1.8 nF | •                     | •   | •   | •   |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 222                        | 2.2 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 272                        | 2.7 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 332                        | 3.3 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 392                        | 3.9 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 472                        | 4.7 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 562                        | 5.6 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 682                        | 6.8 nF | •                     | •   | •   |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 822                        | 8.2 nF | •                     | •   |     |     |      | •                     | •   | •   | •   | •    | •                     | •   | •   | •   |
| 103                        | 10 nF  | •                     |     |     |     |      | •                     | •   | •   | •   |      | •                     | •   | •   | •   |
| 123                        | 12 nF  |                       |     |     |     |      | •                     | •   | •   | •   |      | •                     | •   | •   |     |
| 153                        | 15 nF  |                       |     |     |     |      | •                     | •   |     |     |      | •                     | •   | •   |     |
| 183                        | 18 nF  |                       |     |     |     |      | •                     |     |     |     |      | •                     | •   | •   |     |
| 223                        | 22 nF  |                       |     |     |     |      | •                     |     |     |     |      | •                     | •   | •   |     |
| 273                        | 27 nF  |                       |     |     |     |      |                       |     |     |     |      | •                     | •   | •   |     |
| 333                        | 33 nF  |                       |     |     |     |      |                       |     |     |     |      | •                     | •   |     |     |
| 393                        | 39 nF  |                       |     |     |     |      |                       |     |     |     |      | •                     |     |     |     |
| 473                        | 47 nF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |
| 563                        | 56 nF  |                       |     |     |     |      |                       |     |     |     |      |                       |     |     |     |

## Notes

• RoHS-compliant

• Plastic tape

<sup>(1)</sup> See soldering recommendations within this data book, or visit [www.vishay.com/doc?45034](http://www.vishay.com/doc?45034)



| SELECTION CHART            |        |                       |     |     |     |     |      |                       |     |     |     |      |
|----------------------------|--------|-----------------------|-----|-----|-----|-----|------|-----------------------|-----|-----|-----|------|
| DIELECTRIC                 |        | C0G (NP0)             |     |     |     |     |      |                       |     |     |     |      |
| STYLE                      |        | VJ2220 <sup>(1)</sup> |     |     |     |     |      | VJ2225 <sup>(1)</sup> |     |     |     |      |
| CASE CODE                  |        | 2220                  |     |     |     |     |      | 2225                  |     |     |     |      |
| VOLTAGE (V <sub>DC</sub> ) |        | 50                    | 100 | 200 | 500 | 630 | 1000 | 50                    | 100 | 200 | 500 | 1000 |
| VOLTAGE CODE               |        | A                     | B   | C   | E   | L   | G    | A                     | B   | C   | E   | G    |
| CAP. CODE                  | CAP.   |                       |     |     |     |     |      |                       |     |     |     |      |
| 1R0                        | 1.0 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 1R2                        | 1.2 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 1R5                        | 1.5 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 1R8                        | 1.8 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 2R2                        | 2.2 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 2R7                        | 2.7 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 3R3                        | 3.3 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 3R9                        | 3.9 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 4R7                        | 4.7 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 5R6                        | 5.6 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 6R8                        | 6.8 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 8R2                        | 8.2 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 100                        | 10 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 120                        | 12 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 150                        | 15 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 180                        | 18 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 220                        | 22 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 270                        | 27 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 330                        | 33 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 390                        | 39 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 470                        | 47 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 560                        | 56 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 680                        | 68 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 820                        | 82 pF  |                       |     |     |     |     |      |                       |     |     |     |      |
| 101                        | 100 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 121                        | 120 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 151                        | 150 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 181                        | 180 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 221                        | 220 pF |                       |     |     |     |     |      |                       |     |     |     |      |
| 271                        | 270 pF | •                     | •   | •   | •   | •   | •    |                       |     |     |     | •    |
| 331                        | 330 pF | •                     | •   | •   | •   | •   | •    |                       |     |     |     | •    |
| 391                        | 390 pF | •                     | •   | •   | •   | •   | •    |                       |     |     |     | •    |
| 471                        | 470 pF | •                     | •   | •   | •   | •   | •    |                       |     |     | •   | •    |
| 561                        | 560 pF | •                     | •   | •   | •   | •   | •    |                       |     |     | •   | •    |
| 681                        | 680 pF | •                     | •   | •   | •   | •   | •    |                       |     |     | •   | •    |
| 821                        | 820 pF | •                     | •   | •   | •   | •   | •    |                       |     |     | •   | •    |
| 102                        | 1.0 nF | •                     | •   | •   | •   | •   | •    |                       |     | •   | •   | •    |
| 122                        | 1.2 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 152                        | 1.5 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 182                        | 1.8 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 222                        | 2.2 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 272                        | 2.7 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 332                        | 3.3 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 392                        | 3.9 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   | •    |
| 472                        | 4.7 nF | •                     | •   | •   | •   | •   | •    | •                     | •   | •   | •   |      |
| 562                        | 5.6 nF | •                     | •   | •   | •   | •   |      | •                     | •   | •   | •   |      |
| 682                        | 6.8 nF | •                     | •   | •   |     |     |      | •                     | •   | •   | •   |      |
| 822                        | 8.2 nF | •                     | •   | •   |     |     |      | •                     | •   | •   | •   |      |
| 103                        | 10 nF  | •                     | •   | •   |     |     |      | •                     | •   | •   | •   |      |
| 123                        | 12 nF  | •                     | •   | •   |     |     |      | •                     | •   | •   | •   |      |
| 153                        | 15 nF  | •                     | •   | •   |     |     |      | •                     | •   | •   |     |      |
| 183                        | 18 nF  | •                     | •   |     |     |     |      | •                     | •   | •   |     |      |
| 223                        | 22 nF  | •                     | •   |     |     |     |      | •                     | •   | •   |     |      |
| 273                        | 27 nF  | •                     | •   |     |     |     |      | •                     | •   | •   |     |      |
| 333                        | 33 nF  | •                     | •   |     |     |     |      | •                     | •   | •   |     |      |
| 393                        | 39 nF  | •                     |     |     |     |     |      | •                     | •   | •   |     |      |
| 473                        | 47 nF  | •                     |     |     |     |     |      | •                     | •   |     |     |      |
| 563                        | 56 nF  |                       |     |     |     |     |      | •                     |     |     |     |      |

## Notes

• RoHS-compliant

• Plastic tape

<sup>(1)</sup> See soldering recommendations within this data book, or visit [www.vishay.com/doc?45034](http://www.vishay.com/doc?45034)



| SELECTION CHART            |        |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
|----------------------------|--------|--------|----|----|-----|--------|----|----|-----|-----|--------|----|----|-----|-----|
| DIELECTRIC                 |        | X7R    |    |    |     |        |    |    |     |     |        |    |    |     |     |
| STYLE                      |        | VJ0402 |    |    |     | VJ0603 |    |    |     |     | VJ0805 |    |    |     |     |
| CASE CODE                  |        | 0402   |    |    |     | 0603   |    |    |     |     | 0805   |    |    |     |     |
| VOLTAGE (V <sub>DC</sub> ) |        | 16     | 25 | 50 | 100 | 16     | 25 | 50 | 100 | 200 | 16     | 25 | 50 | 100 | 200 |
| VOLTAGE CODE               |        | J      | X  | A  | B   | J      | X  | A  | B   | C   | J      | X  | A  | B   | C   |
| CAP. CODE                  | CAP.   |        |    |    |     |        |    |    |     |     |        |    |    |     | P   |
| 121                        | 120 pF | ••     | •• | •• | ••  |        |    |    |     |     |        |    |    |     |     |
| 151                        | 150 pF | ••     | •• | •• | ••  |        |    |    |     |     |        |    |    |     |     |
| 181                        | 180 pF | ••     | •• | •• | ••  |        |    |    |     |     |        |    |    |     |     |
| 221                        | 220 pF | ••     | •• | •• | ••  |        |    |    |     |     |        |    |    |     |     |
| 271                        | 270 pF | ••     | •• | •• | ••  |        |    |    |     |     |        |    |    |     |     |
| 331                        | 330 pF | ••     | •• | •• | ••  |        |    | •• | ••  | ••  |        |    |    |     | ••  |
| 391                        | 390 pF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  |        |    |    |     | ••  |
| 471                        | 470 pF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 561                        | 560 pF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 681                        | 680 pF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 821                        | 820 pF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 102                        | 1.0 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 122                        | 1.2 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 152                        | 1.5 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 182                        | 1.8 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 222                        | 2.2 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 272                        | 2.7 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 332                        | 3.3 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 392                        | 3.9 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 472                        | 4.7 nF | ••     | •• | •• | ••  | ••     | •• | •• | ••  | ••  | ••     | •• | •• | ••  | ••  |
| 562                        | 5.6 nF | ••     | •• | •• |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | ••  |
| 682                        | 6.8 nF | ••     | •• | •• |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | ••  |
| 822                        | 8.2 nF | ••     | •• | •• |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | ••  |
| 103                        | 10 nF  | ••     | •• | •• |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | •   |
| 123                        | 12 nF  | ••     | •• |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | •   |
| 153                        | 15 nF  | ••     | •• |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | •   |
| 183                        | 18 nF  | ••     | •• |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | •   |
| 223                        | 22 nF  | ••     |    |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | •   |
| 273                        | 27 nF  | ••     |    |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | ••  | •   |
| 333                        | 33 nF  | ••     |    |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | •   |     |
| 393                        | 39 nF  | ••     |    |    |     | ••     | •• | •• | ••  |     | ••     | •• | •• | •   |     |
| 473                        | 47 nF  | ••     |    |    |     | ••     | •• | •• |     |     | ••     | •• | •• | •   |     |
| 563                        | 56 nF  |        |    |    |     | ••     | •• | •• |     |     | ••     | •• | •• | •   |     |
| 683                        | 68 nF  |        |    |    |     | ••     | •• | •• |     |     | ••     | •• | •  | •   |     |
| 823                        | 82 nF  |        |    |    |     | ••     | •• | •• |     |     | •      | •  | •  | •   |     |
| 104                        | 100 nF |        |    |    |     | ••     | •• | •• |     |     | •      | •  | •  | •   |     |
| 124                        | 120 nF |        |    |    |     | ••     |    |    |     |     | •      | •  | •  |     |     |
| 154                        | 150 nF |        |    |    |     | ••     |    |    |     |     | •      | •  | •  |     |     |
| 184                        | 180 nF |        |    |    |     |        |    |    |     |     | •      | •  |    |     |     |
| 224                        | 220 nF |        |    |    |     |        |    |    |     |     | •      | •  |    |     |     |
| 274                        | 270 nF |        |    |    |     |        |    |    |     |     | •      | •  |    |     |     |
| 334                        | 330 nF |        |    |    |     |        |    |    |     |     | •      | •  |    |     |     |
| 394                        | 390 nF |        |    |    |     |        |    |    |     |     | •      |    |    |     |     |
| 474                        | 470 nF |        |    |    |     |        |    |    |     |     | •      |    |    |     |     |
| 564                        | 560 nF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 684                        | 680 nF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 824                        | 820 nF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 105                        | 1.0 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 125                        | 1.2 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 155                        | 1.5 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 185                        | 1.8 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 225                        | 2.2 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 275                        | 2.7 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 335                        | 3.3 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 395                        | 3.9 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 475                        | 4.7 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 565                        | 5.6 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |
| 685                        | 6.8 μF |        |    |    |     |        |    |    |     |     |        |    |    |     |     |

## Notes

•• RoHS-compliant

•• Paper tape • Plastic tape ••• Variable plastic / paper tape



| SELECTION CHART            |        |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
|----------------------------|--------|-----------------------|----|----|-----|-----|-----|-----|-----|-----------------------|----|----|-----|-----|-----|-----|-----|
| DIELECTRIC                 |        | X7R                   |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| STYLE                      |        | VJ1206 <sup>(1)</sup> |    |    |     |     |     |     |     | VJ1210 <sup>(1)</sup> |    |    |     |     |     |     |     |
| CASE CODE                  |        | 1206                  |    |    |     |     |     |     |     | 1210                  |    |    |     |     |     |     |     |
| VOLTAGE (V <sub>DC</sub> ) |        | 16                    | 25 | 50 | 100 | 200 | 250 | 500 | 630 | 16                    | 25 | 50 | 100 | 200 | 250 | 500 | 630 |
| VOLTAGE CODE               |        | J                     | X  | A  | B   | C   | P   | E   | L   | J                     | X  | A  | B   | C   | P   | E   | L   |
| CAP. CODE                  | CAP.   |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 121                        | 120 pF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 151                        | 150 pF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 181                        | 180 pF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 221                        | 220 pF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 271                        | 270 pF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 331                        | 330 pF |                       |    |    |     |     |     | ••  | ••  |                       |    |    |     |     |     |     |     |
| 391                        | 390 pF |                       |    |    |     |     |     | ••  | ••  |                       |    |    |     |     |     |     | •   |
| 471                        | 470 pF |                       | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     |     | •   |
| 561                        | 560 pF |                       | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     |     | •   |
| 681                        | 680 pF |                       | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     |     | •   |
| 821                        | 820 pF |                       | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     |     | •   |
| 102                        | 1.0 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     | •   | •   |
| 122                        | 1.2 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     | •   | •   |
| 152                        | 1.5 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     | •   | •   |
| 182                        | 1.8 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     | •   | •   |
| 222                        | 2.2 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     | •   | •   |
| 272                        | 2.7 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     |     |     | •   | •   |
| 332                        | 3.3 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     | •   |     | •   | •   |
| 392                        | 3.9 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     | •   |     | •   | •   |
| 472                        | 4.7 nF | ••                    | •• | •• | ••  | ••  |     | ••  | ••  |                       |    |    |     | •   |     | •   | •   |
| 562                        | 5.6 nF | ••                    | •• | •• | ••  | ••  |     | •   | •   |                       |    |    |     | •   |     | •   | •   |
| 682                        | 6.8 nF | ••                    | •• | •• | ••  | ••  |     | •   | •   |                       |    |    |     | •   |     | •   | •   |
| 822                        | 8.2 nF | ••                    | •• | •• | ••  | ••  |     | •   | •   |                       |    |    |     | •   |     | •   | •   |
| 103                        | 10 nF  | ••                    | •• | •• | ••  | ••  | •   | •   | •   | •                     | •  | •  | •   | •   |     | •   | •   |
| 123                        | 12 nF  | ••                    | •• | •• | ••  | ••  | •   | •   | •   | •                     | •  | •  | •   | •   |     | •   | •   |
| 153                        | 15 nF  | ••                    | •• | •• | ••  | ••  | •   | •   | •   | •                     | •  | •  | •   | •   |     | •   | •   |
| 183                        | 18 nF  | ••                    | •• | •• | ••  | ••  | •   | •   | •   | •                     | •  | •  | •   | •   |     | •   | •   |
| 223                        | 22 nF  | ••                    | •• | •• | ••  | ••  | •   |     |     | •                     | •  | •  | •   | •   |     | •   | •   |
| 273                        | 27 nF  | ••                    | •• | •• | ••  | ••  | •   |     |     | •                     | •  | •  | •   | •   |     | •   | •   |
| 333                        | 33 nF  | ••                    | •• | •• | ••  | ••  | •   |     |     | •                     | •  | •  | •   | •   | •   | •   | •   |
| 393                        | 39 nF  | ••                    | •• | •• | ••  | •   | •   |     |     | •                     | •  | •  | •   | •   | •   | •   | •   |
| 473                        | 47 nF  | ••                    | •• | •• | ••  | •   | •   |     |     | •                     | •  | •  | •   | •   | •   | •   | •   |
| 563                        | 56 nF  | ••                    | •• | •• | ••  | •   | •   |     |     | •                     | •  | •  | •   | •   | •   |     |     |
| 683                        | 68 nF  | ••                    | •• | •• | ••  | •   | •   |     |     | •                     | •  | •  | •   | •   | •   |     |     |
| 823                        | 82 nF  | ••                    | •• | •  | •   | •   | •   |     |     | •                     | •  | •  | •   | •   | •   |     |     |
| 104                        | 100 nF | •                     | •  | •  | •   | •   | •   |     |     | •                     | •  | •  | •   | •   | •   |     |     |
| 124                        | 120 nF | •                     | •  | •  | •   |     |     |     |     | •                     | •  | •  | •   | •   |     |     |     |
| 154                        | 150 nF | •                     | •  | •  | •   |     |     |     |     | •                     | •  | •  | •   | •   |     |     |     |
| 184                        | 180 nF | •                     | •  | •  | •   |     |     |     |     | •                     | •  | •  | •   | •   |     |     |     |
| 224                        | 220 nF | •                     | •  | •  | •   |     |     |     |     | •                     | •  | •  | •   |     |     |     |     |
| 274                        | 270 nF | •                     | •  | •  | •   |     |     |     |     | •                     | •  | •  | •   |     |     |     |     |
| 334                        | 330 nF | •                     | •  | •  |     |     |     |     |     | •                     | •  | •  | •   |     |     |     |     |
| 394                        | 390 nF | •                     | •  | •  |     |     |     |     |     | •                     | •  | •  | •   |     |     |     |     |
| 474                        | 470 nF | •                     | •  | •  |     |     |     |     |     | •                     | •  | •  | •   |     |     |     |     |
| 564                        | 560 nF | •                     | •  |    |     |     |     |     |     | •                     | •  | •  |     |     |     |     |     |
| 684                        | 680 nF | •                     | •  |    |     |     |     |     |     | •                     | •  | •  |     |     |     |     |     |
| 824                        | 820 nF | •                     | •  |    |     |     |     |     |     | •                     | •  | •  |     |     |     |     |     |
| 105                        | 1.0 µF | •                     | •  |    |     |     |     |     |     | •                     | •  | •  |     |     |     |     |     |
| 125                        | 1.2 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 155                        | 1.5 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 185                        | 1.8 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 225                        | 2.2 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 275                        | 2.7 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 335                        | 3.3 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 395                        | 3.9 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 475                        | 4.7 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 565                        | 5.6 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |
| 685                        | 6.8 µF |                       |    |    |     |     |     |     |     |                       |    |    |     |     |     |     |     |

## Notes

• RoHS-compliant

•• Paper tape • Plastic tape

<sup>(1)</sup> See soldering recommendations within this data book, or visit [www.vishay.com/doc?45034](http://www.vishay.com/doc?45034)



## SELECTION CHART

| DIELECTRIC                 |        | X7R                   |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
|----------------------------|--------|-----------------------|-----|-----|-----|------|-----------------------|----|-----|-----|-----|-----|-----|------|-----------------------|----|-----|-----|-----|-----|------|--|
| STYLE                      |        | VJ1808 <sup>(1)</sup> |     |     |     |      | VJ1812 <sup>(1)</sup> |    |     |     |     |     |     |      | VJ1825 <sup>(1)</sup> |    |     |     |     |     |      |  |
| CASE CODE                  |        | 1808                  |     |     |     |      | 1812                  |    |     |     |     |     |     |      | 1825                  |    |     |     |     |     |      |  |
| VOLTAGE (V <sub>DC</sub> ) |        | 50                    | 100 | 200 | 500 | 1000 | 25                    | 50 | 100 | 200 | 250 | 500 | 630 | 1000 | 25                    | 50 | 100 | 200 | 250 | 500 | 1000 |  |
| VOLTAGE CODE               |        | A                     | B   | C   | E   | G    | X                     | A  | B   | C   | P   | E   | L   | G    | X                     | A  | B   | C   | P   | E   | G    |  |
| CAP. CODE                  | CAP.   |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 121                        | 120 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 151                        | 150 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 181                        | 180 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 221                        | 220 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 271                        | 270 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 331                        | 330 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 391                        | 390 pF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 471                        | 470 pF |                       |     |     |     | •    |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 561                        | 560 pF |                       |     |     |     | •    |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 681                        | 680 pF |                       |     |     |     | •    |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 821                        | 820 pF |                       |     |     |     | •    |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 102                        | 1.0 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 122                        | 1.2 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 152                        | 1.5 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 182                        | 1.8 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 222                        | 2.2 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 272                        | 2.7 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 332                        | 3.3 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 392                        | 3.9 nF |                       |     |     | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 472                        | 4.7 nF |                       |     | •   | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 562                        | 5.6 nF |                       |     | •   | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 682                        | 6.8 nF |                       |     | •   | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 822                        | 8.2 nF |                       |     | •   | •   | •    |                       |    |     |     |     | •   | •   | •    |                       |    |     |     |     |     |      |  |
| 103                        | 10 nF  | •                     | •   | •   | •   | •    |                       |    |     | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 123                        | 12 nF  | •                     | •   | •   | •   | •    |                       |    |     | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 153                        | 15 nF  | •                     | •   | •   | •   | •    |                       |    |     | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 183                        | 18 nF  | •                     | •   | •   | •   | •    |                       |    |     | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 223                        | 22 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 273                        | 27 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 333                        | 33 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 393                        | 39 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 473                        | 47 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 563                        | 56 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 683                        | 68 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 823                        | 82 nF  | •                     | •   | •   | •   | •    | •                     | •  | •   | •   |     | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 104                        | 100 nF | •                     | •   | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •   | •    | •                     | •  | •   | •   | •   | •   | •    |  |
| 124                        | 120 nF | •                     | •   | •   | •   | •    | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 154                        | 150 nF | •                     | •   | •   | •   | •    | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 184                        | 180 nF | •                     | •   | •   | •   | •    | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 224                        | 220 nF | •                     |     |     |     |      | •                     | •  | •   | •   | •   | •   |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 274                        | 270 nF | •                     |     |     |     |      | •                     | •  | •   | •   | •   | •   |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 334                        | 330 nF |                       |     |     |     |      | •                     | •  | •   | •   | •   | •   |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 394                        | 390 nF |                       |     |     |     |      | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 474                        | 470 nF |                       |     |     |     |      | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 564                        | 560 nF |                       |     |     |     |      | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 684                        | 680 nF |                       |     |     |     |      | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 824                        | 820 nF |                       |     |     |     |      | •                     | •  | •   | •   | •   |     |     |      | •                     | •  | •   | •   | •   | •   | •    |  |
| 105                        | 1.0 μF |                       |     |     |     |      | •                     | •  |     |     |     |     |     |      | •                     | •  | •   | •   | •   |     |      |  |
| 125                        | 1.2 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      | •                     | •  | •   |     |     |     |      |  |
| 155                        | 1.5 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      | •                     | •  | •   |     |     |     |      |  |
| 185                        | 1.8 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      | •                     | •  |     |     |     |     |      |  |
| 225                        | 2.2 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      | •                     |    |     |     |     |     |      |  |
| 275                        | 2.7 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      | •                     |    |     |     |     |     |      |  |
| 335                        | 3.3 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 395                        | 3.9 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 475                        | 4.7 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 565                        | 5.6 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |
| 685                        | 6.8 μF |                       |     |     |     |      |                       |    |     |     |     |     |     |      |                       |    |     |     |     |     |      |  |

## Notes

• RoHS-compliant

• Plastic tape

<sup>(1)</sup> See soldering recommendations within this data book, or visit [www.vishay.com/doc?45034](http://www.vishay.com/doc?45034)



| SELECTION CHART            |        |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
|----------------------------|--------|-----------------------|-----|-----|-----|-----------------------|----|-----|-----|-----|------|-----------------------|----|-----|-----|-----|
| DIELECTRIC                 |        | X7R                   |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| STYLE                      |        | VJ2220 <sup>(1)</sup> |     |     |     | VJ2225 <sup>(1)</sup> |    |     |     |     |      | VJ3640 <sup>(1)</sup> |    |     |     |     |
| CASE CODE                  |        | 2220                  |     |     |     | 2225                  |    |     |     |     |      | 3640                  |    |     |     |     |
| VOLTAGE (V <sub>DC</sub> ) |        | 50                    | 100 | 200 | 500 | 25                    | 50 | 100 | 200 | 500 | 1000 | 25                    | 50 | 100 | 200 | 500 |
| VOLTAGE CODE               |        | A                     | B   | C   | E   | X                     | A  | B   | C   | E   | G    | X                     | A  | B   | C   | E   |
| CAP. CODE                  | CAP.   |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 121                        | 120 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 151                        | 150 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 181                        | 180 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 221                        | 220 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 271                        | 270 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 331                        | 330 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 391                        | 390 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 471                        | 470 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 561                        | 560 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 681                        | 680 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 821                        | 820 pF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 102                        | 1.0 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 122                        | 1.2 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 152                        | 1.5 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 182                        | 1.8 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 222                        | 2.2 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 272                        | 2.7 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 332                        | 3.3 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 392                        | 3.9 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 472                        | 4.7 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 562                        | 5.6 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 682                        | 6.8 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 822                        | 8.2 nF |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 103                        | 10 nF  |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 123                        | 12 nF  |                       |     |     |     |                       |    |     |     |     |      |                       |    |     |     |     |
| 153                        | 15 nF  |                       |     |     | •   |                       |    |     |     |     |      |                       |    |     |     |     |
| 183                        | 18 nF  |                       |     |     | •   |                       |    |     |     |     |      |                       |    |     |     |     |
| 223                        | 22 nF  |                       |     |     | •   |                       |    |     |     |     |      |                       |    |     |     |     |
| 273                        | 27 nF  |                       |     |     | •   |                       |    |     |     |     |      |                       |    |     | •   | •   |
| 333                        | 33 nF  |                       |     |     | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 393                        | 39 nF  |                       |     |     | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 473                        | 47 nF  |                       |     |     | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 563                        | 56 nF  |                       |     |     | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 683                        | 68 nF  |                       |     |     | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 823                        | 82 nF  |                       |     |     | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 104                        | 100 nF |                       |     | •   | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 124                        | 120 nF |                       |     | •   | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 154                        | 150 nF |                       |     | •   | •   | •                     | •  | •   | •   | •   | •    |                       |    |     | •   | •   |
| 184                        | 180 nF |                       |     | •   | •   | •                     | •  | •   | •   | •   | •    | •                     | •  | •   | •   | •   |
| 224                        | 220 nF |                       | •   | •   | •   | •                     | •  | •   | •   | •   | •    | •                     | •  | •   | •   | •   |
| 274                        | 270 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   | •    | •                     | •  | •   | •   | •   |
| 334                        | 330 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   | •    | •                     | •  | •   | •   | •   |
| 394                        | 390 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   |      | •                     | •  | •   | •   | •   |
| 474                        | 470 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   |      | •                     | •  | •   | •   | •   |
| 564                        | 560 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   |      | •                     | •  | •   | •   | •   |
| 684                        | 680 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   |      | •                     | •  | •   | •   | •   |
| 824                        | 820 nF | •                     | •   | •   |     | •                     | •  | •   | •   | •   |      | •                     | •  | •   | •   |     |
| 105                        | 1.0 µF | •                     | •   | •   |     | •                     | •  | •   | •   | •   |      | •                     | •  | •   | •   |     |
| 125                        | 1.2 µF | •                     | •   |     |     | •                     | •  | •   | •   |     |      | •                     | •  | •   | •   |     |
| 155                        | 1.5 µF | •                     |     |     |     | •                     | •  | •   | •   |     |      | •                     | •  | •   | •   |     |
| 185                        | 1.8 µF | •                     |     |     |     | •                     | •  | •   | •   |     |      | •                     | •  | •   | •   |     |
| 225                        | 2.2 µF | •                     |     |     |     | •                     | •  |     |     |     |      | •                     | •  | •   |     |     |
| 275                        | 2.7 µF |                       |     |     |     | •                     | •  |     |     |     |      | •                     | •  |     |     |     |
| 335                        | 3.3 µF |                       |     |     |     | •                     |    |     |     |     |      | •                     | •  | •   |     |     |
| 395                        | 3.9 µF |                       |     |     |     | •                     |    |     |     |     |      | •                     | •  | •   |     |     |
| 475                        | 4.7 µF |                       |     |     |     | •                     |    |     |     |     |      | •                     | •  |     |     |     |
| 565                        | 5.6 µF |                       |     |     |     |                       |    |     |     |     |      | •                     |    |     |     |     |
| 685                        | 6.8 µF |                       |     |     |     |                       |    |     |     |     |      | •                     |    |     |     |     |

## Notes

• RoHS-compliant

• Plastic tape

<sup>(1)</sup> See soldering recommendations within this data book, or visit [www.vishay.com/doc?45034](http://www.vishay.com/doc?45034)



COG (NP0) DIELECTRIC - TYPICAL PARAMETERS





### X7R DIELECTRIC - TYPICAL PARAMETERS



## X7R DIELECTRIC - TYPICAL PARAMETERS



## STANDARD PACKAGING QUANTITIES (1)(2)(3)

| CASE CODE      | TAPE SIZE | 7" REEL QUANTITIES                  |                                 | 11 1/4" AND 13" REEL QUANTITIES     |                                 |
|----------------|-----------|-------------------------------------|---------------------------------|-------------------------------------|---------------------------------|
|                |           | PAPER TAPE PACKAGING CODE "C" / "O" | PLASTIC TAPE PACKAGING CODE "T" | PAPER TAPE PACKAGING CODE "P" / "I" | PLASTIC TAPE PACKAGING CODE "R" |
| 0402           | 8 mm      | 5000                                | n/a                             | 10 000                              | n/a                             |
| 0603 (4)(5)(6) | 8 mm      | 4000                                | 4000                            | 10 000                              | 10 000                          |
| 0805 (4)(5)    | 8 mm      | 3000                                | 3000                            | 10 000                              | 10 000                          |
| 1206 (4)(5)    | 8 mm      | 3000                                | 2500 / 3000                     | 10 000                              | 9000 / 10 000                   |
| 1210 (4)       | 8 mm      | n/a                                 | 2000 / 2500 / 3000              | n/a                                 | 9000 / 10 000                   |
| 1808           | 12 mm     | n/a                                 | 2000                            | n/a                                 | 10 000                          |
| 1812           | 12 mm     | n/a                                 | 1000                            | n/a                                 | 4000                            |
| 1825           | 12 mm     | n/a                                 | 500                             | n/a                                 | 4000                            |
| 2220           | 12 mm     | n/a                                 | 1000                            | n/a                                 | n/a                             |
| 2225           | 12 mm     | n/a                                 | 500                             | n/a                                 | n/a                             |
| 3640           | 16 mm     | n/a                                 | 500                             | n/a                                 | n/a                             |

### Notes

- (1) Vishay Vitramon uses embossed plastic carrier tape
- (2) REFERENCE: EIA standard RS 481 - "Taping of Surface Mount Components for Automatic Placement"
- (3) n/a = not available
- (4) Packaging "C" / "P" / "O" / "I" and "T" / "R" or lower quantities can depend from product thickness
- (5) Polymer termination, code "B", only available in plastic tape "T" / "R"
- (6) Variable packaging codes, see ratings in "Selection Charts"


## STORAGE AND HANDLING CONDITIONS

- (1) Store the components at 5 °C to 40 °C ambient temperature and ≤ 70 % relative humidity conditions.
- (2) The product is recommended to be used within a time-frame of 2 years after shipment.  
Check solderability in case extended shelf life beyond the expiry date is needed.

### Precautions:

- a. Do not store products in an environment containing corrosive elements, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. This may cause corrosion or oxidation of the terminations, which can easily lead to poor soldering.
- b. Store products on the shelf and avoid exposure to moisture or dust.
- c. Do not expose products to excessive shock, vibration, direct sunlight and so on.

## Solder Pad Dimensions for Vishay Surface-Mount Multilayer Ceramic Chip Capacitors

| DIMENSIONS in millimeters                                                         |                     |      |                     |
|-----------------------------------------------------------------------------------|---------------------|------|---------------------|
|  |                     |      |                     |
| CASE CODE                                                                         | A                   | B    | C                   |
| 0402                                                                              | 0.50                | 0.50 | 0.40                |
| 0505                                                                              | 1.35                | 1.00 | 0.60                |
| 0603                                                                              | 0.90                | 1.00 | 1.00 <sup>(3)</sup> |
| 0805                                                                              | 1.30                | 1.20 | 1.00                |
| 1111                                                                              | 2.90                | 1.30 | 1.75                |
| 1206                                                                              | 1.80                | 1.20 | 2.10                |
| 1210                                                                              | 2.80                | 1.30 | 1.90                |
| 1808                                                                              | 2.40                | 1.50 | 3.00                |
| 1812                                                                              | 3.60                | 1.50 | 3.00                |
| 1825                                                                              | 6.50                | 1.50 | 3.00                |
| 2008                                                                              | 2.70                | 1.50 | 4.08                |
| 2220                                                                              | 5.50 <sup>(4)</sup> | 1.50 | 4.20                |
| 2225                                                                              | 6.50                | 1.50 | 4.20                |
| 2525                                                                              | 6.60                | 1.50 | 4.50                |
| 3040                                                                              | 10.80               | 2.00 | 5.50                |
| 3640                                                                              | 10.80               | 2.00 | 7.00                |
| 3838                                                                              | 10.20               | 2.00 | 7.50                |
| 4044                                                                              | 12.30               | 2.00 | 8.00                |

### Notes

- <sup>(1)</sup> For safety capacitors and voltages above 3000 V, corner rounding (R) of 0.5 mm is recommended to suppress arcing
- <sup>(2)</sup> Add a 1 mm slot in PCB between pads to allow cleaning and coating under MLCC
- <sup>(3)</sup> For VJ HiFREQ Series, this dimension is 0.6 mm
- <sup>(4)</sup> For safety capacitors, the A dimension should be 5.80 mm



## PRINTED CIRCUIT BOARD PCB DESIGN CONSIDERATIONS FOR HIGH VOLTAGE SURFACE-MOUNT MLCCS

Special assembly process and design considerations should be employed for today's high voltage rating MLCCs. As case sizes remain the same and voltage ratings increase, MLCC manufacturers must design, evaluate, and qualify their capacitors using methods that reduce the occurrence of corona discharge and arcover events. To meet similar capability in high voltage applications, users should employ similar cautionary design and assembly methods.

### MLCC PAD LAYOUT

A capacitor's arcover inception point can degrade due to factors such as the MLCC termination, PCB pad design, PCB cleanliness, solder flux residue, surface contamination / deposits and environmental conditions. PCB pads and their design affect the air gap distance between the opposing polarities of the MLCC termination. For voltage rating greater than 1500 V<sub>DC</sub> add a corner radius to the inward facing edge of the MLCC pads and as large a gap as possible between the pads. Too small of a pad gap distance will reduce the capacitor's own arcover inception voltage level. Refer to the Figure and Table Figure 1.0, MLCC Pad Layout and Table 1.0, Vishay MLCC Solder Pad Dimensions for the recommended MLCC solder pad dimensions.

### SLOT OR TRENCH BETWEEN PADS

PCB assembly can deposit dust, trap solder balls, or flux residue underneath the capacitors. These contaminants will reduce conductive clearances and the arcover inception level. Assembly methods must include a final PCB cleaning process. A slot or trench can be cut into the PCB in between the pads to allow cleaners to penetrate underneath the MLCC. The slot will also allow conformal or epoxy coatings to flow underneath the MLCC and build an insulative barrier between pads. Refer to Figure 1.0 MLCC Pad Layout for slot reference location.

### COATING PRINTED CIRCUIT BOARD

Coating a printed circuit board with materials such as acrylic, silicone and urethane resins provide a protective dielectric barrier that is non-conductive and will enhance the resistance to arcing. Various processes exist which include dipping, brushing, and spraying. Optimal performance will come from coating the MLCC on all sides, top and bottom. The PCB slot in between the pads should extend slightly beyond the width of the MLCC. Refer to Figure 1.0 MLCC Pad Layout for slot reference location.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.