






- ① MATERIAL: COPPER ALLOY
- ② FINISH: PRE-PLATED WITH SELECT SILVER AND TIN ALL OVER NICKEL.
SEPARABLE CONTACT INTERFACE AREA: 1.00-3.00µm SILVER.
CRIMP AREA: 1.00µm MIN TIN.
- ③ MATERIAL ID FEATURE IN "UP" POSITION.
- 4. NORMAL FORCE 240 GRAMS REFERENCE.
- 5. AVERAGE ENGAGEMENT FORCE TARGET 3.0N REF.
- ⑥ TERMINAL HAS NYE LUBRICANTS NYETACT 568J-50-UV PERFORMANCE
LUBE/GREASE APPLIED. THIS IS A WHITISH COLORED LUBE. AMOUNT
AND VISIBILITY MAY VARY.
- 7. FOR SILVER PLATING: ELECTRICAL PERFORMANCE IS NOT AFFECTED BY
GRAY OR BLACK TARNISH ON THE SILVER PLATING SURFACE. ACCEPTABLE
SILVER SURFACE CAN INCLUDE GRAY OR BLACK TARNISH.
- ⑧ NOT INTENDED FOR SEALED APPLICATIONS.
- ⑨ SEALING CAPABILITY MUST BE EVALUATED ON AN APPLICATION BASIS.



SECTION N - N



DETAIL B
SCALE 2:1



SECTION A - A
SCALE 25:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. P. KINSEY 16APR2007 CHK. C. SCHMID 16APR2007 APPR. C. SCHMID 16APR2007		 STE TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: FRACTION DECIMAL 0 P.L.C. ±. 1 P.L.C. ±. 2 P.L.C. ±0.15 3 P.L.C. ±. 4 P.L.C. ±. ANGLES ±. FINISH		NAME CONTACT, FEMALE, 0.64, SILVER PLATE GENERATION Y	
		PRODUCT SPEC APPLICATION SPEC 114-13183		SIZE CAGE CODE DRAWING NO A100779 C=1456968	
MATERIAL 		WEIGHT 0.23g		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 15:1		SHEET 1 OF 1 REV. E2	