





12		11		10		9		8		7		6		5		4		3		2		1										
SYMBOL DEFINITION														MISSING NUMBERS				DWG STATUS				ZONE	REVISION HISTORY				AUTH	DR	APVD 1	APVD 2		
THE NUMBER INSIDE THE SYMBOL  CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER														TOTAL NO. OF SYMBOLS ON DRAWING	7					DATE	STG	REV	N/P	CHG	CLEARED REVISION COLUMN REVISED NOTES & GRAPHICS				195715	JHH	JHH	RJ
														LAST NO. USED	15					19MY00	-	02	-	-					220C01	-	03	-
																				16AP02	-	04	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES				215725	JMR	JMR	MW
																				06N002	R	05	-	-	DIM F WAS +/-0.1 & UPDATED FORMAT				223829	RAB	RAB	MD
																				03JA03	R	06	-	-	12177007 - UPDATED PDM ATTRIBUTES				232853	TLD	TLD	MJD
																				12FE04	R	07	-	-	12177007 & 12129361 - 2X 3.95±0.15 WAS 2X 3.95±0.1				235051	TLD	TLD	RF
																									12177007 & 12129361 - REVISED CHART ADDED MATERIAL SPEC COLUMN				251019	CTR	JAA	MD





VIEW SCALE DOES NOT REFLECT ACTUAL PART SIZE

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

12177007	R	A8	-		0.35	1.63 MAX	22	M3633FN4	C17200 BECU AU+SN	GOLD	6901	2.1 +/-0.2
12129361	R	A8	-		0.35	1.63 MAX	22	M3635466	C17200 BECU SN	TIN	6901	2.1 +/-0.2
12092440	R	H3	-	OBSOLETE	0.35	1.63 MAX	22	-	-	TIN	6900	2.1
PART NO	STG	REV	N/P	STATUS	SIZE (MM²)	DIA	I.D. NO.	MATL. SPEC.	MATL. DESC.	CONTACT INTERFACE	CODE NO.	F
					CABLE							

15		PROCESS SENSITIVE DIMENSION		
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED				
DIMENSIONAL RANGE (MM)		CHART D		
FROM	0	>12		
TO	12			
TOLERANCE UNLESS OTHERWISE SPECIFIED				
±0.1		±0.2		
ANGULAR TOLERANCE		±2°		

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
ROUTING		SEE CHART	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 PERFECT FORM AT MMC1 DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
			

DELPHI			
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH			
DR		DATE	
APVD1 ROGER WAYT		01FE88	
APVD2 TOM NADASKY		14MY88	
APVD3 JOHN YURTIN		26MY88	
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001			
MATERIAL SEE DRAWING			
DRAWING NAME TERM F MIC/P 064			
DRAWING NUMBER 12092439			
SIZE	SCALE	FRAME NO	SHEET NO
A1	10:1	1 OF 1	1 OF 1
STG	REV	N/P	
R	07	-	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12129361-L](#)