




DIN 933

ISO 4017

Standard withdrawn



BN 622

Hex head screws

fully threaded

Stainless steel A2

- ~UNI 5739
- ~ČSN 021103



The commercial quality of steel grades A2 and A4 is property class 70 (tensile strength 700 N/mm²). Strength of the screw is indicated by the head marking and defined by the applicable product standard.

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e	k	s	L
1729071	M3	6,01	2	5,5	5
1073508					6
1073516					8
1073524					10
1073540					12
1714937					(14)
1073559					16
1073567					20
1127071					25
1127098					30
1729098					35
1729101					40
1208357	M4	7,66	2,8	7	6
1237810					8
1237829					10
1237837					12
1426060					(14)
1237845					16
1237853					20
1127101					25
1127128					30
1426079					35
1127136					40
1729233					45
1737732					50
3145406					60

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e	k	s	L
1208365	M5	8,79	3,5	8	6
1237861					8
1237888					10
1237896					12
1237918					(14)
1237926					16
1120212					(18)
1237934					20
1120220					(22)
1237942					25
1073575					30
1426087					35
1073583					40
1426095					45
1127144					50
1737759					55
1737775					60
5511951					70
1208373	M6	11,05	4	10	8
1237950					10
1237969					12
1237977					(14)
1237985					16
1128027					(18)
1237993					20
1128043					(22)
1238000					25
1238019					30
1073591					35
1073605					40
1426109					45
1073613					50
1128094					55
1127152					60
1128108					65
1426117					70
1128469					(75)
1426125					80
1426133					90
1426141					100
3351190					120

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e	k	s	L
1208403	M8	14,38	5,3	13	10
1238027					12
1238035					(14)
1238043					16
1128809					(18)
1238051					20
1128922					(22)
1238078					25
1238086					30
1238094					35
1238108					40
1073621					45
1073648					50
1426265					55
1073656					60
1129104					65
1208411					70
1129120					(75)
1208438					80
1208446					90
1208454					100
3145427					110
3145428					120
3145429					130
5517997	M10	18,9	6,4	17	10
3145432					12
1238124					(14)
1238132					16
1238140					20
1238159					25
1238167					30
1238175					35
1238183					40
1073664					45
1238191					50
1426273					55
1073672					60
1426346					65
1127160					70
1426362					(75)
1127179					80

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e	k	s	L
1426389	M10	18,9	6,4	17	90
1426923					100
3145430					110
3145431					120
3092249					130
3092250					140
8301793					150
1714961	M12	21,1	7,5	19	16
1238213					20
1238221					25
1238248					30
1238256					35
1238264					40
1073680					45
1238272					50
1427148					55
1073699					60
1427164					65
1127187					70
1427180					(75)
1127195					80
1427202					90
1427229					100
8301815					120
8301858					150
8087431	(M14)	24,49	8,8	22	25
8087458					30
8043213					40
8087466					50
1238280	M16	26,75	10	24	20
1238299					25
1238302					30
1238310					35
1238329					40
1238337					45
1238345					50
1238353					55
1238361					60
1132431					65
1238388					70
1132458					(75)

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e	k	s	L
1127209	M16	26,75	10	24	80
1208462					90
1208470					100
3145435					110
1427245					120
8301947					130
8301955					140
1427253	M20	33,53	12,5	30	30
1427261					35
1238396					40
1238418					45
1238426					50
1238434					55
1238442					60
1132474					65
1238450					70
1133926					(75)
1080393					80
1208489					90
1208497					100
1208500					110
1208519					120
5509569	M24	39,98	15	36	40
3145442					45
1127217					50
3145443					55
1127225					60
1133934					65
1127233					70
1127241					80
1127268					90
1127276					100
1208527					110
1208535					120
1127292	(M27)	45,2	17	41	60
1127306					70
1127314					80
1127322					90
1127330					100
1208543					110
1208578	M30	50,85	18,7	46	60

M10; M12; M14: wrench size according to ISO on request

Article#	d ₁	e	k	s	L
1208586	M30	50,85	18,7	46	70
1209590					80
1209655					90
1209663					100
1209671					110
1209698					120