

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15-92-2480](#)
Status: **Active**
Overview: EBBI™ 50D
Description: 1.27mm Pitch EBBI™ 50D Plug, Vertical, without Latch, 80 Circuits, 2.79mm PC Tail Length

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification


CSA LR19980
UL E29179

General

Product Family PCB Headers
Series [71661](#)
Application Board-to-Board, Signal, Wire-to-Board
Overview [EBBI™ 50D](#)
Product Name EBBI™
UPC 800753641372

Physical

Breakaway No
Circuits (Loaded) 80
Circuits (maximum) 80
Color - Resin Black
Durability (mating cycles max) 2,000
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 4.670/g
Number of Rows 2
Orientation Vertical
PC Tail Length 2.79mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.27mm
Pitch - Termination Interface 1.27mm
Plating min - Mating 0.762µm
Plating min - Termination 1.905µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Shrouded Fully
Stackable No
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40°C to +105°C



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71661Series](#)

Mates With
EBBI™ 50D Receptacle [71660](#) , [87552](#)

Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact
Voltage - Maximum

onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS
1A
30V

Solder Process Data

Duration at Max. Process Temperature (seconds) 40
Lead-free Process Capability Wave Capable (TH only)
Max. Cycles at Max. Process Temperature 3
Process Temperature max. C 260

Material Info

Old Part Number A-71661-1380

Reference - Drawing Numbers

Sales Drawing SDA-71661-1***

This document was generated on 02/28/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION