

PRODUCT NUMBER	AWG	WIRE BARREL			INSULATION BARREL				RECOMMENDED HANDTOOL FOR LOOSE PIECE APPLICATION
SEE SHEET 3	RANGE	DIM A	DIM B	RADIUS C	INSULATION DIAMETER RANGE	DIM D	DIM E	RADIUS F	
	18-20	.104/2.64	.104/2.64	.021/.53	.042/1.07-.103/2.62	.139/3.53	.120/3.05	.050/1.27	HT-0073
	22-26	.070/1.78	.070/1.78	.017/.43	.036/.91-.103/2.62	.139/3.53	.120/3.05	.050/1.27	HT-0095
	28-32	.054/1.37	.058/1.47	.011/.28	.028/.71-.054/1.37	.115/2.92	.105/2.67	.040/1.02	

NOTES:

1. TERMINAL MATES WITH .025±.002/0.64±0.05 SQUARE OR ROUND PIN.
- ② WHEN MEASURED ALONG DATUM -E- WITHIN .340/8.64 REF DIM.
3. PRODUCT SPECIFICATION: BUS-12-067.
APPLICATION SPECIFICATIONS:
TA-75: TERMINAL DATA FOR USE WITH MINI LATCH HOUSING.
TA-146: TERMINAL DATA FOR CONTACTS NOT USED IN HOUSINGS.
TA-210: TERMINAL DATA FOR CONTACTS USED WITH MINI ROD HOUSINGS.
TA-228: APPLICATIONS USING 20 AWG WIRE.
TA-531: INSTALLING AND REMOVING TERMINALS.
- ④ PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
5. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDERING PROCESSES.
- ⑥ THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS.
- ⑦ CONTACT SIDE OF TERMINAL WILL HAVE 50μ"/1.27μm NICKEL UNDERPLATE OVERALL WITH GOLD FLASH REQUIRED INSIDE CONTACT BOX AND WIRE BARREL ONLY. BACKSIDE OF TERMINALS TO BE PLATED WITH 30μ"/0.76μm NICKEL ONLY.

mat'l. code SEE TABLE				surface ☒		tolerance		projection		product family PV TERMINALS	
ltr	ecn no	dr	date	tolerances unless otherwise specified						title	
AN				angles	linear	.XX±.01/.X±.3 .XXX±.005/.XX±.13 XXXX±.0020/.XXX±.051		INCH/MM		MINI PV™ RECEPTACLE CRIMP TO WIRE	
								scale 1:1		dwg no	
				dr	T. BREWBAKER	2006-04-18				sheet 2 of 6	
				engr	T. BREWBAKER	2006-04-18				size	
				chr	T. BREWBAKER	2006-04-18				A3	
				appd	T. BREWBAKER	2006-04-18				type	
sheet	revision									Product Customer Drawing	
index	sheet										

1		2		3						4		5		6
MATERIAL & PLATING		SPRING THICKNESS DIM H±.0005/0.012	AWG RANGE	REELED NOTE 4	LOOSE NOTE 4	PLATING AVAILABILITY								
1/4 HARD BRASS BODY	Be/Cu SPRING					-000	-000LF	-001	-001LF	-002	-002LF			
CONTACT AREA UNDERPLATING: 50μ"/1.27μ Ni CONTACT AREA: 15μ"/0.38μ Au INSIDE BOX AREA: -000LF Au FLASH -001LF 15μ"/0.38μ Au -002LF 6μ"/0.15μ Au REMAINDER: -000LF SEE NOTE 7 -001LF 15μ"/0.38μ Au -002LF Au FLASH	Au FLASH	.0035/0.089	18-20	48241	48250	NO	YES	NO	NO	NO	NO			
			22-26	48242	48251	NO	YES	NO	NO	NO	NO			
			28-32	48243	48252	NO	YES	NO	NO	NO	NO			
		.0048/0.122	18-20	48244	48253	NO	YES	NO	NO	NO	NO			
			22-26	48245	48254	NO	YES	NO	NO	NO	NO			
			28-32	48246	48255	NO	YES	NO	NO	NO	NO			
		.0058/0.147	18-20	94011	94014	NO	NO	NO	NO	NO	NO	NO	OBS.	
			22-26	94012	94015	NO	NO	NO	NO	NO	NO	NO	OBS.	
			28-32	94013	94016	NO	NO	NO	NO	NO	NO	NO	OBS.	
		.0065/0.165	18-20	48247	48256	NO	YES	NO	NO	NO	NO	NO		
			22-26	48248	48257	NO	YES	NO	NO	NO	NO	NO		
			28-32	48249	48258	NO	YES	NO	NO	NO	NO	NO		
CONTACT AREA UNDERPLATING: 50μ"/1.27μ Ni CONTACT AREA: 30μ"/0.76μ Au INSIDE BOX AREA: -000LF Au FLASH -001LF 30μ"/0.76μ Au -002LF 8μ"/0.2μ Au REMAINDER: -000LF SEE NOTE 7 -001LF 30μ"/0.76μ Au -002LF Au FLASH	Au FLASH	.0035/0.089	18-20	48231	48266	NO	YES	NO	NO	NO	NO			
			22-26	48049	48235	NO	YES	NO	NO	NO	NO	YES		
			28-32	48048	48238	NO	YES	NO	NO	NO	NO	YES		
		.0048/0.122	18-20	48047	48232	NO	YES	NO	NO	NO	NO	YES		
			22-26	48046	48234	NO	YES	NO	NO	NO	NO	YES		
			28-32	48045	48237	NO	YES	NO	NO	NO	NO	YES		
		.0058/0.147	18-20	94017	94019	NO	NO	NO	NO	NO	NO	NO	OBS.	
			22-26	94018	94020	NO	NO	NO	NO	NO	NO	NO	OBS.	
			28-32	93259	94021	NO	NO	NO	NO	NO	NO	NO	OBS.	
		.0065/0.165	18-20	48052	48233	NO	YES	NO	NO	NO	NO	YES*		
			22-26	48051	48236	NO	YES	NO	NO	NO	NO	YES		
			28-32	48050	48239	NO	YES	NO	NO	NO	NO	YES		
* LOOSE PIECE NOT AVAILABLE														

mat'l. code SEE TABLE				surface ☒ tolerance		projection 		product family PV TERMINALS	
ltr	ecr no	dr	date	tolerances unless otherwise specified				title	
AN				angles	linear	.XX±.01/.X±.3 XXX±.005/.XX±.13 XXXX±.0020/.XXX±.051		MINI PV™ RECEPTACLE CRIMP TO WIRE	
				dr	T. BREWBAKER 2006-04-18			dwg no	
				engr	T. BREWBAKER 2006-04-18			sheet 3 of 6	
				chr	T. BREWBAKER 2006-04-18			size	
				appd	T. BREWBAKER 2006-04-18			A3	
sheet index	revision sheet							type Product Customer Drawing	

FCI

scale 1:1

1		2		3		4		5		6	
---	--	---	--	---	--	---	--	---	--	---	--

form A3

mat'l. code SEE TABLE				surface ✓		tolerance tolerances unless otherwise specified		projection INCH/MM		product family PV TERMINALS	
ltr	ecr no	dr	date	angles	linear	.XX±.01/.X±.3 .XXX±.005/.XX±.13 XXXX±.0020/.XXX±.051		scale 1:1		title MINI PV™ RECEPTACLE CRIMP TO WIRE	
AN										dwg no 47212	
						dr T. BREWBAKER 2006-04-18		engr T. BREWBAKER 2006-04-18		sheet 3 of 6	
						chr T. BREWBAKER 2006-04-18		appd T. BREWBAKER 2006-04-18		size A3	
sheet index		revision sheet								type Product Customer Drawing	



FCIconnect.com

Copyright FCI

1		2		3						4			5	6
MATERIAL & PLATING		SPRING THICKNESS		AWG	REELED	LOOSE	PLATING AVAILABILITY							
1/4 HARD BRASS BODY	Be/Cu SPRING	DIM H±.0005/0.012		RANGE	NOTE 4	NOTE 4	−000	−000LF	−001	−001LF	−002	−002LF		
CONTACT AREA UNDERPLATING: 50μ"/1.27μ Ni CONTACT AREA: 40μ"/1.02μ Au INSIDE BOX AREA: −000LF Au FLASH −001LF 8μ"/0.2μ Au −002LF 8μ"/0.2μ Au REMAINDER: −000LF SEE NOTE 7 −001LF 8μ"/0.2μ Au −002LF Au FLASH	Au FLASH	.0035/0.089	18−20	48276	N/A	NO	NO	NO	NO	NO	YES			
			22−26	47457	47743	NO	YES	NO	YES	NO	YES			
			28−32	47456	47742	NO	YES	NO	YES	NO	YES			
		.0048/0.122	18−20	47441	47713	NO	YES	NO	YES	NO	YES			
			22−26	47439	47712	NO	YES	NO	YES	NO	YES			
			28−32	47437	47711	NO	YES	NO	YES	NO	YES			
		.0058/0.147	18−20	94022	94025	NO	NO	NO	NO	NO	NO	OBS.		
			22−26	94023	94026	NO	NO	NO	NO	NO	NO	OBS.		
			28−32	94024	94027	NO	NO	NO	NO	NO	NO	OBS.		
		.0065/0.165	18−20	47566	47746	NO	YES	NO	YES	NO	YES			
			22−26	47565	47745	NO	YES	NO	YES	NO	YES			
			28−32	47564	47744	NO	YES	NO	YES	NO	YES			
		DISCONTINUED				48191	48194							
		DISCONTINUED				48192	48195							
		DISCONTINUED				48193	48196							
CONTACT AREA UNDERPLATING: 50μ"/1.27μ Ni CONTACT AREA: 75μ"/1.91μ Au INSIDE BOX AREA: −000LF Au FLASH −001LF 75μ"/1.91μ Au −002LF 30μ"/0.76μ Au REMAINDER: −000LF SEE NOTE 7 −001LF 75μ"/1.91μ Au −002LF 15μ"/0.38μ Au	Au FLASH	.0035/0.089	18−20	47785	48014	NO	YES	NO	NO	NO	NO			
			22−26	47784	48015	NO	NO	NO	NO	NO	NO	OBS.		
			28−32	47783	48013	NO	NO	NO	NO	NO	NO	OBS.		
		.0048/0.122	18−20	47220	47707	NO	NO	NO	NO	NO	NO	OBS.		
			22−26	47216	47706	NO	YES	NO	NO	NO	NO			
			28−32	47212	47705	NO	YES	NO	NO	NO	NO			
		.0058/0.147	18−20	94028	94031	NO	NO	NO	NO	NO	NO	OBS.		
			22−26	94029	94032	NO	NO	NO	NO	NO	NO	OBS.		
			28−32	94030	94033	NO	NO	NO	NO	NO	NO	OBS.		

mat'l. code				surface		tolerance		projection		product family	
SEE TABLE				✓				⊕		PV TERMINALS	
ltr	ecn no	dr	date	tolerances unless otherwise specified						title	
AN				angles		linear		INCH/MM		MINI PV™ RECEPTACLE	
						.XX±.01/.X±.3				CRIMP TO WIRE	
						.XXX±.005/.XX±.13				dwg no	
						.XXX±.0020/.XXX±.051		scale 1:1		sheet 4 of 6	
				dr		T. BREWBAKER 2006-04-18		FCI		size	
				engr		T. BREWBAKER 2006-04-18				47212	
				chr		T. BREWBAKER 2006-04-18				A3	
				appd		T. BREWBAKER 2006-04-18				type Product Customer Drawing	
sheet index	revision sheet										

1

2

3

4

5

6

form A3

1

2

3

4

5

6

D

mat'l. code SEE TABLE				surface ✓		tolerance tolerances unless otherwise specified		projection INCH/MM		product family PV TERMINALS	
ltr	ecr no	dr	date	angles		linear		scale 1:1		title MINI PV™ RECEPTACLE CRIMP TO WIRE	
AN										dwg no 47212	
										sheet 4 of 6	
										size A3	
										type Product Customer Drawing	
sheet	revision										
index	sheet										

MATERIAL & PLATING		SPRING THICKNESS DIM H±.0005/0.012	AWG RANGE	REELED NOTE 4	LOOSE NOTE 4	PLATING AVAILABILITY						
1/4 HARD BRASS BODY	Be/Cu SPRING					-000	-000LF	-001	-001LF	-002	-002LF	
PRE-PLATED: UNDERPLATING: 50μ"/1.27μ Ni OVERPLATING: 100-200μ"/2.54-5.08μ 60/40 TIN LEAD "LF NOT AVAILABLE" SEE LEAD-FREE EQUIVALENTS BELOW	Sn PLATED	.0035/0.089	22-26	47445	47747	NO	NO	NO	NO	NO	NO	OBS.
			28-32	47446	47748	NO	NO	NO	NO	NO	NO	OBS.
		.0048/0.122	18-20	47221	47716	NO	NO	NO	NO	NO	NO	OBS.
			22-26	47217	47715	NO	NO	NO	NO	NO	NO	OBS.
		.0058/0.147	28-32	47213	47714	NO	NO	NO	NO	NO	NO	OBS.
			18-20	94034	94037	NO	NO	NO	NO	NO	NO	OBS.
		.0065/0.165	22-26	94035	94038	NO	NO	NO	NO	NO	NO	OBS.
			28-32	94036	94039	NO	NO	NO	NO	NO	NO	OBS.
		.0065/0.165	18-20	47648	47749	NO	NO	NO	NO	NO	NO	OBS.
			22-26	47649	47750	NO	NO	NO	NO	NO	NO	OBS.
		.0065/0.165	28-32	47650	47751	NO	NO	NO	NO	NO	NO	OBS.
PRE-PLATED: -000LF 100-160μ" 2.54-4.06μ Sn (LEAD-FREE) NOTE 6	Sn PLATED	.0035/0.089	22-26	47445	47747	NO	YES	NO	NO	NO	NO	
			28-32	47446	47748	NO	YES	NO	NO	NO	NO	
		.0048/0.122	18-20	47221	47716	NO	YES	NO	NO	NO	NO	
			22-26	47217	47715	NO	YES	NO	NO	NO	NO	
		.0058/0.147	28-32	47213	47714	NO	YES	NO	NO	NO	NO	
			18-20	94034	94037	NO	NO	NO	NO	NO	NO	OBS.
		.0065/0.165	22-26	94035	94038	NO	NO	NO	NO	NO	NO	OBS.
			28-32	94036	94039	NO	NO	NO	NO	NO	NO	OBS.
		.0065/0.165	18-20	47648	47749	NO	YES	NO	NO	NO	NO	
			22-26	47649	47750	NO	YES	NO	NO	NO	NO	
		.0065/0.165	28-32	47650	47751	NO	YES	NO	NO	NO	NO	

mat'l. code SEE TABLE				surface ✓		tolerance tolerances unless otherwise specified		projection INCH/MM		product family PV TERMINALS	
ltr	ecr no	dr	date	angles	linear	.XX±.01/.X±.3 .XXX±.005/.XX±.13 XXXX±.0020/.XXX±.051		scale 1:1		title MINI PV™ RECEPTACLE CRIMP TO WIRE	
AN										sheet 5 of 6	
										size A3	
										dwg no 47212	
										type Product Customer Drawing	
sheet	revision										
index	sheet										

MATERIAL & PLATING		SPRING THICKNESS DIM H±.0005/0.012	AWG RANGE	REELED NOTE 4	LOOSE-PIECE NOTE 4	
1/4 HARD BRASS BODY	Be/Cu SPRING					
UNDERPLATING: 50u"X1.27u Ni CONTACT AREA: 30u"/0.76u GXT INSIDE BOX AREA: -600 Au FLASH REMAINDER: -600 Au FLASH	Au FLASH	.0035/0.089	18-20	48231-600	48266-600	OBS.
			22-26	48049-600	48235-600	OBS.
			28-32	48048-600	48238-600	OBS.
		.0048/0.122	18-20	48047-600	48232-600	OBS.
			22-26	48046-600	48234-600	OBS.
			28-32	48045-600	48237-600	OBS.
		.0058/0.147	18-20	94017-600	94019-600	OBS.
			22-26	94018-600	94020-600	OBS.
			28-32	93259-600	94021-600	OBS.
		.0065/0.165	18-20	48052-600	48233-600	OBS.
			22-26	48051-600	48236-600	OBS.
			28-32	48050-600	48239-600	OBS.

mat'l. code SEE TABLE				surface ☒ tolerance		projection		product family PV TERMINALS			
ltr	ecn no	dr	date	tolerances unless otherwise specified		 INCH/MM scale 1:1		title			
AN				angles	linear			.XX±.01/.X±.3 .XXX±.005/.XX±.13 .XXXX±.0020/.XXX±.051		MINI PV™ RECEPTACLE CRIMP TO WIRE	
				dr	T. BREWBAKER	2006-04-18			sheet 6 of 6		
				engr	T. BREWBAKER	2006-04-18			size		
				chr	T. BREWBAKER	2006-04-18			A3		
				appd	T. BREWBAKER	2006-04-18					
sheet index		revision sheet							type Product Customer Drawing		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[47751-000](#) [47439-001LF](#) [47649-000LF](#) [47439-000LF](#) [48258-000LF](#) [48239-000LF](#) [48238-000LF](#) [48248-000LF](#)
[48049-000LF](#) [48048-000LF](#) [48046-000](#) [47650-000](#) [48050-000](#) [47750-000](#) [48254-000](#) [47747-000](#) [48242-000](#)
[48236-000](#) [48049-000](#) [48266-000](#) [48052-000](#) [48252-000](#) [48238-000](#) [48257-000](#) [48232-000](#) [48251-000](#) [48237-000](#)
[48234-000](#) [48233-000](#) [48255-000](#) [48239-000](#) [47716-000](#) [47748-000](#) [48248-000](#) [48243-000](#) [48258-000](#) [48235-](#)
[000](#) [48245-000](#) [48045-000](#) [47743-002LF](#) [47748-000LF](#) [47212-000LF](#) [47213-000LF](#) [47439-002LF](#) [47446-000LF](#)
[47457-000LF](#) [47564-001LF](#) [47565-001LF](#) [47566-000LF](#) [47648-000LF](#) [47706-000LF](#) [47711-001LF](#) [47712-001LF](#)
[47744-001LF](#) [47746-000LF](#) [47746-001LF](#) [48046-002LF](#) [48047-000LF](#) [48234-002LF](#) [48236-002LF](#) [48237-002LF](#)
[48238-002LF](#) [48239-002LF](#) [48241-000LF](#) [48244-000LF](#) [48247-000LF](#) [48249-000LF](#) [48253-000LF](#) [48256-000LF](#)
[48234-000LF](#) [48232-000LF](#) [48236-000LF](#) [48237-000LF](#) [48233-000LF](#) [48235-000LF](#) [48254-000LF](#) [48250-000LF](#)
[48252-000LF](#) [48257-000LF](#) [48255-000LF](#) [48251-000LF](#) [48266-000LF](#) [48242-000LF](#) [48246-000LF](#) [48245-000LF](#)
[48243-000LF](#) [48046-000LF](#) [48045-000LF](#) [48052-000LF](#) [48050-000LF](#) [48051-000LF](#) [47743-000LF](#) [47747-000LF](#)
[47744-000LF](#) [47715-000LF](#) [47716-000LF](#) [47714-000LF](#) [47750-000LF](#) [47565-000LF](#) [47564-000LF](#)