

HC-B 32-TFQ-80/O1M25S

Order No.: 1604871



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1604871>

HEAVYCON sleeve housing B32, for double locking latch, height 80 mm, with support 1x M25, lateral conductor exit

Commercial data

GTIN (EAN)	4 017918 882273
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 504 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B32, DD144, M
Design	B32
Height	80 mm
Width	79 mm
Length	94 mm

Housing type	Sleeve housings
Locking type	For double locking latch
Cable exit	Lateral
Type of the screw connection	1x M25
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;