



1	2	3	4	5
---	---	---	---	---



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR MATERIAL: PBT
FLAMMABILITY RATING: UL94-V0
COLOR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: SELECTIVE GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES


ENVIRONMENTAL
OPERATING TEMPERATURE: -40 °C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.5 A
WORKING VOLTAGE: 120 VAC
INSULATION RESISTANCE: >500 MΩ
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MIN
CONTACT RESISTANCE: 20 mΩ MAX


STANDARD
 CERTIFIED: E324776


SOLDERING
JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
TRAY



PCB LAYOUT - COMPONENT VIEW



RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15			DESCRIPTION: HORIZONTAL SHIELDED 3.05mm REAR GROUNDING POST 8P8C MODULAR JACK TAB DOWN WERI PART NO: 615 008 142 621	SIZE A4	D
G										
F										
E	03-JAN-14	UL & TEMP UPDATE	QL							
D	09-SEP-13	DWG REVIEW	QL	APPROVAL: RJ	UNIT: MM					
C	22-MAR-11	CAT 5	GG							
B	06-OCT-09	UL STANDARD	JP							
A	20-JUN-08	PDF	CH							
REV	DATE	FILE	BY							
					SCALE:					
					SHEET: 1/1					
					DRAW:					