







LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
CM		52										C	REV & REDWN PER EC 0730-0059-95	3-21-95	KS	RS	

- 1 WIRE RANGE: 0.13-0.2mm² (26-24 AWG).
- 2 INSULATION RANGE: 0.64-1.27 [.025-.050] MAX. DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- △ TIP PLATE WITH 0.00076-0.00091 [.000030-.000036] MIN GOLD IN THE LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.



△ GOLD PLATE	0.20 [.008] PH05 BRZ	640579-2
PRE-TIN	0.20 [.008] PH05 BRZ	640579-1
FINISH	MATERIAL	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES: ON: 2 PLC DEC ±0.13 [.005] 3 PLC DEC ±- ANGLES ± -		DR 3-21-95 K. SALMON	AMP AMP Incorporated Harrisburg, PA 17105-3608		
MATERIAL		CHK 3-21-95 R. SWING			
SEE TABLE		APPD 3-21-95 W. LONG	NAME		
FINISH		APPD 3-21-95 W. LONG	PIN, LOOSE PIECE, MR		
SEE TABLE		PRODUCT SPEC -			
		APPLICATION SPEC -	SIZE D	CAGE CODE 00779	DRAWING NO C-640579
		WEIGHT -	SCALE 5:1	SHEET 1 OF 1	

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.