

Silicon Epitaxial Planar Transistor

2SA1162

FEATURES


- Low noise: NF=1dB(Typ), 10dB(Max).
- Complementary to 2SC2712.
- Small package.



Lead-free

APPLICATIONS

- General purpose application.



ORDERING INFORMATION

Type No.	Marking	Package Code
2SA1162	SO/SY/SG	SOT-23

MAXIMUM RATING @ Ta=25°C unless otherwise specified

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	-50	V
V_{CEO}	Collector-Emitter Voltage	-50	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current -Continuous	-150	mA
P_C	Collector Dissipation	150	mW
T_j, T_{stg}	Junction and Storage Temperature	-55~125	°C

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified

Silicon Epitaxial Planar Transistor**2SA1162**

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = -100\mu A, I_E = 0$	-50			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = -1mA, I_B = 0$	-50			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E = -100\mu A, I_C = 0$	-5			V
Collector cut-off current	I_{CBO}	$V_{CB} = -50V, I_E = 0$			-0.1	μA
Emitter cut-off current	I_{EBO}	$V_{EB} = -5V, I_C = 0$			-0.1	μA
DC current gain	h_{FE}	$V_{CE} = -6V, I_C = -2mA$	70		400	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = -100mA, I_B = -10mA$			-0.3	V
Transition frequency	f_T	$V_{CE} = -10V, I_C = -1mA$	80			MHz
Collector output capacitance	C_{ob}	$V_{CB} = -10V, I_E = 0, f = 1MHz$			7	pF
Noise figure	NF	$V_{CE} = -6V, I_C = 0.1mA, f = 1MHz, R_g = 10k\Omega$			10	dB








CLASSIFICATION OF $h_{FE(1)}$

Rank	O	Y	G
Range	70-140	120-240	200-400

Silicon Epitaxial Planar Transistor

2SA1162

TYPICAL CHARACTERISTICS @ $T_a=25^\circ\text{C}$ unless otherwise specified




Silicon Epitaxial Planar Transistor

2SA1162


PACKAGE OUTLINE

Plastic surface mounted package

SOT-23



SOLDERING FOOTPRINT



PACKAGE INFORMATION

Device	Package	Shipping
2SA1162	SOT-23	3000/Tape&Reel