


RECOMMENDED P.C.B. LAYOUT
SCALE 1X





CIRCUIT: 4PDT

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
		
DN	NONE	<DN>
2-3,5-6 8-9,11-12	DPEN	2-1, 5-4 8,7 11-10


NOTES:

(ON) = MOMENTARY

1. ALL DIMENSIONS IN MM [INCH]
E
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
OPP
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.4 VOLT-AMPS MAX. @20V MAX. AC OR DC.
5. CONTACT MATERIAL: GOLD PLATING.
6. ELECTRICAL LIFE: 40,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000M OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -30°C TO 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT



SECTION A-A



 E-SWITCH™			
TITLE			
3004P2J2REDM2RE			
SCALE	DATE	DR	DWG
2:1	7/3/07	TN	T346013
REV			
B			