




- 1 0.38µm [.000015] MIN GOLD ON MATING AREA, 1.27µm [.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 2 2.54µm [.000100] MIN BRIGHT TIN-LEAD, OVER 1.27µm [.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA, 2.54µm [.000100] MIN TIN ON MATING AREA, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 4 0.38µm [.000015] MIN GOLD ON MATING AREA, GOLD FLASH ON CRIMP AREA, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3	6	487923-4
5 OBSOLETE	1	487923-3
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME		
0 PLC ± -		PRODUCT SPEC -	CONTACT, SOLDER TAB, .050 C/L		
1 PLC ± -		APPLICATION SPEC -	-		
2 PLC ± 0.13 [.005]		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=487923
3 PLC ± -		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV D1
4 PLC ± -					
ANGLES ± -					
FINISH					
MATERIAL PHOSPHOR BRONZE		SEE TABLE			