









PANEL MOUNTING



CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @ 250 VAC
6A @ 24 VDC
5. MECHANICAL LIFE: 100,000 CYCLES
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. OPERATING TEMP.: -20°C to 55°C
- ▲ 9. LAMP VOLTAGE: 24V DC RED LED
10. SEAL RATING: IP40
11. ▲ DENOTES CRITICAL PARAMETER.
12. PANEL THICKNESS: 0.5mm TO 5.0 mm.
13. 2002/05/EC (ROHS) COMPLIANT.
14. PACKAGE: BOX/20 PIECES PER BOX



PARTS LIST

ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040007	D16OAT11
2	1	F050423	5000423 24VDC RED LED
3	1	F050205	5000205 TRANSPARENT WHITE LENS



E-SWITCH®



TITLE D16OAT11KREDWHT

A	19142	RELEASED FOR PRODUCTION	6/24/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
1.5:1	6/24/2010	BLR	XF0822P	A