




THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION SEP ,2005.							LOC J		DIST		REVISIONS								
© COPYRIGHT 2005 By --				ALL RIGHTS RESERVED.											變更								
															P LTR DESCRIPTION			DATE		DWN		APVD	
															F5 REVISED(ADD A NEW PN)			23DEC2015		A.X		H.W	
NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.																							
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	—	0.5	10.55	—	—	1.1	1.1	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	9—1747981—2									
AVAILABLE	WITH P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITH BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	9—1747981—1									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	14.3	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	8—1747981—2 2—1747981—5									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	CLEAR TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	8—1747981—1									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITH BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	3—1747981—1									
NOT AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	#4—40 UNC	0.5	10.55	12.75	10.08	2.2	1.8	WITH BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—4									
AVAILABLE	WITHOUT P/N	Au 0.76um MIN	16.3	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—3									
NOT AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	#4—40 UNC	0.5	10.05	12.75	10.08	2.2	1.8	WITHOUT BOSS	HARDTRAY PACKING (—)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—2									
AVAILABLE	WITHOUT P/N	Au 0.76um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	2—1747981—1									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	1.5	1.5	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—8									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—7									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 5)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—6									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	14.3	M3 x 0.5	0.5	10.05	10.95	7.98	1.5	1.5	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—5									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—4									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	#4—40 UNC	0.5	10.05	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—3									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	1.5	1.5	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—2									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1—1747981—1									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	—	0.5	10.05	—	—	1.5	1.5	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	1747981—2									
AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	—	—	0.5	10.05	—	—	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	1747981—1									
TOOL STATUS	PART NUMBER MARKING	CONTACT AREA PLATING SPEC J	DIM H	SCREW SIZE DIM G	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	BOSS	PACKING	CONNECTOR TYPE	PART NUMBER									
1 CONTACT COPLANALITY IS 0.1 MAXIMUM. THIS DIMENSION MEANS CENTER OF THE POCKET. FINISH CONTACT: CONTACT AREA J: SEE TABLE 2μm MIN Sn PLATING ON SOLDERING AREA 2μm MIN Ni UNDER PLATING ALL OVER SHELL: 1μm MIN Sn PLATING ALL OVER 1μm MIN Ni UNDER PLATING ALL OVER										THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y.HIRATA 15SEP2005 CHK T.KIMURA 15SEP2005 APVD K.IKEGAMI 15SEP2005 PRODUCT SPEC 製品規格 108—78180—1 APPLICATION SPEC 取付適用規格		NAME 名称 HDMI 19 POS RECEPTACLE ASSY SMT TYPE —LEAD FREE—									
DIMENSIONS: 単位： 耗 mm										TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC ± 0.2 4 PLC ± 0.2 ANGLES ± —		FINISH 仕上		SIZE A3 CAGE CODE 00779 DRAWING NO 番号 C—1747981		RESTRICTED TO							
MATERIAL 材料										WEIGHT		CUSTOMER DRAWING		SCALE 尺度 NTS		SHEET 1 OF 8		REV F5					



2				1				
LOC	DIST	REVISIONS						
J	—	P	LTR	變更 DESCRIPTION		DATE	DWN	APVD
			—	SEE SHEET 1		—	—	—



NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity							
DIMENSIONS: 単位： 耗 mm		CHK		NAME 名称							
		APVD		HDMI 19 POS RECEPTACLE ASSY SMT TYPE -LEAD FREE-							
		PRODUCT SPEC 製品規格 108-78180-1									
		APPLICATION SPEC 取付適用規格									
		WEIGHT									
MATERIAL 材料		FINISH 仕上		SIZE A3		CAGE CODE 00779		DRAWING NO 番号 C-1747981		RESTRICTED TO —	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		± 0.3		CUSTOMER DRAWING							
0 PLC ± 0.2		± 0.2		SCALE 尺度 NTS		SHEET 5 OF 8		REV F5			
1 PLC ± 0.2		± 0.2									
2 PLC ± 0.2		± 0.2									
3 PLC ± 0.2		± 0.2									
4 PLC ± 0.2		± 0.2									
ANGLES ± -											



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,2005.

© COPYRIGHT 2005 By -

ALL RIGHTS RESERVED.

LOC
JDIST
/

REVISIONS

変更

P

LTR




DESCRIPTION

DATE

DWN



APVD

SEE SHEET 1




CONNECTOR WITH FLANGE TYPE

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL
OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± 0.2
1 PLC ± 0.2
2 PLC ± 0.2
3 PLC ± 0.2
4 PLC ± 0.2
ANGLES ± 0.1

MATERIAL
材料FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME
名称

HDMI 19 POS
RECEPTACLE ASSY SMT TYPE
-LEAD FREE-

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A300779

C-1747981

SCALE
尺度 NTS



SHEET

7 of 8

REV
F5

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J			-	SEE SHEET 1	-

NOTICE: THIS COMMUNICATION INCLUDES TE CONNECTIVITY CONFIDENTIAL
OR PROPRIETARY INFORMATION THAT MAY ALSO BE LEGALLY PRIVILEGED.



MATING CONDITION (REFERENCE)
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN			
DIMENSIONS: 単位： 耗 mm		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD			
0 PLC ± 0.2		PRODUCT SPEC			
1 PLC ± 0.2		製品規格			
2 PLC ± 0.2		108-78180-1			
3 PLC ± 0.2		APPLICATION SPEC			
4 PLC ± 0.2		取付適用規格			
ANGLES ± 0.2		WEIGHT			
FINISH 仕上		CUSTOMER DRAWING			
MATERIAL 材料		SCALE 2:1			
		SHEET 8 of 8			
		REV F5			