

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19


© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS		DATE	APPD
				ZONE	DESCRIPTION		
AJ	16	✓	✓				
				G	REDWN, REV & ADD 1--1, 1--2 & 1--3 PER AJ-4833	3-14-91	BAS
				H	REV PER AJ-5802	11-12-91	JL

1 GOLD PLATE PER MIL-G-45204
1.27 μ m [.000050] MINIMUM THICK

2 GOLD PLATE PER MIL-G-45204
2.54 μ m [.000100] MINIMUM THICK



0.64 [.025]	1.07±0.03 [.042±.001]	1	1-225467-3
0.64 [.025]	0.79±0.03 [.031±.001]	2	1-225467-2
0.64 [.025]	0.99±0.03 [.039±.001]	3	1-225467-1
0.38 [.015]	0.46±0.03 [.018±.001]	4	1-225467-0
0.51 [.020]	0.66±0.03 [.026±.001]	5	225467-8
0.64 [.025]	1.07±0.03 [.042±.001]	6	225467-6
0.64 [.025]	0.79±0.03 [.031±.001]	7	225467-4
0.64 [.025]	0.99±0.03 [.039±.001]	8	225467-2
B	A	CONTACT PLATING	PART NUMBER

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20 [.008]
3 PLC DEC ± -
ANGLES ± -

MATERIAL
BRASS PER QQ-B-626

FINISH



DR 3-14-91
B. SCOTT

CHK 3-21-91
J. LIPPERT

APPD 4-5-91
M. PHILLIPS

APPD 4-5-91
J. LIPPERT

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

CONTACT, CENTER,
DUAL CRIMP, SERIES INC

SIZE

CAGE CODE

DRAWING NO

©

00779

225467

SCALE 15:1

SHEET

1 OF 1

AMP 1471-6 REV 9-89

12 NOV 1991 14-55-33 AMP2204

CUSTOMER DRAWING