





MODULAR CONNECTORS

CL 222 TM


Right Angle Dip Type

• TM5RC- * *(50)

CL No.	Part No.	RoHS
222-0270-9-50	TM5RC-44(50)	YES
222-0338-0-50	TM5RC-64(50)	
222-0337-8-50	TM5RC-66(50)	



PCB mounting hole layout
(Connector mounting side)







Note 1: Standard finish color is gray.


Note 2: The drawing is shown sample of TM5RC-66(50).

• TM5RC-88(50)

CL No.	Part No.	RoHS
222-0339-3-50	TM5RC-88(50)	YES



PCB mounting hole layout
(Connector mounting side)




Note : Standard finish color is warm gray.

MODULAR CONNECTORS


CL 222 TM

● TM5RE1- * *(20)

CL No.	Part No.	A	B	C	RoHS
222-0538-0-20	TM5RE1-44(20)	13	10.4	8	YES
222-0539-2-20	TM5RE1-62(20)	15	12.4	10	
222-0540-1-20	TM5RE1-64(20)	15	12.4	10	
222-0541-4-20	TM5RE1-66(20)	15	12.4	10	



PCB mounting hole layout
(Connector mounting side)




Note 1: Standard finish color is dark gray.


Note 2: The drawing is shown sample of TM5RE1-66(20).

● TM5RE2- * *(20)

CL No.	Part No.	A	B	C	RoHS
222-1222-1-20	TM5RE2-44(20)	13	10.4	10.8	YES
222-1224-7-20	TM5RE2-62(20)	15	12.4	12.8	
222-1223-4-20	TM5RE2-64(20)	15	12.4	12.8	
222-1225-0-20	TM5RE2-66(20)	15	12.4	12.8	



PCB mounting hole layout
(Connector mounting side)



Note 1: Standard finish color is dark gray.

Note 3: The drawing is shown sample of TM5RE2-66(20).

MODULAR CONNECTORS


CL 222 TM

● TM5RE3-*(20)


CL No.	Part No.	A	B	C	RoHS
222-1406-4-20	TM5RE3-44(20)	13	10.4	10.8	YES
222-1407-7-20	TM5RE3-62(20)	15	12.4	12.8	
222-1427-4-20	TM5RE3-64(20)	15	12.4	12.8	
222-1428-7-20	TM5RE3-66(20)	15	12.4	12.8	
222-1702-7-20	TM5RE3-88(20)	18.6	16	16.4	




TM5RE3-66(20)



TM5RE3-88(20)





PCB mounting hole layout
(Connector mounting side)



Note 1: Standard finish color is dark gray.

Note 2: The drawing is shown sample of TM5RE3-88(20).


● TM5RF-44(50)



CL No.	Part No.	RoHS
222-0391-3-50	TM5RF-44(50)	YES

PCB mounting hole layout
(Connector mounting side)

C.L. : Center Line



Note 1: Standard finish color is gray.

Note 2: Backboard size is shown the connector mounting side of PCB.

CL 222 TM


MODULAR CONNECTORS

CL 222 TM

● TM5RJ2- * *(50)






TM5RJ2-66(50)




TM5RJ2-88(50)


CL No.	Part No.	A	B	C	RoHS
222-1459-0-50	TM5RJ2-44(50)	12.8	10.2	10	YES
222-1486-3-50	TM5RJ2-62(50)	14.8	12.2	12	
222-1460-0-50	TM5RJ2-64(50)	14.8	12.2	12	
222-1461-2-50	TM5RJ2-66(50)	14.8	12.2	12	
222-1462-5-50	TM5RJ2-88(50)	18.6	16	15	



PCB mounting hole layout
(Connector mounting side)



TM5RJ2-44, 6 *




TM5RJ2-88(50)


Note 1: Standard finish color is gray.

Note 2: The drawing is shown sample of TM5RJ2-88(50).

● TM5RJ3- * *(50)






TM5RJ3-66(50)




TM5RJ3-88(50)


CL No.	Part No.	A	B	C	RoHS
222-1363-3-50	TM5RJ3-44(50)	12.8	10.2	10.76	YES
222-1487-6-50	TM5RJ3-62(50)	14.8	12.2	12.8	
222-1463-8-50	TM5RJ3-64(50)	14.8	12.2	12.8	
222-1464-0-50	TM5RJ3-66(50)	14.8	12.2	12.8	
222-1465-3-50	TM5RJ3-88(50)	18.6	16	16.6	



PCB mounting hole layout
(Connector mounting side)



TM5RJ3-44, 6 *



TM5RJ3-88(50)

Note 1: Standard finish color is gray.




Note 2: The drawing is shown sample of TM5RJ3-88(50).

MODULAR CONNECTORS


CL 222 TM

● TM5RU-6 *(50)

CL No.	Part No.	RoHS
222-2639-8-50	TM5RU-62(50)	YES
222-2638-5-50	TM5RU-64(50)	
222-2630-3-50	TM5RU-66(50)	



PCB mounting hole layout
(Connector mounting side)



Note 1: Standard finish color is black.

Note 2: The drawing is shown sample of TM5RU-66(50).




MODULAR CONNECTORS

CL 222 TM


Gang-Jacks Right Angle Dip Type

● TM2REA-06 * *(50)


CL No.	Part No.	RoHS
222-1277-3-50	TM2REA-0602(50)	YES
222-1466-6-50	TM2REA-0604(50)	
222-1467-9-50	TM2REA-0606(50)	




PCB mounting hole layout
(Connector mounting side)



TM2REA-0602(50)



TM2REA-0604(50)




TM2REA-0606(50)

Note 1: Standard finish color is gray.


Note 2: The drawing is shown sample of TM2REA-0602(50).

● TM2REA-12 * *(50)


CL No.	Part No.	RoHS
222-0802-6-50	TM2REA-1204(50)	YES
222-0799-3-50	TM2REA-1208(50)	
222-0681-3-50	TM2REA-1212(50)	




PCB mounting hole layout
(Connector mounting side)



TM2REA-1204(50)



TM2REA-1208(50)



TM2REA-1212(50)





Note 1: Standard finish color is gray.

Note 2: The drawing is shown sample of TM2REA-1204(50).

MODULAR CONNECTORS


CL 222 TM

● TM2REA-18 * *(50)




TM2REA-1812(50)

PCB mounting hole layout
(Connector mounting side)



TM2REA-1806(50)








TM2REA-1818(50)

Note 1: Standard finish color is gray.

Note 2: The drawing is shown sample of TM2REA-1806(50).


● TM2REA-24 * *(50)




TM2REA-2416(50)

CL No.	Part No.	RoHS
222-0800-0-50	TM2REA-2408(50)	YES
222-0749-5-50	TM2REA-2416(50)	
222-0750-4-50	TM2REA-2424(50)	

PCB mounting hole layout
(Connector mounting side)



TM2REA-2408(50)



TM2REA-2424(50)



Note 1: Standard finish color is gray.

Note 2: The drawing is shown sample of TM2REA-2416(50).

MODULAR CONNECTORS


CL 222 TM

● TM5RQ-1414(50)





CL No.	Part No.	RoHS
222-1504-3-50	TM5RQ-1414(50)	YES

PCB mounting hole layout
(Connector mounting side)




Note : Standard finish color is gray.

● TM5RQ-2020(50)





CL No.	Part No.	RoHS
222-1645-5-50	TM5RQ-2020(50)	YES

PCB mounting hole layout
(Connector mounting side)





Note : Standard finish color is gray.

● TM5RSA-2424(50)



CL No.	Part No.	RoHS
222-3264-2-50	TM5RSA-2424(50)	YES



PCB mounting hole layout (Connector mounting side)


Note : Standard finish color is gray.

CL 222 TM


Technical drawing of a mechanical part with dimensions and a keyway label. The drawing shows a cross-section of a component with a central keyway. Dimensions are provided in millimeters (mm):

- Overall width: 31.9
- Distance between the two main vertical sections: 29
- Distance between the two main vertical sections (inner): 13.1
- Distance between the two main vertical sections (outer): 29.4
- Distance between the two main vertical sections (inner, bottom): 0.43
- Distance between the two main vertical sections (outer, bottom): 3
- Distance between the two main vertical sections (inner, bottom): A


The label "KEY WAY" points to the central keyway.



- TM5RSB-2424(50)



Technical drawing of a three-bladed propeller. The drawing shows a cross-section of the propeller with three blades. Key dimensions are labeled: 45.3 (total width), 42.5 (blade width), 13.1 (blade spacing), 3 (blade thickness), 40.9 (hub diameter), and 0.43 (blade thickness at tip). A label 'KEY WAY' points to a feature on the hub.



- 29 -

MODULAR CONNECTORS

CL 222 TM

EIGHT-CONDUCTOR LOW PROFILE JACKS

● GENERAL

The TM5RL Series are small 8-contact modular connectors designed to be 11.7 mm in height and 23% smaller in volume than our former models to meet the demand for smaller and thinner electronic equipment.

● FEATURES

- (1) 11.7 mm in height above PCB surface (shielded jacks: 11.9 mm)
- (2) 23% smaller in volume than our former models
- (3) Space-saving: 14 mm (14.6 mm) in width and 17 mm (7.6 mm) in depth. (): shielded jacks
- (4) EMI-protected ferrite and shielded jacks available.
- (5) Ferrite and shielded jacks use the same connector body as standard jacks, requiring no change in the PCB for redesigning.
(When you plan to redesign a standard PCB to a shielded PCB, select the shielding pattern in advance).
- (6) A quadruple jack is equal to or smaller in size than four TM5RL-88 jacks combined.
- (7) Plugs and jack connectors comply with the ISO 8877 Standard (ISDN interface connector).




● APPLICATIONS

LAN boards, HUB, ISDN terminals, and personal computers.

● RIGHT-ANGLE DIP TYPE

● TM5RL *-88(50)

CL No.	Part No.	Type	RoHS
222-2665-8-50	TM5RL-88(50)	Standard	YES
222-2666-0-50	TM5RLF-88(50)	With ferrite core	



Note : When preparing frames or PCBs, follow the above  dimensions.




MODULAR CONNECTORS

CL 222 TM


Quadruplet right-angle dip

• TM5RL *-3232(50)

CL No.	Part No.	Type	RoHS
222-2671-0-50	TM5RL-3232(50)	Standard	YES
222-2711-3-50	TM5RLF-3232(50)	With ferrite core	




Mounting dimensions for reference (PCB mounting side)



Note : When preparing frames or PCBs, provide the above  for the connector.

Eight-conductor extension adapter

• TM5RL *-88-JJ(50)



CL No.	Part No.	Type	RoHS
222-3798-7-50	TM5RL-88-JJ(50)	Standard	YES
222-3805-0-50	TM5RLF-88-JJ(50)	With ferrite core	

Terminal numbers

Connector(a) terminal No.	1	2	3	4	5	6	7	8
TM5RL-88								
Connector(b) terminal No.	1	2	3	4	5	6	7	8
TM5RL-88								