





LOC	DIST	REVISONS				
		F	LTR	DESCRIPTION	DATE	DWN APVD
GP	00	A	REV PER	ECO-07-016610	17JULY07	JRP AWF



- ① HOUSING: HIGH TEMPERATURE THERMOPLASTIC.
- ② CONTACT: PHOSPHOR BRONZE.
- ③ CONTACT FINISH: .000100 MIN NICKEL ALL OVER.
.000030 MIN GOLD OVER NICKEL IN CONTACT AREA.
.000100 MIN MATTE TIN OVER NICKEL ON SOLDER TAILS.
- ④ METAL HOLD DOWN: BRASS
- ⑤ METAL HOLD DOWN FINISH: .000050 MIN NICKEL ALL OVER,
.000150 MIN MATTE TIN ALL OVER.
- ⑥ DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- ⑦ AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN APPROXIMATE AREA SHOWN.



SECTION L-L
SCALE 8:1



TUBE	5145547-2
TRAY	5145547-1
PACKAGING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AL FRANTUM 18 MAY 05	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608						
		CHK AL FRANTUM 18 MAY 05									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONNECTOR ASSEMBLY, 92 DUAL POSITION, .050 SERIES, STANDARD EDGE SURFACE MOUNT	SIZE CAGE CODE DRAWING NO A1 00779 C=5145547		RESTRICTED TO —				
		0 PLC ± —							PRODUCT SPEC		
		1 PLC ± —							APPLICATION SPEC		
		2 PLC ± 0.13 [.005]									
		4 PLC ± —									
ANGLES		± 2°									
FINISH		—									
MATERIAL 		WEIGHT —		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2		REV A	

AMP 4809 REV 31MAR2000